

6th Generation 650 V, 16 A Silicon Carbide Schottky Diode


Description

With the performance advantages of a Silicon Carbide (SiC) Schottky Barrier diode, power electronics systems can expect to meet higher efficiency standards than Si-based solutions, while also reaching higher frequencies and power densities. SiC diodes can be easily paralleled to meet various application demands, without concern of thermal runaway. In combination with the reduced cooling requirements and improved thermal performance of SiC products, SiC diodes are able to provide lower overall system costs in a variety of diverse applications.









Package Types: TO-247-3 Marking: C6D16065

Features

- High-Frequency Operation
- Zero Reverse Recovery Current / Forward Recovery Voltage
- Temperature-Independent Switching Behavior
- Parallel Devices Without Thermal Runaway

Applications

- Boost Diodes in PFC or DC/DC Stages
- Free Wheeling Diodes in Inverter Stages
- Switch Mode Power Supplies
- Solar Inverters
- AC/DC Converters

Maximum Ratings (T_c = 25°C Unless Otherwise Specified)

* Per Leg, ** Per Device

Parameter	Symbol	Value	Unit	Test Conditions	Notes	
Repetitive Peak Reverse Voltage	V _{RRM}	650				
Surge Peak Reverse Voltage	V _{RSM}	650	V			
DC Blocking Voltage	V _{DC}	650				
		32*/64**		T _c = 25 °C		
Continuous Forward Current	I _F	16*/32**		T _c = 129 °C	Fig. 3	
		8*/16**		T _c = 157 °C		
Repetitive Peak Forward Surge		38*		$T_{c} = 25 ^{\circ}\text{C}, t_{p} = 10 \text{ms}, \text{Half Sine Wave}$		
Current	FRM	23*	Α	$T_{c} = 110 ^{\circ}\text{C}, t_{p} = 10 \text{ms}, \text{Half Sine Wave}$		
Non-Repetitive Forward Surge		69*		$T_c = 25 ^{\circ}\text{C}$, $t_p = 10 \text{ms}$, Half Sine Wave	F: 0	
Current	FSM	63*		$T_c = 110 ^{\circ}\text{C}$, $t_p = 10 \text{ms}$, Half Sine Wave	Fig. 8	
Non-Repetitive Peak Forward		860*		$T_c = 25 ^{\circ}\text{C}, t_p = 10 \mu\text{s}, \text{Pulse}$		
Surge Current	F,Max	790*		$T_{c} = 110 {}^{\circ}\text{C}, t_{p} = 10 \mu\text{s}, \text{Pulse}$		
Power Dissipation	_	100*		T _c = 25 °C		
	P _{tot}	43*	W	T _c = 110 °C	Fig. 4	

Electrical Characteristics

* Per Leg, ** Per Device

Parameter	Symbol	Тур.	Max.	Unit	Test Conditions	Notes
Forward Voltage	N.	1.27*	1.50*	V	I _F = 8 A, T _j = 25 °C	Fig. 1
	V _F	1.37*	1.60*		I _F = 8 A, T _j = 175 °C	
Reverse Current		2*	40*	μΑ	$V_R = 650 \text{ V}, T_j = 25 \text{ °C}$	Fig. 2
	I _R	15*	160*		V _R = 650 V, T _j = 175 °C	
Total Capacitive Charge	Q _c	29*		nC	$V_R = 400 \text{ V, T}_j = 25 ^{\circ}\text{C}$ $I_F = 8A, \text{ di/dt} = 500A/\mu\text{s}$	Fig. 5
		517*			$V_R = 0 \text{ V}, T_j = 25 \text{ °C}, f = 1 \text{ MHz}$	
Total Capacitance	С	56*		pF	$V_R = 200 \text{ V}, T_j = 25 \text{ °C}, f = 1 \text{ MHz}$	Fig. 6
		43*			$V_R = 400 \text{ V}, T_j = 25 \text{ °C}, f = 1 \text{ MHz}$	
Capacitance Stored Energy	E _c	4.3*		μJ	V _R = 400 V	Fig. 7

SiC Schottky Diodes are majority carrier devices, so there is no reverse recovery charge.

Thermal & Mechanical Characteristics

Parameter	Symbol	Value	Unit	Notes
Thermal Resistance, Junction to Case (Typical)	R _{0, JC (TYP)}	1.5** 0.75*	°C/W	
Junction Temperature	T _j	-55 to +175	0.0	
Case & Storage Temperature	T _c	-55 to +175	°C	
		1	Nm	M3 Screw
TO-247 Mounting Torque	-	8.8	lbf-in	6-32 Screw

^{*} Per Leg, ** Per Device

Typical Performance




Figure 1Forward Characteristics




Figure 2Reverse Characteristics




Figure 3Current Derating






Figure 4Power Derating


Typical Performance




Total Capacitance Charge vs. Reverse Voltage



Capacitance vs. Reverse Voltage



Capacitance Stored Energy



Non-Repetitive Peak Forward Surge Current vs. Pulse Duration





Figure 9 Transient Thermal Impedance


Package Dimensions & Pin-Out

Package: TO-247-3



Recommended Solder Pad Layout

Primary dimensions shown in mm.



Product Ordering Information

Order Number	Packing Type
C6D16065D	Tube

REACh, RoHS, and Halogen-Free compliance documentation available for this product.

Revision History

Document Version	Date of Release	Description of Changes
2	October- 2020	Initial Release
3	November-2023	Update Branding, POD, Package Image, Solder pad layout

Notes & Disclaimer

This document and the information contained herein are subject to change without notice. Any such change shall be evidenced by the publication of an updated version of this document by Wolfspeed. No communication from any employee or agent of Wolfspeed or any third party shall effect an amendment or modification of this document. No responsibility is assumed by Wolfspeed for any infringement of patents or other rights of third parties which may result from use of the information contained herein. No license is granted by implication or otherwise under any patent or patent rights of Wolfspeed.

Notwithstanding any application-specific information, guidance, assistance, or support that Wolfspeed may provide, the buyer of this product is solely responsible for determining the suitability of this product for the buyer's purposes, including without limitation for use in the applications identified in the next bullet point, and for the compliance of the buyers' products, including those that incorporate this product, with all applicable legal, regulatory, and safety-related requirements.

This product has not been designed or tested for use in, and is not intended for use in, applications in which failure of the product would reasonably be expected to cause death, personal injury, or property damage, including but not limited to equipment implanted into the human body, life-support machines, cardiac defibrillators, and similar emergency medical equipment, aircraft navigation, communication, and control systems, air craft power and propulsion systems, air traffic control systems, and equipment used in the planning, construction, maintenance, or operation of nuclear facilities.

RoHS Compliance

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS2), as implemented January 2, 2013. RoHS Declarations for this product can be obtained from your Wolfspeed representative or from the Product Documentation sections of www.wolfspeed. com.

REACh Compliance

REACh substances of high concern (SVHCs) information is available for this product. Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact your Wolfspeed representative to ensure you get the most up-to-date REACh SVHC Declaration. REACh banned substance information (REACh Article 67) is also available upon request.

Contact info:

4600 Silicon Drive Durham, NC 27703 USA Tel: +1.919.313.5300 www.wolfspeed.com/power

© 2023 Wolfspeed, Inc. All rights reserved. Wolfspeed® and the Wolfstreak logo are registered trademarks and the Wolfspeed logo is a trademark of Wolfspeed, Inc. PATENT: https://www.wolfspeed.com/legal/patents

The information in this document is subject to change without notice.