

Test Report

Applicant: Wolfspeed, Inc
 4600 Silicon Drive,
 Durham NC 27703
 USA

Number : TWNC01373046

Issue Date : Jul 01, 2025

Sample Description:


One (1) Group of Submitted Samples Said To Be :

Sample Description : Wolfspeed Materials SiC Uncoated Wafers
Style / Item No. : Wolfspeed Materials SiC Uncoated Wafers
Series No. : Wolfspeed Materials SiC Uncoated Wafers
Date Sample Received : Jun 17, 2025
Date Test Started : Jun 17, 2025

Test Conducted:


As requested by the applicant, for details please refer to attached pages.

Authorized By:
On behalf of Intertek Testing Services
Taiwan Limited


Matt Wang
General Manager



Signed by:


Thomas Chou
Manager



報告查詢 Report Verification



Page 1 of 14



Test Conducted :

Test Result Summary:

Test Result Summary:

Test Item	Unit	Test Method	Result	RL
			Submitted samples	
Heavy Metal				
Cadmium (Cd) Content (CAS No. : 7440-43-9)	ppm	As per applicant's request, the submitted samples were cut it into smaller pieces before test. With reference to IEC 62321-5: 2013, by microwave or acid digestion and determined by ICP-OES.	ND	2
Lead (Pb) Content (CAS No. : 7439-92-1)	ppm	As per applicant's request, the submitted samples were cut it into smaller pieces before test. With reference to IEC 62321-5: 2013, by microwave or acid digestion and determined by ICP-OES.	ND	2
Mercury (Hg) Content (CAS No. : 7439-97-6)	ppm	As per applicant's request, the submitted samples were cut it into smaller pieces before test. With reference to IEC 62321-4:2013+AMD1:2017, by microwave or acid digestion and determined by ICP-OES.	ND	2
Beryllium (Be) Content (CAS No. : 7440-41-7)	ppm	As per applicant's request, the submitted samples were cut it into smaller pieces before test. With reference to USEPA 3052, by microwave digestion and determined by ICP-OES.	ND	2
Antimony (Sb) Content (CAS No. : 7440-36-0)	ppm	As per applicant's request, the submitted samples were cut it into smaller pieces before test. With reference to USEPA 3052, by microwave digestion and determined by ICP-OES.	ND	2
Chromium VI (Cr(VI)) Content (CAS No. : 18540-29-9)	ppm	With reference to IEC 62321-7-2: 2017, organic solvent was used to dissolve or swell sample matrix, followed by alkaline digestion and determined by UV-Vis Spectrophotometer.	ND	8



Test Conducted :

Test Item	Unit	Test Method	Result	RL
			Submitted samples	
Polybrominated Biphenyls (PBBs)				
Monobrominated Biphenyls (MonoBB) (CAS No. : 26264-10-8)	ppm	With reference to IEC 62321-6: 2015, by solvent extraction and determined by GC-MS and further HPLC-DAD confirmation when necessary.	ND	5
Dibrominated Biphenyls (DiBB) (CAS No. : 27479-65-8)	ppm		ND	5
Tribrominated Biphenyls (TriBB) (CAS No. : 51202-79-0)	ppm		ND	5
Tetrabrominated Biphenyls (TetraBB) (CAS No. : 40088-45-7)	ppm		ND	5
Pentabrominated Biphenyls (PentaBB) (CAS No. : 56307-79-0)	ppm		ND	5
Hexabrominated Biphenyls (HexaBB) (CAS No. : 36355-01-8)	ppm		ND	5
Heptabrominated Biphenyls (HeptaBB) (CAS No. : 35194-78-6)	ppm		ND	5
Octabrominated Biphenyls (OctaBB) (CAS No. : 27858-07-7)	ppm		ND	5
Nonabrominated Biphenyls (NonaBB) (CAS No. : 27753-52-2)	ppm		ND	5
Decabrominated Biphenyl (DecaBB) (CAS No. : 13654-09-6)	ppm		ND	5



Test Conducted :

Test Item	Unit	Test Method	Result	RL
			Submitted samples	
Polybrominated Diphenyl Ethers (PBDEs)				
Monobrominated Diphenyl Ethers (MonoBDE) (CAS No. : 101-55-3)	ppm	With reference to IEC 62321-6: 2015, by solvent extraction and determined by GC-MS and further HPLC-DAD confirmation when necessary.	ND	5
Dibrominated Diphenyl Ethers (DiBDE) (CAS No. : 2050-47-7)	ppm		ND	5
Tribrominated Diphenyl Ethers (TriBDE) (CAS No. : 49690-94-0)	ppm		ND	5
Tetrabrominated Diphenyl Ethers (TetraBDE) (CAS No. : 40088-47-9)	ppm		ND	5
Pentabrominated Diphenyl Ethers (PentaBDE) (CAS No. : 32534-81-9)	ppm		ND	5
Hexabrominated Diphenyl Ethers (HexaBDE) (CAS No. : 36483-60-0)	ppm		ND	5
Heptabrominated Diphenyl Ethers (HeptaBDE) (CAS No. : 68928-80-3)	ppm		ND	5
Octabrominated Diphenyl Ethers (OctaBDE) (CAS No. : 32536-52-0)	ppm		ND	5
Nonabrominated Diphenyl Ethers (NonaBDE) (CAS No. : 63936-56-1)	ppm		ND	5
Decabrominated Diphenyl Ether (DecaBDE) (CAS No. : 1163-19-5)	ppm		ND	5
Phthalates				
Di(2-ethylhexyl) Phthalate (DEHP) (CAS No. : 117-81-7)	ppm	With reference to IEC 62321-8:2017, by solvent extraction and determined by GC-MS.	ND	50
Dibutyl Phthalate (DBP) (CAS No. : 84-74-2)	ppm		ND	50
Benzyl Butyl Phthalate (BBP) (CAS No. : 85-68-7)	ppm		ND	50
Diisobutyl Phthalate (DIBP) (CAS No. : 84-69-5)	ppm		ND	50



Test Conducted :

Test Item	Unit	Test Method	Result	RL
			Submitted samples	
Halogen Content				
Fluorine (F) (CAS No. : 7782-41-4)	ppm	With reference to EN 14582:2016 by combustion bomb with oxygen and determined by Ion Chromatography.	ND	50
Chlorine (Cl) (CAS No. : 7782-50-5)	ppm		ND	50
Bromine (Br) (CAS No. : 7726-95-6)	ppm		ND	50
Iodine (I) (CAS No. : 7553-56-2)	ppm		ND	50
Others				
Hexabromocyclododecane (HBCDD)	ppm	With reference to USEPA 3540C, by solvent extraction and determined by GC-MS.	ND	10
Perfluorooctane Sulfonates Including PFOS(CAS No. : 1763-23-1), PFOSA(CAS No. :754-91-6), N-Me-FOSA(CAS No. : 31506-32-8), N-Et-FOSA(CAS No. : 4151-50-2), N-Me-FOSE(CAS No. : 24448-09-7), N-Et-FOSE(CAS No. : 1691-99-2)	ppm	With reference to EN 17681-1:2022, by solvent extraction and determined by LC-MS-MS.	ND	0.01
Perfluorooctanoic Acid (PFOA) (CAS No. : 335-67-1)	ppm	With reference to EN 17681-1:2022, by solvent extraction and determined by LC-MS-MS.	ND	0.01

Remarks: ppm = Parts per million based on weight of tested sample = mg/kg
 ND = Not detected
 RL = Reporting limit, quantitation limit of analyte in sample

Responsibility of Chemist: Andy Yu/ Vita Fu

Date Sample Received : Jun 17, 2025
 Test Period : Jun 17, 2025 to Jun 26, 2025



Test Conducted :

RoHS Limit

<u>Restricted Substances</u>	<u>Limits</u>
Cadmium (Cd) content	0.01% (100ppm)
Lead (Pb) content	0.1% (1000ppm)
Mercury (Hg) content	0.1% (1000ppm)
Chromium VI (Cr(VI)) content	0.1% (1000ppm)
Polybrominated Biphenyls (PBBs)	0.1% (1000ppm)
Polybrominated Diphenyl Ethers (PBDEs)	0.1% (1000ppm)
Di(2-ethylhexyl) Phthalate (DEHP)	0.1% (1000ppm)
Dibutyl Phthalate (DBP)	0.1% (1000ppm)
Benzyl Butyl Phthalate (BBP)	0.1% (1000ppm)
Diisobutyl Phthalate (DIBP)	0.1% (1000ppm)

The limits were quoted from Annex II of 2011/65/EU and Amendment (EU) 2015/863 for homogeneous material.



Test Conducted :

Measurement Flowchart:


Test for Cd/Pb/Hg/Chromium (VI)/PBBs/PBDEs Content

Reference Standard : Cd/Pb: IEC 62321-5:2013; Hg: IEC 62321-4:2013+AMD1:2017;

Chromium (VI): IEC 62321-7-1:2015 (boiling water extraction);

Chromium (VI): IEC 62321-7-2:2017 (solvent and alkaline extraction);

PBBs/PBDEs: IEC 62321-6:2015



Test Conducted :

Remarks:

*1: List of Appropriate Acid :

Material	Acid Added for Digestion
Polymers	HNO ₃ , HCl, HF, H ₂ O ₂ , H ₃ BO ₃
Metals	HNO ₃ , HCl, HF
Electronics	HNO ₃ , HCl, H ₂ O ₂ , HBF ₄


*2: If sample solution is significantly more intense than 0.13 µg/cm² equivalent comparison standard, Chromium VI would be determined as detected, the result of visual observation is positive.



Test Conducted :

Measurement Flowchart:


Test for Heavy Metal (Sb,Be) Content
Reference Method : USEPA 3052



Test Conducted :

Measurement Flowchart:


Test for Phthalates Content
Reference Method: IEC 62321-8:2017



Test Conducted :

Measurement Flowchart:


Test for Halogen Content
Reference Standard : EN 14582:2016



Test Conducted :

Measurement Flowchart:


Test for Hexabromocyclododecane (HBCDD)
Reference Method : USEPA 3540C




Test Conducted :

Measurement Flowchart:

Test for Perfluorooctane Sulfonates (PFOS) / Perfluorooctanoic Acid (PFOA) Content
Reference Method : EN 17681-1:2022



Sample photo:



End of Report

Except where explicitly agreed in writing, all work and services performed by Intertek is subject to our standard Terms and Conditions which can be obtained at our website: <http://www.intertek-twn.com/terms/>. Intertek's responsibility and liability are limited to the terms and conditions of the agreement.

This report is made solely on the basis of your instructions and / or information and materials supplied by you and provide no warranty on the tested sample(s) be truly representative of the sample source. The report is not intended to be a recommendation for any particular course of action, you are responsible for acting as you see fit on the basis of the report results. Intertek is under no obligation to refer to or report upon any facts or circumstances which are outside the specific instructions received and accepts no responsibility to any parties whatsoever, following the issue of the report, for any matters arising outside the agreed scope of the works. This report does not discharge or release you from your legal obligations and duties to any other person. You are the only one authorized to permit copying or distribution of this report (and then only in its entirety). Any such third parties to whom this report may be circulated rely on the content of the report solely at their own risk

Reporting Statements of Conformity: Please note that the test results contain statement of conformity with the decision rules which are based on the specifications of customers, regulations and standards, and does not consider measurement uncertainty.

