


A3



2-R10 —



600 ± 0.3

35

50

32

.

A

$$400 \pm 0.3$$

32-M3 **T** 7.5

21 - M3 (A)

24-M47.5

2-06 Thru

.	2	A	B	C
---	---	---	---	---


50

C

2-R10

- 7 - M4 **T** | 0

- 1.The unmarked dimensions please follow the dimensions in the 3D file
- 2.The unmarked dimension tolerance please follow GB/T 1084-f
- 3.The unmarked Geometric tolerance please follow GB/T 1184-H
- 4.The surface of the part must be clean without oil, no scratches, damage and other general appearance defects
Metallic burrs or spikes are not allow

Product		Name		Type	
60kW		HEATSINK_60kW			
Design	xxx	Matieral		Projection	Drawing No.
Check	xxx				
technology	xxx				
Quality	xxx				
Standardization	xxx	Finish	Scale	Unit	Page 1 of 1
Approva	xxx		0.200	mm	