

C6D25170H

6th Generation 1700 V, 25 A Silicon Carbide Schottky Diode

Description

With the performance advantages of a Silicon Carbide (SiC) Schottky Barrier diode, power electronics systems can expect to meet higher efficiency standards than Si-based solutions, while also reaching higher frequencies and power densities. SiC diodes can be easily paralleled to meet various application demands, without concern of thermal runaway. In combination with the reduced cooling requirements and improved thermal performance of SiC products, SiC diodes are able to provide lower overall system costs in a variety of diverse applications.

Features

- Low Forward Voltage (V_F) Drop with Positive Temperature Coefficient
- Zero Reverse Recovery Current / Forward Recovery Voltage
- Temperature-Independent Switching Behavior

PIN 10 PIN 20 Package Types: T0-247-2 Marking: C6D25170H

Applications

- Industrial Switched Mode Power Supplies
- Uninterruptible & AUX Power Supplies
- Boost for PFC & DC-DC Stages
- Solar Inverters

Maximum Ratings ($T_c = 25^{\circ}C$ Unless Otherwise Specified)

Parameter	Symbol	Value	Unit	Test Conditions	Notes	
Repetitive Peak Reverse Voltage	V _{RRM}	1700	v			
DC Blocking Voltage	V _{DC}	1700	V			
		83		$T_c = 25 \text{ °C}$		
Continuous Forward Current	I _F	39	A	T _c = 135 °C	Fig. 3	
		29		T _c = 150 °C		
Repetitive Peak Forward Surge Current	I _{FRM}	131		$T_c = 25 \text{ °C}, t_p = 10 \text{ ms}, \text{Half Sine Wave}$		
		73		$T_c = 110 \text{ °C}, t_p = 10 \text{ ms}, \text{Half Sine Wave}$		
Non-Repetitive Peak Forward Surge Current	I _{FSM}	206		$T_c = 25 \text{ °C}, t_p = 10 \text{ ms}, \text{Half Sine Wave}$	Fig. 8	
		173		$T_c = 110 \text{ °C}, t_p = 10 \text{ ms}, \text{Half Sine Wave}$		
Power Dissipation	P _{tot}	375	W	$T_c = 25 \text{ °C}$	Fig. 4	
		162		T _c = 110 °C		
i²t Value	∫i²t	212	A ² s	$T_{c} = 25 \text{ °C}, t_{p} = 10 \text{ ms}$		
		149		$T_{c} = 110 \text{ °C}, t_{p} = 10 \text{ ms}$		

Rev. 0, November 2022

© 2022 Wolfspeed, Inc. All rights reserved. Wolfspeed[®] and the Wolfstreak logo are registered trademarks and the Wolfspeed logo is a trademark of Wolfspeed, Inc. The information in this document is subject to change without notice.



Electrical Characteristics

Parameter	Symbol	Тур.	Max.	Unit	Test Conditions	Notes	
Forward Voltage		1.45	1.7	V	I _F = 25 A, T _j = 25 °C	Fig. 1	
	V _F	2.0	2.8		I _F = 25 A, T _j = 175 °C	Fig. 1	
Reverse Current		10	45	μA	V _R = 1700 V, T _j = 25 °C	Fig. 2	
	I _R	60	225		V _R = 1700 V, T _j = 175 °C		
Total Capacitive Charge	Q _c	325		nC	V _R = 1700 V, T _j = 25 °C	Fig. 5	
Total Capacitance		3108		pF	$V_{R} = 0 V, T_{j} = 25 \text{ °C}, f = 1 \text{ MHz}$		
	С	135			$V_{R} = 800 \text{ V}, \text{ T}_{j} = 25 \text{ °C}, \text{ f} = 1 \text{ MHz}$	Fig. 6	
		133			$V_{R} = 1700 \text{ V}, \text{ T}_{j} = 25 \text{ °C}, \text{ f} = 1 \text{ MHz}$		
Capacitance Stored Energy	E _c	203		μJ	V _R = 1700 V	Fig. 7	

Notes:

SiC Schottky Diodes are majority carrier devices, so there is no reverse recovery charge.


Thermal & Mechanical Characteristics

Parameter	Symbol	Value	Unit	Notes
Thermal Resistance, Junction to Case (Typical)	R _{0, JC (TYP)}	0.26	8C (M)	
Thermal Resistance, Junction to Case (Maximum)	R _{0, JC (MAX)}	0.4	− °C / W	
Junction Temperature	T _j	-55 to +175	°C	
Case & Storage Temperature	T _c	-55 to +150		
TO 247 Mounting Toursus		1	Nm	M3 Screw
TO-247 Mounting Torque	-	8.8	lbf-in	6-32 Screw

Rev. 0, November 2022



Typical Performance




Rev. 0, November 2022

4600 Silicon Drive | Durham, NC 27703 | Tel: +1.919.313.5300 | wolfspeed.com/power

© 2022 Wolfspeed, Inc. All rights reserved. Wolfspeed® and the Wolfstreak logo are registered trademarks and the Wolfspeed logo is a trademark of Wolfspeed, Inc. The information in this document is subject to change without notice.



Typical Performance



Capacitance Stored Energy


Transient Thermal Impedance

Rev. 0, November 2022



Package Dimensions & Pin-Out

Package: TO-247-2 (All dimensions are in mm)




Rev. 0, November 2022

4600 Silicon Drive | Durham, NC 27703 | Tel: +1.919.313.5300 | wolfspeed.com/power

© 2022 Wolfspeed, Inc. All rights reserved. Wolfspeed® and the Wolfstreak logo are registered trademarks and the Wolfspeed logo is a trademark of Wolfspeed, Inc. The information in this document is subject to change without notice.



Recommended Solder Pad Layout Package: TO-247-2 (All dimensions are in mm)



Product Ordering Information

Order Number	Packing Type
C6D25170H	Tube

REACh, RoHS, and Halogen-Free compliance documentation available for this product.

Rev. 0, November 2022

© 2022 Wolfspeed, Inc. All rights reserved. Wolfspeed® and the Wolfstreak logo are registered trademarks and the Wolfspeed logo is a trademark of Wolfspeed, Inc. The information in this document is subject to change without notice.



Revision History

Document Version	Date of Release	Description of changes
0	November-2022	Initial datasheet

Rev. 0, November 2022

© 2022 Wolfspeed, Inc. All rights reserved. Wolfspeed[®] and the Wolfstreak logo are registered trademarks and the Wolfspeed logo is a trademark of Wolfspeed, Inc. The information in this document is subject to change without notice.



Notes & Disclaimer

This document and the information contained herein are subject to change without notice. Any such change shall be evidenced by the publication of an updated version of this document by Wolfspeed. No communication from any employee or agent of Wolfspeed or any third party shall effect an amendment or modification of this document. No responsibility is assumed by Wolfspeed for any infringement of patents or other rights of third parties which may result from use of the information contained herein. No license is granted by implication or otherwise under any patent or patent rights of Wolfspeed.

Notwithstanding any application-specific information, guidance, assistance, or support that Wolfspeed may provide, the buyer of this product is solely responsible for determining the suitability of this product for the buyer's purposes, including without limitation for use in the applications identified in the next bullet point, and for the compliance of the buyers' products, including those that incorporate this product, with all applicable legal, regulatory, and safety-related requirements.

This product has not been designed or tested for use in, and is not intended for use in, applications in which failure of the product would reasonably be expected to cause death, personal injury, or property damage, including but not limited to equipment implanted into the human body, life-support machines, cardiac defibrillators, and similar emergency medical equipment, aircraft navigation, communication, and control systems, aircraft power and propulsion systems, air traffic control systems, and equipment used in the planning, construction, maintenance, or operation of nuclear facilities.

RoHS Compliance

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS2), as implemented January 2, 2013. RoHS Declarations for this product can be obtained from your Wolfspeed representative or from the Product Documentation sections of www.wolfspeed. com.

REACh Compliance

REACh substances of high concern (SVHCs) information is available for this product. Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact your Wolfspeed representative to ensure you get the most up-to-date REACh SVHC Declaration. REACh banned substance information (REACh Article 67) is also available upon request.

Contact info:

4600 Silicon Drive Durham, NC 27703 USA Tel: +1.919.313.5300 www.wolfspeed.com/power

© 2022 Wolfspeed, Inc. All rights reserved. Wolfspeed® and the Wolfstreak logo are registered trademarks and the Wolfspeed logo is a trademark of Wolfspeed, Inc. PATENT: https://www.wolfspeed.com/legal/patents

The information in this document is subject to change without notice.