

DPG10 Power Choke Tester

D.U.T.: MAG-3000764


Inspector:

Date: 2022/5/17

'Maximalstrom [A]': 60

'Meßspannung [V]': 60

'Impulsdauer [µs]': 1000 (435)



I [A]	L_inc [µH]	I [A]	L_inc [µH]	I [A]	L_inc [µH]	I [A]	L_inc [µH]	I [A]	L_inc [µH]
		21	501	41	269				
2	730	22	486	42	261				
3	722	23	472	43	253				
4	717	24	458	44	246				
5	714	25	444	45	238				
6	704	26	431	46	230				
7	693	27	418	47	223				
8	681	28	406	48	216				
9	672	29	394	49	209				
10	661	30	382	50	203				
11	649	31	370	51	197				
12	637	32	359	52	191				
13	623	33	347	53	185				
14	608	34	338	54	180				
15	591	35	327	55	174				
16	576	36	317	56	169				
17	562	37	306	57	164				
18	546	38	296	58	159				
19	530	39	287	59	155				
20	516	40	277	60	150				

Remarks:

Customer spec: TBD Ts 500uH Min@25A

Bourns spec: 58Ts 444uH@25A