

C3D08065A


3rd Generation 650 V, 8 A Silicon Carbide Schottky

Description

With the performance advantages of a Silicon Carbide (SiC) Schottky Barrier diode, power electronics systems can expect to meet higher efficiency standards than Si-based solutions, while also reaching higher frequencies and power densities. SiC diodes can be easily paralleled to meet various application demands, without concern of thermal runaway. In combination with the reduced cooling requirements and improved thermal performance of SiC products, SiC diodes are able to provide lower overall system costs in a variety of diverse applications.

Features

- Low Forward Voltage $(V_{\rm F})$ Drop with Positive Temperature Coefficient
- Zero Reverse Recovery Current / Forward Recovery Voltage
- Temperature-Independent Switching Behavior



Package Types: TO-220-2 Marking: C3D08065A

Applications

- Industrial Switched Mode Power Supplies
- Uninterruptible & AUX Power Supplies
- Boost for PFC & DC-DC Stages
- Solar Inverters

Maximum Ratings ($T_c = 25^{\circ}C$ Unless Otherwise Specified)

Parameter	Symbol	Value	Unit	Test Conditions	Notes	
Repetitive Peak Reverse Voltage	V _{RRM}	650				
DC Blocking Voltage	V _{DC}	650	V			
		24		T _J = 25 °C		
Continuous Forward Current	I _F	11		T _J = 135 °C	Fig. 3	
		8	A	T _j = 152 °C		
Repetitive Peak Forward Surge Current	I _{FRM}	37.5		$T_c = 25 \text{ °C}, t_p = 10 \text{ ms}, \text{ Half Sine Wave}$		
		25.5		$T_c = 110 \text{ °C}, t_p = 10 \text{ ms}, \text{Half Sine Wave}$		
Non-Repetitive Forward Surge		71		$T_c = 25 \text{ °C}, t_p = 10 \text{ ms}, \text{ Half Sine Wave}$	=: 0	
Current	FSM	60		$T_c = 110 \text{ °C,} t_p = 10 \text{ ms, Half Sine Wave}$	Fig. 8	
Non-Repetitive Peak Forward	_	650		$T_c = 25 ^{\circ}C, t_p = 10 \mu s, Pulse$		
Surge Current	F,Max	530		$T_{c} = 110^{\circ}C, t_{p} = 10 \mu s, Pulse$		
Power Dissipation	P _{tot}	107		T, = 25 °C	Fig. 4	
		46.5	W	T ₁ = 110 °C		

Rev. 6, March 2023



Electrical Characteristics

Parameter	Symbol	Тур.	Max.	Unit	Test Conditions	Notes
Family of the sec		1.5	1.8		I _F = 8 A, T _j = 25 °C	- Fi- 1
Forward Voltage	V _F	2.1	2.4	V	I _F = 8 A, T _j = 175 °C	Fig. 1
Reverse Current		10	51	μA	V _R = 650 V, T _j = 25 °C	Fig. 2
	I _R	12	204		V _R = 650 V, T _j = 175 °C	
Total Capacitive Charge	Q _c	20		nC	V _R = 650 V, T _j = 25 °C	Fig. 5
		395			$V_{R} = 0 V, T_{j} = 25 °C, f = 1 MHz$	
Total Capacitance	С	37		pF	$V_{R} = 200 \text{ V}, \text{ T}_{j} = 25 \text{ °C}, \text{ f} = 1 \text{ MHz}$	Fig. 6
		32			$V_{R} = 400 \text{ V}, \text{ T}_{j} = 25 \text{ °C}, \text{ f} = 1 \text{ MHz}$	
Capacitance Stored Energy	E _c	3.0		μJ	V _R = 400 V	Fig. 7

Notes:

SiC Schottky Diodes are majority carrier devices, so there is no reverse recovery charge.

Thermal & Mechanical Characteristics

Parameter	Symbol	Value	Unit	Notes
Thermal Resistance, Junction to Case (Typical)	R _{0, JC (TYP)}	1.4	°C / W	
Junction Temperature	T _j	-55 to +175		
Case & Storage Temperature	T _c	-55 to +175	- °C	
		1	Nm	M3 Screw
TO-220 Mounting Torque	-	8.8	lbf-in	6-32 Screw

Electrostatic Discharge (ESD) Classifications

Parameter	Symbol	Notes
Human Body Model	НВМ	Class 3B (≥ 8000 V)
Charge Device Model	CDM	Class C3 (≥ 1000 V)

Typical Performance




Figure 1 Forward Characteristics




Figure 2 Reverse Characteristics




Figure 3 Current Derating




Figure 4 Power Derating

3

Rev. 6, March 2023




Figure 5 Total Capacitance vs. Reverse Voltage




Figure 6 Capacitace vs. Reverse Voltage




Figure 7 Capacitance Stored Energy






Figure 8

Non-Repetitive Peak Forward Surge Current versus Pulse Duration (sinusoidal waveform)


Rev. 6, March 2023

4600 Silicon Drive | Durham, NC 27703 | Tel: +1.919.313.5300 | wolfspeed.com/power





Diode Model



 $Vf_T = V_T + If * R_T$

$$V_{T} = 0.95 + (T_{J} * -1.2 * 10^{-3})$$

 $R_{T} = 0.054 + (T_{J} * 5.5 * 10^{-4})$


Note: T_j = Diode Junction Temperature In Degrees Celsius, valid from 25°C to 175°C 5

Rev. 6, March 2023

4600 Silicon Drive | Durham, NC 27703 | Tel: +1.919.313.5300 | wolfspeed.com/power

Package Dimensions & Pin-Out

Package: TO-220-2



6

Rev. 6, March 2023


4600 Silicon Drive | Durham, NC 27703 | Tel: +1.919.313.5300 | wolfspeed.com/power





Recommended Solder Pad Layout

Primary dimensions shown in mm. Learn more about recommended soldering profiles in <u>this application note.</u>



Product Ordering Information

Order Number	Packing Type
C3D08065A	Tube

Learn more about power device packing & shipment information in this application note.

Rev. 6, March 2023



Revision History

Document Version	Date of Release	Description of Changes	
1	December-2015	Initial Release	
6	March-2023	Update Package Drawing Update Landing Pad	



Notes & Disclaimer

This document and the information contained herein are subject to change without notice. Any such change shall be evidenced by the publication of an updated version of this document by Wolfspeed. No communication from any employee or agent of Wolfspeed or any third party shall effect an amendment or modification of this document. No responsibility is assumed by Wolfspeed for any infringement of patents or other rights of third parties which may result from use of the information contained herein. No license is granted by implication or otherwise under any patent or patent rights of Wolfspeed.

Notwithstanding any application-specific information, guidance, assistance, or support that Wolfspeed may provide, the buyer of this product is solely responsible for determining the suitability of this product for the buyer's purposes, including without limitation for use in the applications identified in the next bullet point, and for the compliance of the buyers' products, including those that incorporate this product, with all applicable legal, regulatory, and safety-related requirements.

This product has not been designed or tested for use in, and is not intended for use in, applications in which failure of the product would reasonably be expected to cause death, personal injury, or property damage, including but not limited to equipment implanted into the human body, life-support machines, cardiac defibrillators, and similar emergency medical equipment, aircraft navigation, communication, and control systems, aircraft power and propulsion systems, air traffic control systems, and equipment used in the planning, construction, maintenance, or operation of nuclear facilities.

RoHS Compliance

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS2), as implemented January 2, 2013. RoHS Declarations for this product can be obtained from your Wolfspeed representative or from the Product Documentation sections of www.wolfspeed. com.

REACh Compliance

REACh substances of high concern (SVHCs) information is available for this product. Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact your Wolfspeed representative to ensure you get the most up-to-date REACh SVHC Declaration. REACh banned substance information (REACh Article 67) is also available upon request.

Contact info:

4600 Silicon Drive Durham, NC 27703 USA Tel: +1.919.313.5300 www.wolfspeed.com/power

© 2022 Wolfspeed, Inc. All rights reserved. Wolfspeed® and the Wolfstreak logo are registered trademarks and the Wolfspeed logo is a trademark of Wolfspeed, Inc. PATENT: https://www.wolfspeed.com/legal/patents

The information in this document is subject to change without notice.

Rev. 6, March 2023