

Silicon Carbide Power MOSFET

C3M™ MOSFET Technology

N-Channel Enhancement Mode

Features

- 3rd generation SiC MOSFET technology
- Optimized package with separate driver source pin
- High blocking voltage with low on-resistance
- High-speed switching with low capacitances
- Fast intrinsic diode with low reverse recovery (Q,,)
- Halogen free, RoHS compliant

Benefits

- Reduce switching losses and minimize gate ringing
- Higher system efficiency
- Reduce cooling requirements
- Increase power density
- Increase system switching frequency

Applications

- Datacenter Power Supplies
- Telecom Power Supplies
- Energy Storage Systems
- Solar (PV) inverters
- High Voltage DC/DC converters

Maximum Ratings (T_c = 25 °C unless otherwise specified)

Package

Drain Tab







12345678

	(Т	AB)
Gate (Pin 1)		
	Driver Source (Pin 2)	Power Source (Pin 3,4,5,6,7,8)

Orderable Part Number		Package	Marking	
	C3M0025065L-TR	TOLL	C3M0025065L	

Wolfspeed, Inc. is in the process of rebranding its products and related materials pursuant to the entity name change from Cree, Inc. to Wolfspeed, Inc. During this transition period, products received may be marked with either the Cree name and/or logo or the Wolfspeed name and/or logo.

Symbol	Parameter	Value	Unit	Note	
V _{DSmax}	Drain - Source Voltage		650	٧	
V_{GSmax}	Gate - Source Voltage		-8/+19	٧	Note: 1
		T _C = 25°C	77		Fig. 19 Note: 2
I _D	Continuous Drain Current, V _{GS} = 15 V	T _C = 100°C	59	A	
I _{D(pulse)}	Pulsed Drain Current, Pulse width t _P limited by T _{jmax}	235	Α	Fig. 22	
P _D	Power Dissipation, T _c =25°C, T _J = 175 °C	326	W	Fig. 20 Note: 2	
T _J	Junction Temperature	-40 to +175	°C		
T_{C} , T_{stg}	Case Temperature and Storage Temperature	-40 to +175	°C		
T _L	Solder Temperature (According to JEDEC J-STD-020)	260	°C		

Note (1): Recommended turn off / turn on gate voltage $V_{\rm GS}$ - 4V...0V / +15V

Note (2): Verified by design

Electrical Characteristics (T_c = 25°C unless otherwise specified)

Symbol	Parameter	Min.	Тур.	Max.	Unit	Test Conditions	Note	
$V_{(BR)DSS}$	Drain-Source Breakdown Voltage	650			٧	V _{GS} = 0 V, I _D = 100 μA		
.,	Gate Threshold Voltage	1.8	2.3	3.6	٧	V _{DS} = V _{GS} , I _D = 9.22 mA	Fig. 11	
$V_{\text{GS(th)}}$			1.9		٧	V _{DS} = V _{GS} , I _D = 9.22 mA, T _J = 175°C		
I _{DSS}	Zero Gate Voltage Drain Current		1	50	μA	V _{DS} = 650 V, V _{GS} = 0 V		
I_{GSS}	Gate-Source Leakage Current		10	250	nA	V _{GS} = 15 V, V _{DS} = 0 V		
D			25	34		V _{GS} = 15 V, I _D = 33.5 A	Fig. 4,	
R _{DS(on)}	Drain-Source On-State Resistance		33		mΩ	V _{GS} = 15 V, I _D = 33.5 A, T _J = 175°C	5, 6	
_	Transcanductors		24			V _{DS} = 20 V, I _{DS} = 33.5 A		
g _{fs}	Transconductance		23		S	V _{DS} = 20 V, I _{DS} = 33.5 A, T _J = 175°C	Fig. 7	
C_{iss}	Input Capacitance		2970			V _{GS} = 0 V, V _{DS} = 400 V	Fig. 17,	
C_{oss}	Output Capacitance		186		pF	f = 1 Mhz		
C_{rss}	Reverse Transfer Capacitance		11			Vac = 25 mV		
E _{oss}	C _{oss} Stored Energy		18		μJ	V _{DS} = 400 V, f = 1 Mhz		
$C_{o(er)}$	Effective Output Capacitance (Energy Related)		226		pF			
$C_{o(tr)}$	Effective Output Capacitance (Time Related)		322		pF	V _{GS} = 0 V, V _{DS} = 0 400V	Note: 3	
Eon	Turn-On Switching Energy (Body Diode FWD)		123			$V_{DS} = 400 \text{ V}, V_{GS} = -4 \text{ V}/15 \text{ V}, I_{D} = 33.5 \text{A},$	Fig. 23	
E _{OFF}	Turn-Off Switching Energy (Body Diode FWD)		14		μJ	$R_{G(ext)} = 2.5 \Omega$, L= 59 μ H, $T_J = 25^{\circ}$ C FWD = Internal Body Diode		
$t_{\text{d(on)}} \\$	Turn-On Delay Time		10					
t _r	Rise Time		13			$V_{DD} = 400 \text{ V}, V_{GS} = -4 \text{ V}/15 \text{ V}$ $I_D = 33.5 \text{ A}, R_{G(ext)} = 2.5 \Omega,$	Fig. 26	
t _{d(off)}	Turn-Off Delay Time		26		ns	Timing relative to V _{DS}		
t _f	Fall Time		8			inductive load		
R _{G(int)}	Internal Gate Resistance		1.3		Ω	f = 1 MHz, V _{AC} = 25 mV		
Q_{gs}	Gate to Source Charge		33			V _{DS} = 400 V, V _{GS} = -4 V/15 V		
Q_{gd}	Gate to Drain Charge		32		nC	I _D = 33.5 A	Fig. 12	
Qg	Total Gate Charge		111			Per IEC60747-8-4 pg 21		


Note (3): $C_{o(er)}$, a lumped capacitance that gives same stored energy as Coss while Vds is rising from 0 to 400V $C_{o(tr)}$, a lumped capacitance that gives same charging time as Coss while Vds is rising from 0 to 400V

Reverse Diode Characteristics ($T_c = 25^{\circ}C$ unless otherwise specified)

Symbol	Parameter	Тур.	Max.	Unit	Test Conditions	Note
.,	Diode Forward Voltage	5.0		V	V _{GS} = -4 V, I _{SD} = 16.8 A, T _J = 25 °C	Fig. 8, 9, 10
V_{SD}		4.4		V	V _{GS} = -4 V, I _{SD} = 16.8 A, T _J = 175 °C	
Is	Continuous Diode Forward Current		54	А	V _{GS} = -4 V, T _C = 25°C	
I _{S, pulse}	Diode pulse Current		235	А	$V_{GS} = -4 \text{ V}$, pulse width t_P limited by T_{jmax}	
t _{rr}	Reverse Recover time	14		ns		
Q _{rr}	Reverse Recovery Charge	338		nC	V _{GS} = -4 V, I _{SD} = 33.5 A, V _R = 400 V dif/dt = 4717 A/μs, Τ _ι = 25 °C	
I _{rrm}	Peak Reverse Recovery Current	40		А		
t _{rr}	Reverse Recover time	16		ns		
Q _{rr}	Reverse Recovery Charge	164		nC $V_{GS} = -4 \text{ V, } I_{SD} = 33.5 \text{ A, } V_{R} = 400 \text{ V}$ dif/dt = 2137 A/ μ s, T, = 25 °C		
I	Peak Reverse Recovery Current	17		А	α από το επό	

Thermal Characteristics

Symbol	Parameter	Тур.	Max.	Unit	Note
$R_{\theta JC}$	Thermal Resistance from Junction to Case	0.41	0.46	°C/W	







Figure 1. Output Characteristics T_J = -40 °C

Figure 2. Output Characteristics $T_J = 25$ °C







Figure 3. Output Characteristics T_J = 175 °C

Figure 4. Normalized On-Resistance vs. Temperature







Figure 5. On-Resistance vs. Drain Current For Various Temperatures

Figure 6. On-Resistance vs. Temperature For Various Gate Voltage

5








Figure 7. Transfer Characteristic for Various Junction Temperatures









Figure 9. Body Diode Characteristic at 25 °C

Figure 10. Body Diode Characteristic at 175 °C







Figure 11. Threshold Voltage vs. Temperature

Figure 12. Gate Charge Characteristics








Figure 13. 3rd Quadrant Characteristic at -40 °C









Figure 15. 3rd Quadrant Characteristic at 175 °C

Figure 16. Output Capacitor Stored Energy







Figure 17. Capacitances vs. Drain-Source Voltage (0 - 200V)

Figure 18. Capacitances vs. Drain-Source Voltage (0 - 650V)







Figure 19. Continuous Drain Current Derating vs.

Case Temperature

Figure 20. Maximum Power Dissipation Derating vs.

Case Temperature







Figure 21. Transient Thermal Impedance (Junction - Case)

Figure 22. Safe Operating Area






Figure 23. Clamped Inductive Switching Energy vs. Drain Current $(V_{DD} = 400V)$

Figure 24. Clamped Inductive Switching Energy vs. R_{G(ext)}




Figure 25. Clamped Inductive Switching Energy vs.
Temperature




Figure 27. Switching Times Definition




Figure 26. Switching Times vs. $R_{G(ext)}$

9

Test Circuit Schematic






Figure 28. Clamped Inductive Switching Waveform Test Circuit

Package Dimensions



Recommended Solder Pad Layout

(Note: All Dimensions are listed in Millimeters)



Revision history

Document Version	Date of release	Description of changes
1	October-2022	Initial datasheet

Notes & Disclaimer

This document and the information contained herein are subject to change without notice. Any such change shall be evidenced by the publication of an updated version of this document by Wolfspeed. No communication from any employee or agent of Wolfspeed or any third party shall effect an amendment or modification of this document. No responsibility is assumed by Wolfspeed for any infringement of patents or other rights of third parties which may result from use of the information contained herein. No license is granted by implication or otherwise under any patent or patent rights of Wolfspeed.

Notwithstanding any application-specific information, guidance, assistance, or support that Wolfspeed may provide, the buyer of this product is solely responsible for determining the suitability of this product for the buyer's purposes, including without limitation for use in the applications identified in the next bullet point, and for the compliance of the buyers' products, including those that incorporate this product, with all applicable legal, regulatory, and safety-related requirements.

This product has not been designed or tested for use in, and is not intended for use in, applications in which failure of the product would reasonably be expected to cause death, personal injury, or property damage, including but not limited to equipment implanted into the human body, life-support machines, cardiac defibrillators, and similar emergency medical equipment, aircraft navigation, communication, and control systems, air craft power and propulsion systems, air traffic control systems, and equipment used in the planning, construction, maintenance, or operation of nuclear facilities.

RoHS Compliance

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS2), as implemented January 2, 2013. RoHS Declarations for this product can be obtained from your Wolfspeed representative or from the Product Documentation sections of www.wolfspeed. com.

REACh Compliance

REACh substances of high concern (SVHCs) information is available for this product. Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact your Wolfspeed representative to ensure you get the most up-to-date REACh SVHC Declaration. REACh banned substance information (REACh Article 67) is also available upon request.

Contact info:

4600 Silicon Drive Durham, NC 27703 USA Tel: +1.919.313.5300 www.wolfspeed.com/power

© 2023 Wolfspeed, Inc. All rights reserved. Wolfspeed® and the Wolfstreak logo are registered trademarks and the Wolfspeed logo is a trademark of Wolfspeed, Inc. PATENT: https://www.wolfspeed.com/legal/patents

The information in this document is subject to change without notice.