

## 650 V, 10 A Silicon Carbide Schottky Diode

### **Description**


With the performance advantages of a Silicon Carbide (SiC) Schottky Barrier diode, power electronics systems can expect to meet higher efficiency standards than Si-based solutions, while also reaching higher frequencies and power densities. SiC diodes can be easily paralleled to meet various application demands, without concern of thermal runaway. In combination with the reduced cooling requirements and improved thermal performance of SiC products, SiC diodes are able to provide lower overall system costs in a variety of diverse applications.







TO-263-2



Package Types: TO-263-2 PN: C6D10065G

Wolfspeed, Inc. is in the process of rebranding its products and related materials pursuant to the entity name change from Cree, Inc. to Wolfspeed, Inc. During this transition period, products received may be marked with either the Cree name and/or logo or the Wolfspeed name and/or logo.

## **Applications**

- Industrial power supplies
- Switch mode power supplies
- Server/telecom power supplies
- Power factor correction
- Solar inverter
- Uninterruptible power supply

### **Features**

- Low forward voltage (V<sub>F</sub>) drop with positive temperature coefficient
- Zero reverse recovery current/forward recovery voltage
- Temperature-independent switching behavior
- Low leakage current (I<sub>R</sub>)

## **Maximum Ratings** (T<sub>c</sub> = 25 °C Unless Otherwise Specified)

Parameter	Symbol	Value	Unit	Test Conditions	Note
Repetitive Peak Reverse Voltage	V <sub>RRM</sub>	650	V		
DC Blocking Voltage	V <sub>DC</sub>	650	V		
Continuous Forward Current	I <sub>F</sub>	36	A	T <sub>c</sub> = 25 °C	Fig. 3
		18		T <sub>C</sub> = 125 °C	
		10		T <sub>c</sub> = 155 °C	
	I <sub>FRM</sub>	39		T <sub>C</sub> = 25 °C, t <sub>P</sub> = 10 ms, Half Sine Wave	
Repetitive Peak Forward Surge Current		22		T <sub>c</sub> = 110 °C, t <sub>p</sub> = 10 ms, Half Sine Wave	
Non-Repetitive Peak Forward Surge Current	I <sub>FSM</sub>	80		T <sub>C</sub> = 25 °C, t <sub>P</sub> = 10 ms, Half Sine Wave	Fig. 8
		68		T <sub>c</sub> = 110 °C, t <sub>p</sub> = 10 ms, Half Sine Wave	
	I <sub>F, Max</sub>	1020		$T_C = 25 ^{\circ}\text{C}, t_P = 10 \mu\text{s}, \text{Pulse}$	
		F, Max	960		T <sub>C</sub> = 110 °C, t <sub>P</sub> = 10 μs, Pulse
Power Dissipation	P <sub>tot</sub>	108	W	T <sub>c</sub> = 25 °C	Fig. 4
		47		T <sub>C</sub> = 110 °C	

### **Electrical Characteristics**

Parameter	Symbol	Тур.	Max.	Unit	Test Conditions	Note
- IV I	.,	1.27	1.40	V	I <sub>F</sub> = 10 A, T <sub>J</sub> = 25 °C	Fig. 1
Forward Voltage	V <sub>F</sub>	1.37	1.50		I <sub>F</sub> = 10 A, T <sub>J</sub> = 175 °C	
Reverse Current	2 20		V <sub>R</sub> = 650 V, T <sub>J</sub> = 25 °C	Fig. 2		
Reverse Current	I <sub>R</sub>	12	200	μΑ	V <sub>R</sub> = 650 V, T <sub>J</sub> = 175 °C	Fig. 2
Total Capacitive Charge	Q <sub>c</sub>	34		nC	V <sub>R</sub> = 400 V, T <sub>J</sub> = 25 °C	Fig. 5
		611			V <sub>R</sub> = 0 V, T <sub>J</sub> = 25 °C, f = 1 MHz	
Total Capacitance C	С	67		pF	V <sub>R</sub> = 200 V, T <sub>J</sub> = 25 °C, f = 1 MHz	Fig. 6
		53			V <sub>R</sub> = 400 V, T <sub>J</sub> = 25 °C, f = 1 MHz	
Capacitance Stored Energy	E <sub>c</sub>	5.2		μJ	V <sub>R</sub> = 400 V	Fig. 7

Note: SiC Schottky Diodes are majority carrier devices, so there is no reverse recovery charge.

### **Thermal & Mechanical Characteristics**

Parameter	Symbol	Тур.	Unit	Note
Thermal Resistance, Junction to Case	$R_{\theta, JC}$	1.38	°C/W	
Operating Junction & Storage Temperature	$T_{J}, T_{stg}$	-55 to +175	°C	Fig. 9

## **Typical Performance**





Figure 1. Forward Characteristics



2

Figure 2. Reverse Characteristics

### **Typical Performance**




Figure 3. Current Derating




Figure 4. Power Derating




Figure 5. Total Capacitance Charge vs. Reverse Voltage




Figure 6. Capacitance vs. Reverse Voltage

# 4

## **Typical Performance**




Figure 7. Capacitance Stored Energy




Figure 8. Non-Repetitive Peak Forward Surge Current (Sine Wave)






Figure 9. Transient Thermal Impedance

## **Package Dimensions**

Package: TO-263-2







Part Number	Package	Marking
C6D10065G	TO-263-2	C6D10065

## **Electrostatic Discharge (ESD) Classifications**

Parameter	Symbol	Class
Human Body Model	НВМ	Class 3B (≥ 8000 V)
Charge Device Model	CDM	Class C3 (≥ 1000 V)

## **Revision History**

<b>Document Version</b>	Date of Release	Description of Changes
0	July-2021	Initial Release
1	October-2023	Updated Wolfspeed branding, package drawing, and solder pad layout (Not Released)
2	November-2023	Corrected Package Drawing L and L1

### Notes & Disclaimer

This document and the information contained herein are subject to change without notice. Any such change shall be evidenced by the publication of an updated version of this document by Wolfspeed. No communication from any employee or agent of Wolfspeed or any third party shall effect an amendment or modification of this document. No responsibility is assumed by Wolfspeed for any infringement of patents or other rights of third parties which may result from use of the information contained herein. No license is granted by implication or otherwise under any patent or patent rights of Wolfspeed.

Notwithstanding any application-specific information, guidance, assistance, or support that Wolfspeed may provide, the buyer of this product is solely responsible for determining the suitability of this product for the buyer's purposes, including without limitation for use in the applications identified in the next bullet point, and for the compliance of the buyers' products, including those that incorporate this product, with all applicable legal, regulatory, and safety-related requirements.

This product has not been designed or tested for use in, and is not intended for use in, applications in which failure of the product would reasonably be expected to cause death, personal injury, or property damage, including but not limited to equipment implanted into the human body, life-support machines, cardiac defibrillators, and similar emergency medical equipment, aircraft navigation, communication, and control systems, aircraft power and propulsion systems, air traffic control systems, and equipment used in the planning, construction, maintenance, or operation of nuclear facilities.

### **RoHS Compliance**

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS2), as implemented January 2, 2013. RoHS Declarations for this product can be obtained from your Wolfspeed representative or from the Product Documentation sections of <a href="https://www.wolfspeed.com">www.wolfspeed.com</a>.

### **REACh Compliance**

REACh substances of high concern (SVHCs) information is available for this product. Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact your Wolfspeed representative to ensure you get the most up-to-date REACh SVHC Declaration. REACh banned substance information (REACh Article 67) is also available upon request.

#### **Contact info:**

4600 Silicon Drive Durham, NC 27703 USA Tel: +1.919.313.5300 www.wolfspeed.com/power

© 2023 Wolfspeed, Inc. All rights reserved. Wolfspeed® and the Wolfstreak logo are registered trademarks and the Wolfspeed logo is a trademark of Wolfspeed, Inc. PATENT: https://www.wolfspeed.com/legal/patents

The information in this document is subject to change without notice.