


4th Generation 1200 V, 40 A Silicon Carbide Schottky Diode

Description

With the performance advantages of a Silicon Carbide (SiC) Schottky Barrier diode, power electronics systems can expect to meet higher efficiency standards than Si-based solutions, while also reaching higher frequencies and power densities. SiC diodes can be easily paralleled to meet various application demands, without concern of thermal runaway. In combination with the reduced cooling requirements and improved thermal performance of SiC products, SiC diodes are able to provide lower overall system costs in a variety of diverse applications.





Wolfspeed, Inc. is in the process of rebranding its products and related materials pursuant to the entity name change from Cree, Inc. to Wolfspeed, Inc. During this transition period, products received may be marked with either the Cree name and/or logo or the Wolfspeed name and/or logo.

Part Number	Package	Marking	
C4D40120H	TO-247-2	C4D40120H	

Features

- Low Forward Voltage (V_F) Drop with Positive **Temperature Coefficient**
- Zero Reverse Recovery Current / Forward Recovery Voltage
- Temperature-Independent Switching Behavior

Applications

- Industrial Switched Mode Power Supplies
- Uninterruptible & AUX Power Supplies
- Boost for PFC & DC-DC Stages
- Solar Inverters

Key Parameters (T_c = 25°C Unless Otherwise Specified)

Parameter	Symbol	Value	Unit	Conditions	Notes
Repetitive Peak Reverse Voltage	V _{RRM}	1200	V		
DC Blocking Voltage	V _{DC}	1200	V		
		128		T _c = 25 °C	
Continuous Forward Current	I _F	62		T _c = 135 °C	Fig. 3
		41		T _c = 155 °C	
Repetitive Peak Forward Surge Current	I _{FRM}	161		T _c = 25 °C, t _p = 10 ms, Half Sine Wave	
		91	Α	$T_c = 110 ^{\circ}\text{C}, t_p = 10 \text{ms}, \text{Half Sine Wave}$	
Non-Repetitive Forward Surge	1.	247		T _c = 25 °C, t _p = 10 ms, Half Sine Wave	F: 0
Current	FSM	245		$T_c = 110 ^{\circ}\text{C}$, $t_p = 10 \text{ms}$, Half Sine Wave	Fig. 8
i²t Value	∫i²t	305		$T_{c} = 25 ^{\circ}\text{C}, t_{D} = 10 \text{ms}$	
		300		$T_c = 110 {}^{\circ}\text{C}, t_p = 10 \text{ms}$	
Power Dissipation	P _{tot}	667		T _c = 25 °C	F' . 4
		289	W	T _c = 110 °C	Fig. 4

Electrical Characteristics

Parameter	Symbol	Тур.	Max.	Unit	Test Conditions	Notes
F	, v	1.5	1.8	.,	I _F = 40A, T _j = 25 °C	F:- 1
Forward Voltage	V _F	2.1	3	V	I _F = 40A, T _j = 175 °C	Fig. 1
Reverse Current		45	300	μΑ	$V_R = 1200V, T_j = 25 ^{\circ}C$	Fig. 2
	l R	75	500		V _R = 1200V, T _j = 175 °C	Fig. 2
Total Capacitive Charge	Q _c	194.9		nC	V _R = 800V, T _j = 25 °C	Fig. 5
		2809			$V_R = 0V, T_j = 25 ^{\circ}C, f = 1 ^{\circ}MHz$	
Total Capacitance	С	174		pF	$V_R = 400V, T_j = 25 ^{\circ}C, f = 1 ^{\circ}MHz$	Fig. 6
		127			$V_R = 800V, T_j = 25 ^{\circ}C, f = 1 ^{\circ}MHz$	
Capacitance Stored Energy	E _c	56.6		μJ	V _p = 800V	Fig. 7


Notes:

SiC Schottky Diodes are majority carrier devices, so there is no reverse recovery charge.

Thermal & Mechanical Characteristics

Parameter	Symbol	Value	Unit	Notes
Thermal Resistance, Junction to Case (Typical)	R _{0, JC (TYP)}	0.225	°C/W	
Junction Temperature	T _j	-55 to +175	°C	
Case & Storage Temperature	T _c	-55 to +150	°C	
TO 247 Manuskin - Tanana		1	Nm	M3 Screw
TO-247 Mounting Torque	-	8.8	lbf-in	6-32 Screw

Typical Performance







Figure 1. Forward Characteristics

Figure 2. Reverse Characteristics




700 600 500 400 200 100 0 25 50 75 100 125 150 175 T_c (°C)

Figure 3. Current Derating

Figure 4. Power Derating

Typical Performance



2500

T_j = 25 °C
F_{test} = 1 MHz
V_{test} = 25 mV

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000

1000


1000

10

Conditions:

Figure 5.
Total Capacitance Charge vs. Reverse Voltage

Figure 6.
Capacitance vs. Reverse Voltage







Figure 7.

Typical Capacitance Stored Energy

Figure 8. Transient Thermal Impedance


Package Dimensions & Pin-Out

Package: TO-247-2 (All dimensions are in mm)



Recommended Solder Pad Layout

(All dimensions are in mm)



Product Ordering Information

Order Number	Packing Type
C4D40120H	Tube

REACh, RoHS, and Halogen-Free compliance documentation available for this product.

Revision History

Document Version	Date of Release	Description of changes
0	January - 2019	Initial Release
1	January - 2023	Updated POD and Landing Pad
2	August - 2023	Total Capacitance test condition 800V value corrected Qc and Ec corrected for test condition Renamed Table on Page 1
3	September- 2023	Corrected I _E value at T _{C=} 135C

Notes & Disclaimer

This document and the information contained herein are subject to change without notice. Any such change shall be evidenced by the publication of an updated version of this document by Wolfspeed. No communication from any employee or agent of Wolfspeed or any third party shall effect an amendment or modification of this document. No responsibility is assumed by Wolfspeed for any infringement of patents or other rights of third parties which may result from use of the information contained herein. No license is granted by implication or otherwise under any patent or patent rights of Wolfspeed.

Notwithstanding any application-specific information, guidance, assistance, or support that Wolfspeed may provide, the buyer of this product is solely responsible for determining the suitability of this product for the buyer's purposes, including without limitation for use in the applications identified in the next bullet point, and for the compliance of the buyers' products, including those that incorporate this product, with all applicable legal, regulatory, and safety-related requirements.

This product has not been designed or tested for use in, and is not intended for use in, applications in which failure of the product would reasonably be expected to cause death, personal injury, or property damage, including but not limited to equipment implanted into the human body, life-support machines, cardiac defibrillators, and similar emergency medical equipment, aircraft navigation, communication, and control systems, aircraft power and propulsion systems, air traffic control systems, and equipment used in the planning, construction, maintenance, or operation of nuclear facilities.

RoHS Compliance

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS2), as implemented January 2, 2013. RoHS Declarations for this product can be obtained from your Wolfspeed representative or from the Product Documentation sections of www.wolfspeed.com.

REACh Compliance

REACh substances of high concern (SVHCs) information is available for this product. Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact your Wolfspeed representative to ensure you get the most up-to-date REACh SVHC Declaration. REACh banned substance information (REACh Article 67) is also available upon request.

Contact info:

4600 Silicon Drive Durham, NC 27703 USA Tel: +1.919.313.5300 www.wolfspeed.com/power

© 2023 Wolfspeed, Inc. All rights reserved. Wolfspeed® and the Wolfstreak logo are registered trademarks and the Wolfspeed logo is a trademark of Wolfspeed, Inc. PATENT: https://www.wolfspeed.com/legal/patents

The information in this document is subject to change without notice.