


RoHS

compliant

C2D05120E 1200 V, 5 A Silicon Carbide Schottky Diode

Features

- 1.2 kV Schottky rectifier
- Zero reverse recovery current
- Zero forward recovery voltage
- High-frequency operation
- Temperature-independent switching behavior
- Extremely fast switching
- Positive temperature coefficient on V_F



Package Types: TO-252-2 PN's: C2D05120E

Wolfspeed, Inc. is in the process of rebranding its products and related materials pursuant to the entity name change from Cree, Inc. to Wolfspeed, Inc. During this transition period, products received may be marked with either the Cree

Halogen-Free

Applications

- Switch mode power supplies
- Power factor correction
- Motor drives
- High voltage multipliers

Benefits

- Replace bipolar with unipolar rectifiers
- Essentially no switching losses
- Higher efficiency
- Reduction of heat sink requirements
- Parallel devices without thermal runaway

Maximum Ratings (T_c = 25 °C Unless Otherwise Specified)

Parameter	Symbol	Value	Unit	Test Conditions	Note
Repetitive Peak Reverse Voltage	V _{RRM}	1200			
Surge Peak Reverse Voltage	V _{RSM}	1200	V		
DC Blocking Voltage	V _{DC}	1200			
Continuous Forward Current	I _F	17.5		T _c = 25 °C	
		8.5		T _c = 135 °C	
		5		T _c = 157 °C	
Repetitive Peak Forward Surge Current	I _{FRM}	30	A	T_c = 25 °C, t_p = 10 ms, Half Sine Wave	
Non-Repetitive Peak Forward Surge Current	I _{FSM}	100		T _c = 25 °C, t _P = 10 μs, Pulse	
Power Dissipation	P _{tot}	136	W	T _c = 25 °C	
		59		T _c = 110 °C	
Operating Junction and Storage Temperature	T _J , T _{stg}	-55 to +175	°C		

Rev. 3, January 2024



Electrical Characteristics


Parameter	Symbol	Тур.	Max.	Unit	Test Conditions	Note
Forward Voltage		1.6	1.8	V	I _F = 5 A, T _J = 25 °C	
	V _F	2.6	3.0		I _F = 5 A, T _J = 175 °C	
Reverse Current		50	200	μΑ	V _R = 1200 V, T _J = 25 °C	
	I _R	100	1000		V _R = 1200 V, T _J = 150 °C	
Total Capacitive Charge	Q _c	28		nC	V _R = 1200 V, I _F = 5 A di/dt = 500 A/μs	
Total Capacitance	С	455		pF	V _R = 0 V, T _J = 25 °C, f = 1 MHz	
		45			$V_{R} = 200 \text{ V}, T_{J} = 25 \text{ °C}, f = 1 \text{ MHz}$	
		33			$V_{R} = 400 \text{ V}, \text{ T}_{J} = 25 \text{ °C}, \text{ f} = 1 \text{ MHz}$	


Note: This is a majority carrier diode, so there is no reverse recovery charge.

Thermal Characteristics

Parameter	Symbol	Тур.	Unit
Thermal Resistance from Junction to Case	$R_{ extsf{ heta}JC}$	1.1	°C/W


Typical Performance









Typical Performance










Rev. 3, January 2024




Typical Performance



4



Package Dimensions




Rev. 3, January 2024

4600 Silicon Drive | Durham, NC 27703 | Tel: +1.919.313.5300 | wolfspeed.com/power

C2D05120E



Recommended Solder Pad Layout



Part Number	Package	Marking
C2D05120E	TO-252-2	C2D05120

Rev. 3, January 2024



Revision History

Current Revision	Date of Release	Description of Changes
3	January-2024	Updated Wolfspeed branding, package drawing, and solder pad layout

Rev. 3, January 2024



Notes & Disclaimer

This document and the information contained herein are subject to change without notice. Any such change shall be evidenced by the publication of an updated version of this document by Wolfspeed. No communication from any employee or agent of Wolfspeed or any third party shall effect an amendment or modification of this document. No responsibility is assumed by Wolfspeed for any infringement of patents or other rights of third parties which may result from use of the information contained herein. No license is granted by implication or otherwise under any patent or patent rights of Wolfspeed.

Notwithstanding any application-specific information, guidance, assistance, or support that Wolfspeed may provide, the buyer of this product is solely responsible for determining the suitability of this product for the buyer's purposes, including without limitation for use in the applications identified in the next bullet point, and for the compliance of the buyers' products, including those that incorporate this product, with all applicable legal, regulatory, and safety-related requirements.

This product has not been designed or tested for use in, and is not intended for use in, applications in which failure of the product would reasonably be expected to cause death, personal injury, or property damage, including but not limited to equipment implanted into the human body, life-support machines, cardiac defibrillators, and similar emergency medical equipment, aircraft navigation, communication, and control systems, aircraft power and propulsion systems, air traffic control systems, and equipment used in the planning, construction, maintenance, or operation of nuclear facilities.

RoHS Compliance

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS2), as implemented January 2, 2013. RoHS Declarations for this product can be obtained from your Wolfspeed representative or from the Product Documentation sections of www.wolfspeed.com.

REACh Compliance

REACh substances of high concern (SVHCs) information is available for this product. Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact your Wolfspeed representative to ensure you get the most up-to-date REACh SVHC Declaration. REACh banned substance information (REACh Article 67) is also available upon request.

Contact info:

4600 Silicon Drive Durham, NC 27703 USA Tel: +1.919.313.5300 www.wolfspeed.com/power

© 2024 Wolfspeed, Inc. All rights reserved. Wolfspeed® and the Wolfstreak logo are registered trademarks and the Wolfspeed logo is a trademark of Wolfspeed, Inc. PATENT: https://www.wolfspeed.com/legal/patents

The information in this document is subject to change without notice.