

E3M0160120D

Silicon Carbide Power MOSFET
E-Series Automotive
N-Channel Enhancement Mode



Features

- 3rd generation SiC MOSFET technology
- High blocking voltage with low on-resistance
- High-speed switching with low capacitances
- Fast intrinsic diode with low reverse recovery (Q_{rr})
- Halogen free, RoHS compliant
- Automotive Qualified (AEC-Q101) and PPAP Capable



Benefits

- Higher system efficiency
- Reduce cooling requirements
- Increase power density
- Increase system switching frequency

Applications

- EV Battery Chargers
- High Voltage DC/DC Converters

Package



Part Number	Package	Marking
E3M0160120D	TO-247-3L	E3M0160120D

Maximum Ratings ($T_c = 25^\circ\text{C}$ unless otherwise specified)

Symbol	Parameter	Value	Unit	Note	
V_{DSmax}	Drain - Source Voltage	1200	V		
V_{GSmax}	Gate - Source Voltage	-8/+19	V	Note: 1	
I_D	Continuous Drain Current, $V_{GS} = 15\text{V}$	$T_c = 25^\circ\text{C}$	17.9	A	Fig. 19 Note: 2
		$T_c = 100^\circ\text{C}$	13.5		
$I_{D(pulse)}$	Pulsed Drain Current, Pulse width t_p limited by T_{jmax}	34	A	Fig. 22	
P_D	Power Dissipation, $T_c=25^\circ\text{C}$, $T_j = 175^\circ\text{C}$	103	W	Fig. 20 Note: 2	
T_j, T_{stg}	Operating Junction and Storage Temperature	-55 to +175	$^\circ\text{C}$		
T_L	Solder Temperature, 1.6mm (0.063") from case for 10s	260	$^\circ\text{C}$		
M_d	Mounting Torque, M3 or 6-32 screw	1	Nm		
		8.8	lbf-in		

Note (1): Recommended turn off / turn on gate voltage $V_{GS} = -4V...0V / +15V$

Note (2): Verified by design


Electrical Characteristics ($T_C = 25^\circ\text{C}$ unless otherwise specified)

Symbol	Parameter	Min.	Typ.	Max.	Unit	Test Conditions	Note
$V_{(BR)DSS}$	Drain-Source Breakdown Voltage	1200			V	$V_{GS} = 0\text{ V}, I_D = 100\ \mu\text{A}$	
$V_{GS(th)}$	Gate Threshold Voltage	1.8	2.8	3.6	V	$V_{DS} = V_{GS}, I_D = 2.33\ \text{mA}$	Fig. 11
			2.2		V	$V_{DS} = V_{GS}, I_D = 2.33\ \text{mA}, T_J = 175^\circ\text{C}$	
I_{DSS}	Zero Gate Voltage Drain Current		1	50	μA	$V_{DS} = 1200\ \text{V}, V_{GS} = 0\ \text{V}$	
I_{GSS}	Gate-Source Leakage Current		10	250	nA	$V_{GS} = 15\ \text{V}, V_{DS} = 0\ \text{V}$	
$R_{DS(on)}$	Drain-Source On-State Resistance		159	208	m Ω	$V_{GS} = 15\ \text{V}, I_D = 8.5\ \text{A}$	Fig. 4, 5, 6
			280			$V_{GS} = 15\ \text{V}, I_D = 8.5\ \text{A}, T_J = 175^\circ\text{C}$	
g_{fs}	Transconductance		5		S	$V_{DS} = 20\ \text{V}, I_{DS} = 8.5\ \text{A}$	Fig. 7
			5			$V_{DS} = 20\ \text{V}, I_{DS} = 8.5\ \text{A}, T_J = 175^\circ\text{C}$	
C_{iss}	Input Capacitance		730		pF	$V_{GS} = 0\ \text{V}, V_{DS} = 0\ \text{V to } 1000\ \text{V}$ $F = 1\ \text{Mhz}$ $V_{AC} = 25\ \text{mV}$	Fig. 17, 18
C_{oss}	Output Capacitance		31				
C_{rss}	Reverse Transfer Capacitance		2				
E_{oss}	C_{oss} Stored Energy		17		μJ	$V_{DS} = 1000\ \text{V}, F = 1\ \text{Mhz}$	Fig. 16
$C_{o(er)}$	Effective Output Capacitance (Energy Related)		36		pF	$V_{GS} = 0\ \text{V}, V_{DS} = 0\ \text{V to } 800\ \text{V}$	Note: 3
$C_{o(tr)}$	Effective Output Capacitance (Time Related)		55				
E_{oN}	Turn-On Switching Energy (External Diode)		195		μJ	$V_{DS} = 800\ \text{V}, V_{GS} = -4\ \text{V}/15\ \text{V}, I_D = 8.5\ \text{A},$ $R_{G(ext)} = 2.5\ \Omega, L = 404\ \mu\text{H}, T_J = 175^\circ\text{C}$ FWD = External SiC DIODE	Fig. 26
E_{oOFF}	Turn Off Switching Energy (External Diode)		11				
E_{oN}	Turn-On Switching Energy (Body Diode FWD)		337		μJ	$V_{DS} = 800\ \text{V}, V_{GS} = -4\ \text{V}/15\ \text{V}, I_D = 8.5\ \text{A},$ $R_{G(ext)} = 2.5\ \Omega, L = 404\ \mu\text{H}, T_J = 175^\circ\text{C}$ FWD = Internal Body Diode	Fig. 26
E_{oOFF}	Turn-Off Switching Energy (Body Diode FWD)		11				
$t_{d(on)}$	Turn-On Delay Time		25		ns	$V_{DD} = 800\ \text{V}, V_{GS} = -4\ \text{V}/15\ \text{V}$ $I_D = 8.5\ \text{A}, R_{G(ext)} = 2.5\ \Omega,$ Timing relative to V_{DS} Inductive load	Fig. 27
t_r	Rise Time		15				
$t_{d(off)}$	Turn-Off Delay Time		14				
t_f	Fall Time		12				
$R_{G(int)}$	Internal Gate Resistance		6.5		Ω	$f = 1\ \text{MHz}, V_{AC} = 25\ \text{mV}$	
Q_{gs}	Gate to Source Charge		10		nC	$V_{DS} = 800\ \text{V}, V_{GS} = -4\ \text{V}/15\ \text{V}$ $I_D = 8.5\ \text{A}$ Per IEC60747-8-4 pg 21	Fig. 12
Q_{gd}	Gate to Drain Charge		13				
Q_g	Total Gate Charge		33				

Note (3): $C_{o(er)}$, a lumped capacitance that gives same stored energy as C_{oss} while V_{ds} is rising from 0 to 800V
 $C_{o(tr)}$, a lumped capacitance that gives same charging time as C_{oss} while V_{ds} is rising from 0 to 800V


Reverse Diode Characteristics ($T_c = 25^\circ\text{C}$ unless otherwise specified)

Symbol	Parameter	Typ.	Max.	Unit	Test Conditions	Note
V_{SD}	Diode Forward Voltage	4.8		V	$V_{GS} = -4\text{ V}, I_{SD} = 4.25\text{ A}, T_J = 25^\circ\text{C}$	Fig. 8, 9, 10
		4.2		V	$V_{GS} = -4\text{ V}, I_{SD} = 4.25\text{ A}, T_J = 175^\circ\text{C}$	
I_S	Continuous Diode Forward Current		17	A	$V_{GS} = -4\text{ V}, T_c = 25^\circ\text{C}$	
$I_{S, pulse}$	Diode pulse Current		34	A	$V_{GS} = -4\text{ V}$, pulse width t_p limited by T_{jmax}	
t_{rr}	Reverse Recover time	36		ns	$V_{GS} = -4\text{ V}, I_{SD} = 8.5\text{ A}, V_R = 800\text{ V}$ $dif/dt = 1140\text{ A}/\mu\text{s}, T_J = 175^\circ\text{C}$	
Q_{rr}	Reverse Recovery Charge	199		nC		
I_{rrm}	Peak Reverse Recovery Current	10		A		
t_{rr}	Reverse Recover time	38		ns	$V_{GS} = -4\text{ V}, I_{SD} = 8.5\text{ A}, V_R = 800\text{ V}$ $dif/dt = 580\text{ A}/\mu\text{s}, T_J = 175^\circ\text{C}$	
Q_{rr}	Reverse Recovery Charge	174		nC		
I_{rrm}	Peak Reverse Recovery Current	7		A		

Thermal Characteristics

Symbol	Parameter	Typ.	Max.	Unit	Test Conditions	Note
$R_{\theta JC}$	Thermal Resistance from Junction to Case	1.13	1.24	$^\circ\text{C}/\text{W}$		Fig. 21



Typical Performance




Figure 1. Output Characteristics $T_j = -55\text{ }^\circ\text{C}$




Figure 2. Output Characteristics $T_j = 25\text{ }^\circ\text{C}$




Figure 3. Output Characteristics $T_j = 175\text{ }^\circ\text{C}$




Figure 4. Normalized On-Resistance vs. Temperature




Figure 5. On-Resistance vs. Drain Current For Various Temperatures




Figure 6. On-Resistance vs. Temperature For Various Gate Voltage



Typical Performance




Figure 7. Transfer Characteristic for Various Junction Temperatures




Figure 8. Body Diode Characteristic at -55 °C




Figure 9. Body Diode Characteristic at 25 °C




Figure 10. Body Diode Characteristic at 175 °C




Figure 11. Threshold Voltage vs. Temperature




Figure 12. Gate Charge Characteristics



Typical Performance




Figure 13. 3rd Quadrant Characteristic at $-55\text{ }^{\circ}\text{C}$




Figure 14. 3rd Quadrant Characteristic at $25\text{ }^{\circ}\text{C}$




Figure 15. 3rd Quadrant Characteristic at $175\text{ }^{\circ}\text{C}$




Figure 16. Output Capacitor Stored Energy




Figure 17. Capacitances vs. Drain-Source Voltage (0 - 200V)




Figure 18. Capacitances vs. Drain-Source Voltage (0 - 1200V)



Typical Performance




Figure 19. Continuous Drain Current Derating vs. Case Temperature




Figure 20. Maximum Power Dissipation Derating vs. Case Temperature




Figure 21. Transient Thermal Impedance (Junction - Case)




Figure 22. Safe Operating Area




Figure 23. Clamped Inductive Switching Energy vs. Drain Current ($V_{DD} = 600V$)




Figure 24. Clamped Inductive Switching Energy vs. Drain Current ($V_{DD} = 800V$)



Typical Performance




Figure 25. Clamped Inductive Switching Energy vs. $R_{G(ext)}$




Figure 26. Clamped Inductive Switching Energy vs. Temperature




Figure 27. Switching Times vs. $R_{G(ext)}$




Figure 28. Switching Times Definition

Test Circuit Schematic





Figure 29. Clamped Inductive Switching Waveform Test Circuit

Package Dimensions



⌀0.25(M) B A(M)


SYMBOL	MIN (mm)	MAX (mm)
A	4.83	5.21
A1	2.29	2.54
A2	1.91	2.16
b	1.07	1.33
b1	1.91	2.41
b3	2.87	3.38
c	0.55	0.68
D	20.8	21.1
D1	16.25	17.65
D2	0.95	1.25
E	15.75	16.13
E1	13.1	14.15
E2	3.68	5.1
E3	1	1.9
E4	12.38	13.43
e	5.44 BSC	
L	19.81	20.32
L1	4.1	4.4
ØP	3.51	3.65
Q	5.49	6
S	6.04	6.3
T	17.5° REF.	
W	3.5° REF.	
X	4° REF.	

1	GATE
2	DRAIN
3	SOURCE
4	DRAIN

- NOTES:
1. ALL METAL SURFACES ARE TIN PLATED (MATTE), EXCEPT AREA OF CUT.
 2. DIMENSIONING & TOLERANCING CONFORM TO ASME Y14.5M-1994.
 3. ALL DIMENSIONS ARE LISTED IN MILLIMETERS. ANGLES ARE IN DEGREES.
 4. BURR OR MOLD FLASH SIZE (0.5 mm) IS NOT INCLUDED IN THE DIMENSIONS



Recommended Solder Pad Layout



TO-247-3



Revision history

Document Version	Date of release	Description of changes
1.0	July-2023	Initial datasheet
2.0	October-2023	Corrected Rdson max value on page 2



Notes & Disclaimer

This document and the information contained herein are subject to change without notice. Any such change shall be evidenced by the publication of an updated version of this document by Wolfspeed. No communication from any employee or agent of Wolfspeed or any third party shall effect an amendment or modification of this document. No responsibility is assumed by Wolfspeed for any infringement of patents or other rights of third parties which may result from use of the information contained herein. No license is granted by implication or otherwise under any patent or patent rights of Wolfspeed.

Notwithstanding any application-specific information, guidance, assistance, or support that Wolfspeed may provide, the buyer of this product is solely responsible for determining the suitability of this product for the buyer's purposes, including without limitation for use in the applications identified in the next bullet point, and for the compliance of the buyers' products, including those that incorporate this product, with all applicable legal, regulatory, and safety-related requirements.

This product has not been designed or tested for use in, and is not intended for use in, applications in which failure of the product would reasonably be expected to cause death, personal injury, or property damage, including but not limited to equipment implanted into the human body, life-support machines, cardiac defibrillators, and similar emergency medical equipment, aircraft navigation, communication, and control systems, aircraft power and propulsion systems, air traffic control systems, and equipment used in the planning, construction, maintenance, or operation of nuclear facilities.

RoHS Compliance

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS2), as implemented January 2, 2013. RoHS Declarations for this product can be obtained from your Wolfspeed representative or from the Product Documentation sections of www.wolfspeed.com.

REACH Compliance

REACH substances of high concern (SVHCs) information is available for this product. Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact your Wolfspeed representative to ensure you get the most up-to-date REACH SVHC Declaration. REACH banned substance information (REACH Article 67) is also available upon request.

Contact info:

4600 Silicon Drive
Durham, NC 27703 USA
Tel: +1.919.313.5300
www.wolfspeed.com/power