

# 4th Generation 1200 V, 10 A Silicon Carbide Schottky Diode


# **Description**

With the performance advantages of a Silicon Carbide (SiC) Schottky Barrier diode, power electronics systems can expect to meet higher efficiency standards than Si-based solutions, while also reaching higher frequencies and power densities. SiC diodes can be easily paralleled to meet various application demands, without concern of thermal runaway. In combination with the reduced cooling requirements and improved thermal performance of SiC products, SiC diodes are able to provide lower overall system costs in a variety of diverse applications.









Package Types: TO-247-3 Marking: C4D10120

#### **Features**

- High-Frequency Operation
- Zero Reverse Recovery Current / Forward Recovery Voltage
- Temperature-Independent Switching Behavior
- Parallel Devices Without Thermal Runaway

# **Applications**

- Boost Diodes in PFC or DC/DC Stages
- Free Wheeling Diodes in Inverter Stages
- Switch Mode Power Supplies
- Solar Inverters
- AC/DC Converters

# **Maximum Ratings** ( $T_c = 25^{\circ}$ C Unless Otherwise Specified)

\* Per Leg, \*\* Per Device

Parameter	Symbol	Value	Unit	Test Conditions	Notes	
Repetitive Peak Reverse Voltage	V <sub>RRM</sub>	1200				
Surge Peak Reverse Voltage	V <sub>RSM</sub>	1300	V			
DC Blocking Voltage	V <sub>DC</sub>	1200				
		19/38		T <sub>c</sub> = 25 °C		
Continuous Forward Current (Per Leg/Per Device)	I <sub>F</sub>	9/18		T <sub>c</sub> = 135 °C	Fig. 3	
		5/10		T <sub>c</sub> = 160 °C		
Repetitive Peak Forward Surge Current	   FRM	26*	A	T <sub>c</sub> = 25 °C, t <sub>p</sub> = 10 ms, Half Sine Wave		
		18*		T <sub>c</sub> = 110 °C, t <sub>p</sub> = 10 ms, Half Sine Wave		
Non-Repetitive Forward Surge Current	I <sub>FSM</sub>	46*		T <sub>c</sub> = 25 °C, t <sub>p</sub> = 10 ms, Half Sine Wave	Fig. 0	
		36*		T <sub>c</sub> = 110 °C, t <sub>p</sub> = 10 ms, Half Sine Wave	Fig. 8	
Non-Repetitive Peak Forward Surge Current	l <sub>F,Max</sub>	400*		T <sub>c</sub> = 25 °C, t <sub>p</sub> = 10 μs, Pulse		
		320*		$T_{c} = 110 {}^{\circ}\text{C},  t_{p} = 10  \mu\text{s},  \text{Pulse}$		
Power Dissipation (Per Leg/Per Device)	P <sub>tot</sub>	93/187	W	T <sub>c</sub> = 25 °C	Fig. 4	
		40/81		T <sub>c</sub> = 110 °C		
i²t value	∫i²dt	10.6*	A²s	T <sub>c</sub> = 25C, tp=10ms		
		6.5*		T <sub>c</sub> = 110C, tp=10ms		
Diode dV/dt Ruggedness	dV/dt	200	V/ns	V <sub>R</sub> = 0-650V		

# **Electrical Characteristics**

Parameter	Symbol	Тур.	Max.	Unit	Test Conditions	Notes
Forward Voltage	V	1.4	1.8	V	I <sub>F</sub> = 5 A, T <sub>j</sub> = 25 °C	Fig. 1
	V <sub>F</sub>	1.9	3		I <sub>F</sub> = 5 A, T <sub>j</sub> = 175 °C	
Reverse Current		20	150		V <sub>R</sub> = 1200 V, T <sub>j</sub> = 25 °C	F:- 2
	I <sub>R</sub>	40	300	μΑ	V <sub>R</sub> = 1200 V, T <sub>j</sub> = 175 °C	Fig. 2
Total Capacitive Charge	Q <sub>c</sub>	27		nC	$V_R = 800 \text{ V, T}_j = 25 ^{\circ}\text{C}$ $I_F = 5A, \text{ di/dt} = 200A/\mu\text{s}$	Fig. 5
		390			$V_R = 0 \text{ V}, T_j = 25 \text{ °C}, f = 1 \text{ MHz}$	
Total Capacitance	С	27		pF	$V_R = 400 \text{ V}, T_j = 25 \text{ °C}, f = 1 \text{ MHz}$	Fig. 6
		20			$V_R = 800 \text{ V}, T_j = 25 \text{ °C}, f = 1 \text{ MHz}$	
Capacitance Stored Energy	E <sub>c</sub>	8.0		μJ	V <sub>R</sub> = 800 V	Fig. 7


SiC Schottky Diodes are majority carrier devices, so there is no reverse recovery charge.

## **Thermal & Mechanical Characteristics**


Parameter	Symbol	Value	Unit	Notes
Thermal Resistance, Junction to Case (Typical)	R <sub>0, JC (TYP)</sub>	0.8** 1.6*	°C/W	
Junction Temperature	T <sub>j</sub>	-55 to +175	0.5	
Case & Storage Temperature	T <sub>c</sub>	-55 to +135	°C	
	-	1	Nm	M3 Screw
TO-247 Mounting Torque		8.8	lbf-in	6-32 Screw

<sup>\*</sup> Per Leg, \*\* Per Device


# **Typical Performance**




**Figure 1**Forward Characteristics



Reverse Characteristics




**Figure 3**Current Derating




**Figure 4** Power Derating


# **Typical Performance**




Total Capacitance Charge vs. Reverse Voltage



Capacitance Stored Energy



Capacitance vs. Reverse Voltage



Non-Repetitive Peak Forward Surge Current vs. Pulse Duration





Figure 9 Transient Thermal Impedance


# **Package Dimensions & Pin-Out**

Package: TO-247-3



# **Recommended Solder Pad Layout**

Primary dimensions shown in mm.



## **Diode Model**

$$Vf_T = V_T + If * R_T$$

$$V_T = 0.96 + (T_j * -1.22*10^{-3})$$

$$V_T = 0.08 + (T_j * 8.5*10^{-4})$$

$$V_T = 0.08 + (T_j * 8.5*10^{-4})$$
Note: T<sub>j</sub> = Diode Junction Temperature In Degrees Celsius, valid from 25°C to 175°C

## **Product Ordering Information**

Order Number	Packing Type
C4D10120D	Tube

REACh, RoHS, and Halogen-Free compliance documentation available for this product.

# **Revision History**

Document Version	Date of Release	Description of Changes
Н	September- 2016	Initial Release
9	May-2023	Update Branding, Forward Voltage Test Conditions, POD, Package Image, solder pad layout
10	November-2023	Corrected V <sub>F</sub> test conditions, added dV/dT ruggedness characteristic, updated Q <sub>C</sub> , I <sub>E</sub> , P <sub>tot</sub> test conditions

## Notes & Disclaimer

This document and the information contained herein are subject to change without notice. Any such change shall be evidenced by the publication of an updated version of this document by Wolfspeed. No communication from any employee or agent of Wolfspeed or any third party shall effect an amendment or modification of this document. No responsibility is assumed by Wolfspeed for any infringement of patents or other rights of third parties which may result from use of the information contained herein. No license is granted by implication or otherwise under any patent or patent rights of Wolfspeed.

Notwithstanding any application-specific information, guidance, assistance, or support that Wolfspeed may provide, the buyer of this product is solely responsible for determining the suitability of this product for the buyer's purposes, including without limitation for use in the applications identified in the next bullet point, and for the compliance of the buyers' products, including those that incorporate this product, with all applicable legal, regulatory, and safety-related requirements.

This product has not been designed or tested for use in, and is not intended for use in, applications in which failure of the product would reasonably be expected to cause death, personal injury, or property damage, including but not limited to equipment implanted into the human body, life-support machines, cardiac defibrillators, and similar emergency medical equipment, aircraft navigation, communication, and control systems, air craft power and propulsion systems, air traffic control systems, and equipment used in the planning, construction, maintenance, or operation of nuclear facilities.

## **RoHS Compliance**

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS2), as implemented January 2, 2013. RoHS Declarations for this product can be obtained from your Wolfspeed representative or from the Product Documentation sections of www.wolfspeed. com.

#### **REACh Compliance**

REACh substances of high concern (SVHCs) information is available for this product. Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact your Wolfspeed representative to ensure you get the most up-to-date REACh SVHC Declaration. REACh banned substance information (REACh Article 67) is also available upon request.

#### **Contact info:**

4600 Silicon Drive Durham, NC 27703 USA Tel: +1.919.313.5300 www.wolfspeed.com/power

© 2023 Wolfspeed, Inc. All rights reserved. Wolfspeed® and the Wolfstreak logo are registered trademarks and the Wolfspeed logo is a trademark of Wolfspeed, Inc. PATENT: https://www.wolfspeed.com/legal/patents

The information in this document is subject to change without notice.