

Silicon Carbide Power MOSFET E-Series Automotive N-Channel Enhancement Mode

Features

- 3rd generation SiC MOSFET technology
- Optimized package with separate driver source pin
- 4.7mm of creepage distance between drain and source
- High blocking voltage with low on-resistance
- High-speed switching with low capacitances
- Fast intrinsic diode with low reverse recovery (Q_{rr})
- Halogen free, RoHS compliant
- Automotive Qualified (AEC-Q101) and PPAP Capable

Benefits

- Reduce switching losses and minimize gate ringing
- Higher system efficiency
- Reduce cooling requirements
- Increase power density
- Increase system switching frequency

Applications

- Motor Control
- EV Battery Chargers
- High Voltage DC/DC Converters

Maximum Ratings ($T_c = 25$ °C unless otherwise specified)

Symbol	Parameter	Value	Unit	Note	
V_{DSmax}	Drain - Source Voltage		1200	V	
V_{GSmax}	Gate - Source Voltage		-8/+19	V	Note: 1
		$T_C = 25^{\circ}C$	114	A	Fig. 19 Note: 2
I _D	Continuous Drain Current, V _{GS} = 15 V	T _C = 100°C	83		
I _{D(pulse)}	Pulsed Drain Current, Pulse width t_p limited by T_{jmax}		248	А	Fig. 22
P _D	Power Dissipation, $T_c = 25^{\circ}C$, $T_j = 175^{\circ}C$	500	W	Fig. 20 Note: 2	
T _J , T _{stg}	Operating Junction and Storage Temperature	-55 to +175	°C		
TL	Solder Temperature, 1.6mm (0.063") from case for 10s		260	°C	

Package

123456


Tab

Drain

Note (1): Recommended turn off / turn on gate voltage $\rm V_{GS}\,$ - 4V...0V / +15V Note (2): Verified by design

Rev. 1, December 2023





Part Number	Package	Marking
E3M0021120J2	TO-263-7XL	E3M0021120J2

Symbol	Parameter	Min.	Тур.	Max.	Unit	Test Conditions	Note
V _{(BR)DSS}	Drain-Source Breakdown Voltage	1200		1	V	$V_{GS} = 0 \text{ V}, I_D = 100 \mu\text{A}$	
M	Gate Threshold Voltage	1.8	2.9	3.8	V	$V_{DS} = V_{GS}, I_D = 17.10 \text{ mA}$ $V_{DS} = V_{GS}, I_D = 17.10 \text{ mA}, T_J = 175^{\circ}\text{C}$	Fig. 11
$V_{\text{GS(th)}}$			2.3	1	V		
I _{DSS}	Zero Gate Voltage Drain Current		1	50	μA	$V_{DS} = 1200 V$, $V_{GS} = 0 V$	
I _{GSS}	Gate-Source Leakage Current		10	250	nA	$V_{GS} = 15 V, V_{DS} = 0 V$	
D	Drain-Source On-State Resistance		21	29	mΩ	$V_{GS} = 15 \text{ V}, I_D = 62.12 \text{ A}$	Fig. 4,
R _{DS(on)}			35			$V_{GS} = 15 \text{ V}, I_D = 62.12 \text{ A}, T_J = 175 ^{\circ}\text{C}$	5,6
g _{fs}	Transconductance		38		s	V_{DS} = 20 V, I_{DS} = 62.12 A	Fig. 7
913			35			V_{DS} = 20 V, I_{DS} = 62.12 A, T_J = 175°C	119.7
C _{iss}	Input Capacitance		5100			$V_{GS} = 0 V, V_{DS} = 0V \text{ to } 1000 V$ f = 100 kHz $V_{AC} = 25 \text{ mV}$	
C _{oss}	Output Capacitance		174		рF		Fig. 17
C _{rss}	Reverse Transfer Capacitance		11	1	1		
Eoss	Coss Stored Energy		98	1	μJ	V _{DS} = 800 V, f = 100 kHz	Fig. 1
C _{o(er)}	Effective Output Capacitance (Energy Related)		210	1	pF	$V_{GS} = 0 V, V_{DS} = 0 \text{ to } 800 V$	Note: 3
C _{o(tr)}	Effective Output Capacitance (Time Related)		323		pF		
E _{ON}	Turn-On Switching Energy (Body Diode FWD)		1.7			V_{DS} = 800 V, V_{GS} = -4 V/15 V, I_{D} = 62.12 A,	Fig. 26, 28
EOFF	Turn-Off Switching Energy (Body Diode FWD)		0.3		mJ	$R_{G(ext)} = 2.5 \Omega$, L= 59 μH, T _J = 175°C FWD = Internal Body Diode	
t _{d(on)}	Turn-On Delay Time	+	15				+
			_			$V_{\text{DD}} = 800 \text{ V}, V_{\text{GS}} = -4 \text{ V}/15 \text{ V}, I_{\text{D}} = 62.12 \text{ A},$	Fig. 27, 28
tr	Rise Time	+	34		ns	$R_{G(ext)} = 2.5 \Omega, L = 59 \mu H, T_J = 25^{\circ}C$	
$t_{d(off)}$	Turn-Off Delay Time		54			Timing relative to V _{DS} Inductive load	
t _f	Fall Time		13				
$R_{G(int)}$	Internal Gate Resistance		2.9		Ω	$f = 1 MHz$, $V_{AC} = 25 mV$	
Q_{gs}	Gate to Source Charge		60			$V_{DS} = 800 \text{ V}, V_{GS} = -4 \text{ V}/15 \text{ V}$	Fig. 12
Q_{gd}	Gate to Drain Charge		45		nC	I _D = 62.12 A	
Qg	Total Gate Charge		169			Per IEC60747-8-4 pg 21	

Electrical Characteristics ($T_c = 25^{\circ}C$ unless otherwise specified)

Note (3): $C_{o(er)}$, a lumped capacitance that gives same stored energy as Coss while Vds is rising from 0 to 800V $C_{o(tr)}$, a lumped capacitance that gives same charging time as Coss while Vds is rising from 0 to 800V

Rev. 1, December 2023



Reverse Diode Characteristics ($T_c = 25^{\circ}C$ unless otherwise specified)

Symbol	Parameter	Тур.	Max.	Unit	Test Conditions	Note
N	Diode Forward Voltage	4.9		V	$V_{_{GS}} = -4 \text{ V}, \text{ I}_{_{SD}} = 31.1 \text{ A}, \text{ T}_{_{J}} = 25 ^{\circ}\text{C}$	Fig. 8, 9, 10
V _{sD}		4.4		V	$V_{_{GS}} = -4 \text{ V}, \text{ I}_{_{SD}} = 31.1 \text{ A}, \text{ T}_{_{J}} = 175 \text{ °C}$	
ls	Continuous Diode Forward Current		85	А	$V_{GS} = -4 V, T_C = 25^{\circ}C$	
I _{S, pulse}	Diode pulse Current		248	А	V_{GS} = -4 V, pulse width t _P limited by T _{jmax}	
t _{rr}	Reverse Recover time	16		ns		
Q _{rr}	Reverse Recovery Charge	416		nC	$V_{gS} = -4 V, I_{SD} = 62.12 A, V_{R} = 800 V$ $di_{F}/dt = 5300 A/\mu s, T_{J} = 25 °C$	
I _{rrm}	Peak Reverse Recovery Current	44		A		
t _{rr}	Reverse Recover time	22		ns		
Q _{rr}	Reverse Recovery Charge	268		nC	$V_{GS} = -4 V, I_{SD} = 62.12 A, V_{R} = 800 V$ $di_{F}/dt = 2240 A/\mu s, T_{J} = 25 °C$	
I _{rrm}	Peak Reverse Recovery Current	21		A		

Thermal Characteristics

Symbol	Parameter	Тур.	Max.	Unit	Test Conditions	Note
R _{ejc}	Thermal Resistance from Junction to Case	0.23	0.30	°C/W		Fig. 21



Typical Performance









Figure 1. Output Characteristics T_J = -55 °C
























Rev. 1, December 2023

4600 Silicon Drive | Durham, NC 27703 | Tel: +1.919.313.5300 | wolfspeed.com/power



0

0

-25

-50

-75

-100

-125

-150

-175

-200

-25

-50

-75

-100 -125

-150

-175

-200

180

0 - 0

Typical Performance




Figure 11. Threshold Voltage vs. Temperature

Figure 12. Gate Charge Characteristics

Rev. 1, December 2023

4600 Silicon Drive | Durham, NC 27703 | Tel: +1.919.313.5300 | wolfspeed.com/power






Figure 13. 3rd Quadrant Characteristic at -55 °C







Figure 15. 3rd Quadrant Characteristic at 175 °C







6






Figure 16. Output Capacitor Stored Energy





Figure 18. Capacitances vs. Drain-Source Voltage (0 - 1200V)


Rev. 1, December 2023


4600 Silicon Drive | Durham, NC 27703 | Tel: +1.919.313.5300 | wolfspeed.com/power


Typical Performance






























Rev. 1, December 2023

4600 Silicon Drive | Durham, NC 27703 | Tel: +1.919.313.5300 | wolfspeed.com/power






Figure 25. Clamped Inductive Switching Energy vs. R_{G(ext)}




Figure 27. Switching Times vs. $R_{G(ext)}$




Figure 26. Clamped Inductive Switching Energy vs. Temperature




Figure 28. Switching Times Definition

8

Rev. 1, December 2023

Test Circuit Schematic








Figure 29. Clamped Inductive Switching Waveform Test Circuit


Rev. 1, December 2023

Package Dimensions









SYMBOL	MIN (mm)	MAX (mm)		
A	4.30	4.70		
A1	0.00	0.25		
A2	2.20	2.60		
b	0.52	0.72		
b1	0.60	0.80		
с	0.42	0.62		
c1	1.07	1.47		
D	9.05	9.45		
D1	7.58	7.98		
D2	2.05	2.45		
Е	9.80	10.20		
E1	6.30	6.97		
E2	7.80	8.20		
e	1.27 H	BSC		
Н	14.87	15.27		
H1	4.55	4.95		
L	2.48	2.88		
L1	0.87	1.27		
θ	0°	8°		
θ1	4°	10°		
θ2	0°	6°		

NOTE

1. ALL METAL SURFACES ARE TIN PLATED (MATTE), EXCEPT AREA OF CUT.

2. DIMENSIONING & TOLERANCING CONFORM TO ASME Y14.5M-1994.


3. ALL DIMENSIONS ARE LISTED IN MILLIMETERS. ANGLES ARE IN DEGREES.

4. PACKAGE BURR FLASH SIZE (0.5 mm) IS NOT INCLUDED IN THE DIMENSIONS

Rev. 1, December 2023

Recommended Solder Pad Layout

All dimensions in mm





11

Revision history

Document Version Date of release		Descriptiion of changes
1.0	December 2023	Initial release

Rev. 1, December 2023



Notes & Disclaimer

This document and the information contained herein are subject to change without notice. Any such change shall be evidenced by the publication of an updated version of this document by Wolfspeed. No communication from any employee or agent of Wolfspeed or any third party shall effect an amendment or modification of this document. No responsibility is assumed by Wolfspeed for any infringement of patents or other rights of third parties which may result from use of the information contained herein. No license is granted by implication or otherwise under any patent or patent rights of Wolfspeed.

Notwithstanding any application-specific information, guidance, assistance, or support that Wolfspeed may provide, the buyer of this product is solely responsible for determining the suitability of this product for the buyer's purposes, including without limitation for use in the applications identified in the next bullet point, and for the compliance of the buyers' products, including those that incorporate this product, with all applicable legal, regulatory, and safety-related requirements.

This product has not been designed or tested for use in, and is not intended for use in, applications in which failure of the product would reasonably be expected to cause death, personal injury, or property damage, including but not limited to equipment implanted into the human body, life-support machines, cardiac defibrillators, and similar emergency medical equipment, aircraft navigation, communication, and control systems, aircraft power and propulsion systems, air traffic control systems, and equipment used in the planning, construction, maintenance, or operation of nuclear facilities.

RoHS Compliance

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS2), as implemented January 2, 2013. RoHS Declarations for this product can be obtained from your Wolfspeed representative or from the Product Documentation sections of www.wolfspeed. com.

REACh Compliance

REACh substances of high concern (SVHCs) information is available for this product. Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact your Wolfspeed representative to ensure you get the most up-to-date REACh SVHC Declaration. REACh banned substance information (REACh Article 67) is also available upon request.

Contact info:

4600 Silicon Drive Durham, NC 27703 USA Tel: +1.919.313.5300 www.wolfspeed.com/power

© 2023 Wolfspeed, Inc. All rights reserved. Wolfspeed® and the Wolfstreak logo are registered trademarks and the Wolfspeed logo is a trademark of Wolfspeed, Inc. PATENT: https://www.wolfspeed.com/legal/patents

The information in this document is subject to change without notice.