

Silicon Carbide Power MOSFET E-Series Automotive N-Channel Enhancement Mode

AND THE CONSTITUTION OF THE CASE OF THE CA

Features

- · 3rd generation SiC MOSFET technology
- High blocking voltage with low on-resistance
- High-speed switching with low capacitances
- Fast intrinsic diode with low reverse recovery (Q,,)
- Halogen free, RoHS compliant
- Automotive Qualified (AEC-Q101) and PPAP Capable

Benefits

- Higher system efficiency
- Reduce cooling requirements
- Increase power density
- · Increase system switching frequency

Applications


- EV Battery Chargers
- · High Voltage DC/DC Converters

Package









Part Number	Package	Marking
E3M0075120D	TO-247-3L	E3M0075120D

Maximum Ratings ($T_c = 25 \, ^{\circ}\text{C}$ unless otherwise specified)

Symbol	Parameter	Value	Unit	Note	
V _{DSmax}	Drain - Source Voltage	1200	V		
V_{GSmax}	Gate - Source Voltage		-8/+19	٧	Note: 1
	Continuous Drain Current, $V_{GS} = 15 \text{ V}$ $ T_C = 25^{\circ}\text{C} $ $ T_C = 100^{\circ}\text{C} $		32		Fig. 19
I _D			23		Note: 2
I _{D(pulse)}	Pulsed Drain Current, Pulse width t _P limited by T _{jmax}	80	А	Fig. 22	
P _D	Power Dissipation, T _c =25°C, T _J = 175 °C	145	W	Fig. 20 Note: 2	
T_J , T_{stg}	Operating Junction and Storage Temperature	-55 to +175	°C		
T _L	Solder Temperature, 1.6mm (0.063") from case for 10s	260	°C		
M _d	Mounting Torque , M3 or 6-32 screw	1 8.8	Nm Ibf-in		

Note (1): Recommended turn off / turn on gate voltage $V_{_{GS}}$ - 4V...0V / +15V

Note (2): Verified by design

Electrical Characteristics ($T_c = 25$ °C unless otherwise specified)

Symbol	Parameter	Min.	Тур.	Max.	Unit	Test Conditions	Note	
$V_{(BR)DSS}$	Drain-Source Breakdown Voltage	1200			٧	V _{GS} = 0 V, I _D = 100 μA		
V	Cata Thurshald Valteria	1.8	2.6	3.6	V	$V_{DS} = V_{GS}$, $I_D = 5 \text{ mA}$	Fi 11	
$V_{GS(th)}$	Gate Threshold Voltage		2.1		V	V _{DS} = V _{GS} , I _D = 5 mA, T _J = 175°C	5°C Fig. 11	
I _{DSS}	Zero Gate Voltage Drain Current		1	50	μA	V _{DS} = 1200 V, V _{GS} = 0 V		
I _{GSS}	Gate-Source Leakage Current		10	250	nA	V _{GS} = 15 V, V _{DS} = 0 V		
$R_{DS(on)}$	Drain-Source On-State Resistance		75	97.5	mΩ	V _{GS} = 15 V, I _D = 17.9 A	Fig. 4,	
*DS(on)	Brain Source on State Resistance		135		11122	V _{GS} = 15 V, I _D = 17.9, T _J = 175°C	5, 6	
g fs	Transconductance		11		s	V _{DS} = 20 V, I _{DS} = 17.9 A	Fig. 7	
	Transconductance		10.5		L ~	V _{DS} = 20 V, I _{DS} = 17.9 A, T _J = 175°C	1 ig. /	
C_{iss}	Input Capacitance		1480			$V_{GS} = 0 \text{ V}, V_{DS} = 0 \text{V to } 1000 \text{ V}$		
Coss	Output Capacitance		58		pF	F = 1 Mhz	Fig. 17, 18	
C _{rss}	Reverse Transfer Capacitance		2.7			Vac = 25 mV		
E _{oss}	Coss Stored Energy		32		μJ	V _{DS} = 1000 V, F = 1 Mhz	Fig. 16	
$C_{o(er)}$	Effective Output Capacitance (Energy Related)		67		pF			
$C_{o(tr)}$	Effective Output Capacitance (Time Related)		96		pF	$V_{GS} = 0 \text{ V, } V_{DS} = 0 \text{V to } 800 \text{V}$	Note: 3	
E _{on}	Turn-On Switching Energy (External Diode)		719			$V_{DS} = 800 \text{ V}, V_{GS} = -4 \text{ V}/15 \text{ V}, I_D = 20 \text{ A},$		
E _{OFF}	Turn Off Switching Energy (External Diode)		118		μJ	$R_{G(ext)} = 2.5 \Omega$, L= 135 μ H, T_J =175°C FWD = External SiC DIODE	Fig. 26	
E _{on}	Turn-On Switching Energy (Body Diode FWD)		732		$V_{DS} = 800 \text{ V}, V_{GS} = -4 \text{ V}/15 \text{ V}, I_D = 20 \text{ A},$		F: 06	
E _{OFF}	Turn-Off Switching Energy (Body Diode FWD)		125		μJ	$R_{G(ext)} = 2.5 \Omega$, L= 135 μ H, T_J =175°C FWD = Internal Body Diode	Fig. 26	
t _{d(on)}	Turn-On Delay Time		52					
t _r	Rise Time		18			$V_{DD} = 800 \text{ V}, V_{GS} = -4 \text{ V}/15 \text{ V}$ $I_D = 20 \text{ A}, R_{G(ext)} = 2.5 \Omega,$	Fig. 27,	
$t_{\text{d(off)}}$	Turn-Off Delay Time		31		ns	Timing relative to V _{DS} Inductive load	28	
t _f	Fall Time		16			- Maddive load		
$R_{G(int)}$	Internal Gate Resistance		9		Ω	f = 1 MHz, V _{AC} = 25 mV		
Q_gs	Gate to Source Charge		19			V _{DS} = 800 V, V _{GS} = -4 V/15 V		
Q_{gd}	Gate to Drain Charge		18		nC	I _D = 20 A	Fig. 12	
Q_g	Total Gate Charge		57			Per IEC60747-8-4 pg 21		

Note (3): $C_{o(er)}$, a lumped capacitance that gives same stored energy as Coss while Vds is rising from 0 to 800V $C_{o(tr)}$, a lumped capacitance that gives same charging time as Coss while Vds is rising from 0 to 800V


Reverse Diode Characteristics ($T_c = 25^{\circ}C$ unless otherwise specified)

Symbol	Parameter	Тур.	Max.	Unit	Test Conditions	Note
V	Die de Fermand Vallence	4.8		٧	$V_{GS} = -4 \text{ V, I}_{SD} = 9 \text{ A, T}_{J} = 25 \text{ °C}$	Fig. 8.
V_{SD}	Diode Forward Voltage	Forward Voltage 4.2 V	V	V _{GS} = -4 V, I _{SD} = 9 A, T _J = 175 °C	Fig. 8, 9, 10	
Is	Continuous Diode Forward Current		27	Α	V _{GS} = -4 V, T _C = 25°C	
I _{S, pulse}	Diode pulse Current		80	Α	V_{GS} = -4 V, pulse width t_P limited by T_{jmax}	
t _{rr}	Reverse Recover time	34		ns		
Q _{rr}	Reverse Recovery Charge	286		nC	$V_{GS} = -4 \text{ V, } I_{SD} = 20 \text{ A, } V_{R} = 800 \text{ V}$ dif/dt = 885 A/ μ s, T $_{J} = 175 ^{\circ}\text{C}$	
I _{rrm}	Peak Reverse Recovery Current	13		Α		
t _{rr}	Reverse Recover time	40		ns		
Q _{rr}	Reverse Recovery Charge	256		nC	V _{GS} = -4 V, I _{SD} = 20 A, V _R = 800 V dif/dt = 740 A/μs, Τ _ι = 175 °C	
I _{rrm}	Peak Reverse Recovery Current	9		А]	

Thermal Characteristics

Symbol	Parameter	Тур.	Max.	Unit	Test Conditions	Note
$R_{\theta JC}$	Thermal Resistance from Junction to Case	0.88	1.03	°C/W		Fig. 21

Typical Performance








Figure 1. Output Characteristics T_J = -55 °C









Figure 3. Output Characteristics T_J = 175 °C

Figure 4. Normalized On-Resistance vs. Temperature







Figure 5. On-Resistance vs. Drain Current For Various Temperatures

Figure 6. On-Resistance vs. Temperature For Various Gate Voltage

Typical Performance






-10

-8

Drain-Source Current, I_{DS} (A)



0 -10 Drain-Source Current, I_{DS} (A) $V_{GS} = 0 V$ -20 V_{GS} = -2 V -30 -40 -50 -60 Conditions: $T_j = 175$ °C $t_p < 200 \mu s$ -70 -80 Drain-Source Voltage V_{DS} (V)

Figure 10. Body Diode Characteristic at 175 °C

Drain-Source Voltage V_{DS} (V)

-4

-6

0

-10

-20

-30

-40

-50

-60

-70

-80


0

T_j = -55°C

t_p < 200 μs

-2

Figure 9. Body Diode Characteristic at 25 °C




4.0 Conditons $V_{GS} = V_{DS}$ 3.5 I_{DS} = 5 mA Threshold Voltage, V_{th} (V) 1.0 0.5 0.0 -50 -25 175 Junction Temperature T, (°C)

Figure 11. Threshold Voltage vs. Temperature

Figure 12. Gate Charge Characteristics

Typical Performance






Figure 15. 3rd Quadrant Characteristic at 175 °C

Drain-Source Voltage V_{DS} (V)





Figure 17. Capacitances vs. Drain-Source Voltage (0 - 200V)



6

Figure 14. 3rd Quadrant Characteristic at 25 °C




Figure 16. Output Capacitor Stored Energy





Figure 18. Capacitances vs. Drain-Source Voltage (0 - 1200V)

t_o < 200 μs

Typical Performance







Figure 19. Continuous Drain Current Derating vs.

Case Temperature

Figure 20. Maximum Power Dissipation Derating vs.

Case Temperature







Figure 21. Transient Thermal Impedance (Junction - Case)

Figure 22. Safe Operating Area






Figure 23. Clamped Inductive Switching Energy vs. Drain Current (V_{DD} = 600V)

Figure 24. Clamped Inductive Switching Energy vs. Drain Current (V_{DD} = 800V)

Typical Performance




Figure 25. Clamped Inductive Switching Energy vs. $R_{G(ext)}$




Figure 27. Switching Times vs. $R_{G(ext)}$




Figure 26. Clamped Inductive Switching Energy vs.
Temperature




Figure 28. Switching Times Definition

9

Test Circuit Schematic






Figure 29. Clamped Inductive Switching Waveform Test Circuit

Package Dimensions





SYMBOL	MIN (mm)	MAX (mm)			
A	4.83	5.21			
A1	2.29	2.54			
A2	1.91	2.16			
ь	1.07	1.33			
b1	1.91	2.41			
b3	2.87	3.38			
c	0.55	0.68			
D	20.8	21.1			
D1	16.25	17.65			
D2	0.95	1.25			
E	15.75	16.13			
E1	13.1	14.15			
E2	3.68	5.1			
E3	1	1.9			
E4	12.38	13.43			
e	5.44 BSC				
L	19.81	20.32			
L1	4.1	4.4			
ØΡ	3.51	3.65			
Q	5.49	6			
S	6.04	6.3			
T	17.5° REF.				
W	3.5° REF.				
X	4° REF.				


1	GATE	
2	DRAIN	
3	SOURCE	
4	DRAIN	

NOTES

- 1. ALL METAL SURFACES ARE TIN PLATED (MATTE), EXCEPT AREA OF CUT.
- 2. DIMENSIONING & TOLERANCING CONFORM TO ASME Y14.5M-1994.
- 3. ALL DIMENSIONS ARE LISTED IN MILLIMETERS, ANGLES ARE IN DEGREES.
- 4. BURR OR MOLD FLASH SIZE (0.5 mm) IS NOT INCLUDED IN THE DIMENSIONS

Recommended Solder Pad Layout

All dimensions in mm



TO-247-3

Revision history

Document Version	Date of release	Descriptiion of changes
2.0	July-2021	Initial datasheet
3.0	November-2023	Updated format and logo to Wolfspeed

E3M0075120D 1.

Notes & Disclaimer

This document and the information contained herein are subject to change without notice. Any such change shall be evidenced by the publication of an updated version of this document by Wolfspeed. No communication from any employee or agent of Wolfspeed or any third party shall effect an amendment or modification of this document. No responsibility is assumed by Wolfspeed for any infringement of patents or other rights of third parties which may result from use of the information contained herein. No license is granted by implication or otherwise under any patent or patent rights of Wolfspeed.

Notwithstanding any application-specific information, guidance, assistance, or support that Wolfspeed may provide, the buyer of this product is solely responsible for determining the suitability of this product for the buyer's purposes, including without limitation for use in the applications identified in the next bullet point, and for the compliance of the buyers' products, including those that incorporate this product, with all applicable legal, regulatory, and safety-related requirements.

This product has not been designed or tested for use in, and is not intended for use in, applications in which failure of the product would reasonably be expected to cause death, personal injury, or property damage, including but not limited to equipment implanted into the human body, life-support machines, cardiac defibrillators, and similar emergency medical equipment, aircraft navigation, communication, and control systems, aircraft power and propulsion systems, air traffic control systems, and equipment used in the planning, construction, maintenance, or operation of nuclear facilities.

RoHS Compliance

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS2), as implemented January 2, 2013. RoHS Declarations for this product can be obtained from your Wolfspeed representative or from the Product Documentation sections of www.wolfspeed. com.

REACh Compliance

REACh substances of high concern (SVHCs) information is available for this product. Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact your Wolfspeed representative to ensure you get the most up-to-date REACh SVHC Declaration. REACh banned substance information (REACh Article 67) is also available upon request.

Contact info:

4600 Silicon Drive Durham, NC 27703 USA Tel: +1.919.313.5300 www.wolfspeed.com/power

© 2023 Wolfspeed, Inc. All rights reserved. Wolfspeed® and the Wolfstreak logo are registered trademarks and the Wolfspeed logo is a trademark of Wolfspeed, Inc. PATENT: https://www.wolfspeed.com/legal/patents

The information in this document is subject to change without notice.