


1700 V, 8.0 mΩ, Silicon Carbide, Half-Bridge Module

| V_{DS} | 1700 V |
|----------|--------|
| I_{DS} | 300 A |

Technical Features

- Industry Standard 62 mm Footprint
- Ultra Low Loss, High-Frequency Operation
- Zero Reverse Recovery from Diodes
- Zero Turn-off Tail Current from MOSFET
- Normally-off, Fail-safe Device Operation
- Copper Baseplate and Aluminum Nitride Insulator





Applications

- HF Resonant Converters/Inverters
- Solar and Wind Inverters
- UPS and SMPS
- Motor Drive
- Traction

System Benefits

- Enables Compact and Lightweight Systems
- High Efficiency Operation
- Mitigates Over-voltage Protection
- Reduced Thermal Requirements
- Reduced System Cost

Key Parameters

| Parameter | Symbol | Min. | Тур. | Max. | Unit | Conditions | Note |
|--|----------------------|------|--------|------|---|---|-------------------|
| Drain-Source Voltage | V _{DS} | | | 1700 | | T _c = 25 °C | |
| Gate-Source Voltage, Maximum Value | V _{GS(max)} | -10 | | +25 | V | Transient | Note 1 |
| Gate-Source Voltage, Recommended | $V_{GS(op)}$ | | -5/+20 | | | Static | Fig. 33 |
| DC Continuous Drain Current | I _D | | 325 | | | $V_{GS} = 20 \text{ V}, T_C = 25 \text{ °C}, T_{VJ} \le 150 \text{ °C}$ | |
| | | 225 | | | $V_{GS} = 20 \text{ V}, T_C = 90 \text{ °C}, T_{VJ} \le 150 \text{ °C}$ | Notes | |
| DC Source-Drain Current (Schottky Diode) | I _{SD(SD)} | | 556 | | Α | $V_{GS} = -5 \text{ V}, T_C = 25 \text{ °C}, T_{VJ} \le 150 \text{ °C}$ | 2, 3 Fig. 21 |
| Pulsed Drain-Source Current | I _{DM} | | 900 | | | t_{Pmax} limited by T_{VJmax} $V_{GS} = 20 \text{ V}, T_C = 25 ^{\circ}\text{C}$ | |
| Power Dissipation | P _D | | 1866 | | W | $T_{\rm C} = 25 {\rm ^{\circ}C}, T_{\rm VJ} \leq 150 {\rm ^{\circ}C}$ | Note 4 Fig. 21 |
| Virtual Junction Temperature | T _{VJ(op)} | -40 | | 150 | °C | Operation | |

Note (1): Recommended turn-on gate voltage is 20 V with ±5 % regulation tolerance

Note (2): Current limit at $T_C = 90$ °C calculated by $I_{D(max)} = \sqrt{(P_D/R_{DS(typ)}(T_{VJ(max)},I_{D(max)}))}$

Note (3): Verified by design

Note (4): $P_D = (T_{VJ} - T_C)/R_{TH(JC,typ)}$

MOSFET Characteristics (Per Position) ($T_{VJ} = 25$ °C Unless Otherwise Specified)

| Parameter | Symbol | Min. | Тур. | Max. | Unit | Conditions | Note |
|--|----------------------|------|-------|-------|------|--|----------------------------|
| Drain-Source Breakdown Voltage | V _{(BR)DSS} | 1700 | | | V | V _{GS} = 0 V, I _{DS} = 2 mA | Fig. 29 |
| Gate Threshold Voltage | V _{GS(th)} | 1.8 | 2.5 | | | $V_{DS} = V_{GS}$, $I_{DS} = 104 \text{ mA}$ | Fig. 7 |
| | | | 0.7 | 2 | | V _{GS} = 0 V, V _{DS} = 1700 V | |
| Zero Gate Voltage Drain Current | I _{DSS} | | 1.5 | 4 | mA | V _{GS} = 0 V, V _{DS} = 1700 V, T _{VJ} = 150 °C | |
| Gate-Source Leakage Current | I _{GSS} | | 1 | 600 | nA | V _{GS} = 25 V, V _{DS} = 0 V | |
| Drain-Source On-State Resistance | _ | | 8.0 | 10.0 | | V _{GS} = 20 V, I _D = 300 A | Fig. 4 Fig. 5 Fig. 6 |
| (MOSFET Only) | R _{DS(on)} | | 16.2 | 20.0 | mΩ | V _{GS} = 20 V, I _D = 300 A, T _{VJ} = 150 °C | |
| | | | 133 | | | V _{DS} = 20 V, I _D = 300 A | Fig. 8 |
| Transconductance | g fs | | 131 | | S | V _{DS} = 20 V, I _D = 300 A, T _{VJ} = 150 °C | |
| Turn-On Switching Energy | E _{on} | | 13.0 | | ! | $V_{DD} = 900 \text{ V}, I_D = 300 \text{ A},$ $V_{GS} = -5 \text{ V}/+20 \text{ V},$ $R_{G(ON)} = 2.5 \Omega, R_{G(OFF)} = 2.5 \Omega,$ | Fig. 22 |
| Turn-Off Switching Energy | E _{OFF} | | 10.0 | | - mJ | L = 77 μH T _{vJ} = 150 °C Note: IEC 60747-8-4 Definitions | |
| Internal Gate Resistance | R _{G(int)} | | 3.7 | | Ω | f = 100 kHz, V _{AC} = 25 mV | |
| Input Capacitance | C _{iss} | | 20 | | _ | V _{DS} = 1000 V, V _{AC} = 25 mV f = 100 kHz | Fig. 16 Fig. 17 |
| Output Capacitance | C _{oss} | | 2.5 | | nF | | |
| Reverse Transfer Capacitance | C _{rss} | | 80 | | pF | | |
| Gate to Source Charge | Q _{GS} | | 273 | | | $V_{DS} = 900 \text{ V}, V_{GS} = -5 \text{ V}/+20 \text{ V},$ $I_{D} = 300 \text{ A}, \text{ Per JEDED24 pg 27}$ | Fig. 15 |
| Gate to Drain Charge | $Q_{\sf GD}$ | | 324 | | nC | | |
| Total Gate Charge | Q _G | | 1076 | | | | |
| Turn-On Delay Time | t _{d(on)} | | 105 | | | $V_{DD} = 900 \text{ V}, V_{GS} = -5/+20 \text{ V}, \\ I_{D} = 300 \text{ A}, R_{G(ext)} = 2.5 \Omega, \\ Timing Relative to V_{DS} \\ Note: IEC 60747-8-4, pg 83$ | |
| Rise Time | t _r | | 72 | | ns | | |
| Turn-Off Delay Time | t _{d(off)} | | 211 | | | | Fig. 23 |
| Fall Time | t _f | | 56 | | | Inductive Load | |
| FET Thermal Resistance, Junction to Case | R _{th-JCM} | | 0.067 | 0.071 | °C/W | | Fig. 27 |

Diode Characteristics (Per Position) (T_{VJ} = 25 °C Unless Otherwise Specified)

| Parameter | Symbol | Min. | Тур. | Max. | Unit | Test Conditions | Note |
|--|---------------------|------|-------|-----------|------|--|--------------------|
| D 1 D: 1 5 1 V I | | | 1.7 | 2.0 | V | V _{GS} = 0 V, I _{SD} = 300 A | Fig. 10 Fig. 11 |
| Body Diode Forward Voltage | V _{SD} | | 2.2 | 2.2 2.5 V | V | V _{GS} = 0 V, I _{SD} = 300 A, T _{VJ} = 150 °C | |
| Total Capacitive Charge | Qc | | 4.4 | | μС | $I_{SD} = 300 \text{ A}, V_{DS} = 900 \text{ V}, T_{VJ} = 25^{\circ} \text{ C},$ $di_{SD}/dt = 9 \text{ kA}/\mu\text{s}, V_{GS} = -5 \text{ V}$ | |
| DIODE Thermal Resistance, Junction to Case | R _{th-JCD} | | 0.060 | 0.065 | °C/W | | Fig. 28 |

Module Physical Characteristics

| Parameter | Symbol | Min. | Тур. | Max. | Unit | Test Conditions |
|------------------------|--------------------|------|------|------|------|---------------------------|
| Stray Inductance | L _{Stray} | | 15 | | nH | Between Terminals 2 & 3 |
| Case Temperature | T _c | -40 | | 125 | °C | |
| Mounting Torque | Ms | | 5.0 | | N-m | To Heatsink and Terminals |
| Weight | W | | 300 | | g | |
| Case Isolation Voltage | V _{Isol} | 5.0 | | | kV | AC, 50 Hz, 1 minute |
| Clearance Distance | | 9 | | | | Terminal to Terminal |
| Creepage Distance | | 30 | | | mm | Terminal to Terminal |
| | | 40 | | | | Terminal to Baseplate |




Figure 1. Output Characteristics for T_{VJ} = 40 °C




Figure 3. Output Characteristics for $T_{VJ} = 150 \, ^{\circ}\text{C}$




Figure 5. On-Resistance vs. Drain Current For Various Temperatures




Figure 2. Output Characteristics for $T_{VJ} = 25 \,^{\circ}\text{C}$




Figure 4. Normalized On-Resistance vs. Temperature




Figure 6. On-Resistance vs. Temperature for Various Gate-Source Voltage

5




Figure 7. Threshold Voltage vs. Temperature




Figure 9. Diode Characteristic at $T_{VJ} = -40 \, ^{\circ}\text{C}$




Figure 11. Diode Characteristic at T_{VJ} = 150 °C




Figure 8. Transfer Characteristic for Various Junction Temperatures




Figure 10. Diode Characteristic at T_{VJ} = 25 °C




Figure 12. 3^{rd} Quadrant Characteristic at $T_{VJ} = -40$ °C




Figure 13. 3^{rd} Quadrant Characteristic at $T_{VJ} = 25$ °C




Figure 15. Gate Charge Characteristics




Figure 17. Capacitances vs. Drain-Source Voltage (0 - 1 kV)




Figure 14. 3rd Quadrant Characteristic at T_{VJ} = 150 °C




Figure 16. Capacitances vs. Drain-Source Voltage (0 - 200 V)




Figure 18. Output Capacitor Stored Energy




Figure 19. Inductive Switching Energy vs. Drain Current For V_{DS} = 900 V, R_G = 2.5 Ω




Figure 21. Inductive Switching Energy vs. $R_{G(ext)}$




Figure 23. Timing vs. R_{G(ext)}




Figure 20. Inductive Switching Energy vs. Drain Current For V_{DS} = 1200 V, R_G = 2.5 Ω




Figure 22. Inductive Switching Energy vs. Temperature




Figure 24. Resistive Switching Time Description

Timing Characteristics




Figure 25. Maximum Power Dissipation (MOSFET) Derating vs. Case Temperature




Figure 27. MOSFET Junction to Case Thermal Impedance




Figure 29. Safe Operating Area




Figure 26. Continuous Drain Current Derating vs. Case Temperature






Figure 28. Diode Junction to Case Thermal Impedance


9

Schematic



Package Dimension (mm)





Supporting Links & Tools

Evaluation Tools & Support

- KIT-CRD-CIL17N-BM: Dynamic Performance Evaluation Board for the 62 mm Module
- SpeedFit 2.0 Design Simulator™
- <u>Technical Support Forum</u>

Dual-Channel Gate Driver Board

- CGD1700HB2P-BM2: Dual Channel Differential Isolated Half Bridge Gate Driver Board
- CGD12HB00D: Differential Transceiver Daughter Board Companion Tool for Differential Gate Drivers

Application Notes

- 62 mm Module Mounting Guide
- 62 mm Module Thermal Interface Material Guide

Notes & Disclaimer

This document and the information contained herein are subject to change without notice. Any such change shall be evidenced by the publication of an updated version of this document by Wolfspeed. No communication from any employee or agent of Wolfspeed or any third party shall effect an amendment or modification of this document. No responsibility is assumed by Wolfspeed for any infringement of patents or other rights of third parties which may result from use of the information contained herein. No license is granted by implication or otherwise under any patent or patent rights of Wolfspeed.

Notwithstanding any application-specific information, guidance, assistance, or support that Wolfspeed may provide, the buyer of this product is solely responsible for determining the suitability of this product for the buyer's purposes, including without limitation for use in the applications identified in the next bullet point, and for the compliance of the buyers' products, including those that incorporate this product, with all applicable legal, regulatory, and safety-related requirements.

This product has not been designed or tested for use in, and is not intended for use in, applications in which failure of the product would reasonably be expected to cause death, personal injury, or property damage, including but not limited to equipment implanted into the human body, life-support machines, cardiac defibrillators, and similar emergency medical equipment, aircraft navigation, communication, and control systems, air craft power and propulsion systems, air traffic control systems, and equipment used in the planning, construction, maintenance, or operation of nuclear facilities.

RoHS Compliance

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS2), as implemented January 2, 2013. RoHS Declarations for this product can be obtained from your Wolfspeed representative or from the Product Documentation sections of www.wolfspeed.com.

REACh Compliance

REACh substances of high concern (SVHCs) information is available for this product. Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact your Wolfspeed representative to ensure you get the most up-to-date REACh SVHC Declaration. REACh banned substance information (REACh Article 67) is also available upon request.

Contact info:

4600 Silicon Drive Durham, NC 27703 USA Tel: +1.919.313.5300 www.wolfspeed.com/power

© 2024 Wolfspeed, Inc. All rights reserved. Wolfspeed® and the Wolfstreak logo are registered trademarks and the Wolfspeed logo is a trademark of Wolfspeed, Inc. PATENT: https://www.wolfspeed.com/legal/patents

The information in this document is subject to change without notice.