

Silicon Carbide Power MOSFET E-Series Automotive N-Channel Enhancement Mode

Features

- Optimized package with separate driver source pin
- High blocking voltage with low on-resistance
- High-speed switching with low capacitances
- Fast intrinsic diode with low reverse recovery (Q_r)
- · Halogen free, RoHS compliant
- Automotive Qualified (AEC-Q101) and PPAP Capable


Benefits

- · Reduce switching losses and minimize gate ringing
- · Higher system efficiency
- · Reduce cooling requirements
- Increase power density
- Increase system switching frequency

Applications

- Motor Control
- EV Battery Chargers
- High Voltage DC/DC Converters

Package





Halogen-Free	RoHS
Drain (Pin 1, TAB)	
Gate (Pin 4) Driver Source Source (Pin 3)	

Part Number	Package	Marking
E4M0015075K1	TO-247-4L	E4M0015075K1

Maximum Ratings (T_c = 25 °C unless otherwise specified)

Symbol	Parameter	Value	Unit	Note	
V _{DSmax}	Drain - Source Voltage		750	٧	
V_{GSmax}	Gate - Source Voltage		-8/+19	V	Note: 1
	Continuous Drain Current, $V_{GS} = 15 \text{ V}$ $T_C = 2$ $T_C = 10$		128		Fig. 19 Note: 2
l _D			95		
I _{D(pulse)}	Pulsed Drain Current, Pulse width t _P limited by T _{jmax}	418	А	Fig. 22	
P _D	Power Dissipation, $T_c = 25^{\circ}C$, $T_J = 175^{\circ}C$	372	W	Fig. 20 Note: 2	
T_J , T_stg	Operating Junction and Storage Temperature	-40 to +175	°C		
T _L	Solder Temperature, 1.6mm (0.063") from case for 10s	260	°C		
M_d	Mounting Torque , M3 or 6-32 screw	1 8.8	Nm lbf-in		

Note (1): Recommended turn off / turn on gate voltage $V_{\rm GS}$ - 4V...0V / +15V

Note (2): Verified by design

Electrical Characteristics ($T_c = 25^{\circ}C$ unless otherwise specified)

Symbol	Parameter	Min.	Тур.	Max.	Unit	Test Conditions	Note	
$V_{(BR)DSS}$	Drain-Source Breakdown Voltage	750			V	V _{GS} = 0 V, I _D = 100 μA		
V	Cota Throphold Voltage		2.6	3.8	V	V _{DS} = V _{GS} , I _D = 15.4 mA	Fig. 11	
$V_{GS(th)}$	Gate Threshold Voltage		2.0		V	V _{DS} = V _{GS} , I _D = 15.4 mA, T _J = 175°C	Fig. 11	
I _{DSS}	Zero Gate Voltage Drain Current		1	50	μA	V _{DS} = 750 V, V _{GS} = 0 V		
I_{GSS}	Gate-Source Leakage Current		10	250	nA	V _{GS} = 15 V, V _{DS} = 0 V		
R _{DS(on)}	Drain-Source On-State Resistance		15	21	mΩ	V _{GS} = 15 V, I _D = 55.8 A	Fig. 4,	
**DS(on)	Brain course on state resistance		22	ļ	11112	$V_{GS} = 15 \text{ V}, I_D = 55.8 \text{ A}, T_J = 175^{\circ}\text{C}$	5, 6	
g fs	Transconductance		42		S	V _{DS} = 20 V, I _{DS} = 55.8 A	Fig. 7	
919			42	ļ		V _{DS} = 20 V, I _{DS} = 55.8 A, T _J = 175°C	1	
C_{iss}	Input Capacitance		5128					
C_{oss}	Output Capacitance		255		pF	$V_{GS} = 0 \text{ V}, V_{DS} = 0 \text{V to } 500 \text{ V}$	Fig. 17,	
C _{rss}	Reverse Transfer Capacitance		23		1	F = 100 kHz	10	
Eoss	Coss Stored Energy		45	 	μJ	V _{AC} = 25 mV	Fig. 16	
	37			1	 		Fig. 10	
C _{o(er)}	Effective Output Capacitance (Energy Related)		326		pF	V _{GS} = 0 V, V _{DS} = 0 500V	Note: 3	
$C_{o(tr)}$	Effective Output Capacitance (Time Related)		469		pF			
Eon	Turn-On Switching Energy (External Diode)		258			V_{DS} = 500 V, V_{GS} = -4 V/15 V, I_{D} = 55.8 A, $R_{G(ext)}$ = 2.5 Ω , L= 59 μ H, T_{J} = 175°C	Fig. 26,	
E _{OFF}	Turn Off Switching Energy (External Diode)		203		μJ	FWD = External SiC DIODE	28	
Eon	Turn-On Switching Energy (Body Diode FWD)		374			$V_{DS} = 500 \text{ V}, V_{GS} = -4 \text{ V}/15 \text{ V}, I_{D} = 55.8 \text{ A},$ $R_{G(ext)} = 2.5 \Omega, L = 59 \mu\text{H}, T_{J} = 175^{\circ}\text{C}$	Fig. 26,	
E _{OFF}	Turn-Off Switching Energy (Body Diode FWD)		178		μJ	FWD = Internal Body Diode	28	
t _{d(on)}	Turn-On Delay Time		16					
t _r	Rise Time		23]	V_{DD} = 500 V, V_{GS} = -4 V/15 V I_D = 55.8 A, $R_{G(ext)}$ = 2.5 Ω ,	Fig. 27,	
t _{d(off)}	Turn-Off Delay Time		42		ns	Timing relative to V _{DS}	28	
t _f	Fall Time		12			maddive load		
$R_{G(int)}$	Internal Gate Resistance		2.1		Ω	f = 1 MHz, V _{AC} = 25 mV		
Q_{gs}	Gate to Source Charge		51			V _{DS} = 500 V, V _{GS} = -4 V/15 V		
Q_{gd}	Gate to Drain Charge		58]	nC	I _D = 55.8 A	Fig. 12	
Q_g	Total Gate Charge		191			Per IEC60747-8-4 pg 21		


Note (3): $C_{\circ(er)}$, a lumped capacitance that gives same stored energy as Coss while Vds is rising from 0 to 500V $C_{\circ(tr)}$, a lumped capacitance that gives same charging time as Coss while Vds is rising from 0 to 500V

Reverse Diode Characteristics ($T_c = 25^{\circ}C$ unless otherwise specified)

Symbol	Parameter	Тур.	Max.	Unit	Test Conditions	Note
V		4.9		٧	V_{GS} = -4 V, I_{SD} = 27.9 A, T_{J} = 25 °C	Fig. 8,
V _{SD}	Diode Forward Voltage	4.4		٧	V _{GS} = -4 V, I _{SD} = 27.9 A, T _J = 175 °C	9,10
Is	Continuous Diode Forward Current		67	Α	V _{GS} = -4 V, T _C = 25°C	
I _{S, pulse}	Diode pulse Current		418.5	Α	$V_{GS} = -4 \text{ V}$, pulse width t_P limited by T_{jmax}	
t _{rr}	Reverse Recover time	23		ns		
Q _{rr}	Reverse Recovery Charge	1017		nC	V _{SS} = -4 V, I _{SD} = 55.8 A, V _R = 500 V dif/dt = 7590 A/μs, T ₁ = 175 °C	
I _{rrm}	Peak Reverse Recovery Current	75		А		
t _{rr}	Reverse Recover time	29		ns		
Q _{rr}	Reverse Recovery Charge	619		nC	V _{GS} = -4 V, I _{SD} = 55.8 A, V _R = 500 V dif/dt = 2620 A/µs, T ₁ = 175 °C	
l _{rrm}	Peak Reverse Recovery Current	36		А		

Thermal Characteristics

Symbol	Parameter	Тур.	Max.	Unit	Test Conditions	Note
$R_{\theta JC}$	Thermal Resistance from Junction to Case	0.29	0.4	°C/W		Fig. 21







Figure 1. Output Characteristics T_J = -55 °C

Figure 2. Output Characteristics T_J = 25 °C







Figure 3. Output Characteristics T_J = 175 °C

Figure 4. Normalized On-Resistance vs. Temperature






Figure 5. On-Resistance vs. Drain Current For Various Temperatures

Figure 6. On-Resistance vs. Temperature For Various Gate Voltage




Figure 7. Transfer Characteristic for Various Junction Temperatures




Figure 8. Body Diode Characteristic at -55 °C




Figure 9. Body Diode Characteristic at 25 °C




Figure 10. Body Diode Characteristic at 175 °C




Figure 11. Threshold Voltage vs. Temperature





Figure 12. Gate Charge Characteristics







Figure 13. 3rd Quadrant Characteristic at -55 °C

Figure 14. 3rd Quadrant Characteristic at 25 °C







Figure 15. 3rd Quadrant Characteristic at 175 °C

Figure 16. Output Capacitor Stored Energy







Figure 17. Capacitances vs. Drain-Source Voltage (0 - 200V)

Figure 18. Capacitances vs. Drain-Source Voltage (0 - 750V)

400




Conditions T_J ≤ 175 °C 350 Maximum Dissipated Power, P_{tot} (W) 300 250 200 150 100 50 -25 75 175 -50 25 50 100 125 150 Case Temperature, T_C (°C)

Figure 19. Continuous Drain Current Derating vs.

Case Temperature

Figure 20. Maximum Power Dissipation Derating vs.
Case Temperature







Figure 21. Transient Thermal Impedance (Junction - Case)

Figure 22. Safe Operating Area






Figure 23. Clamped Inductive Switching Energy vs. Drain Current (V_{DD} = 500V)

Figure 24. Clamped Inductive Switching Energy vs. Drain Current (V_{DD} = 500V)




Figure 25. Clamped Inductive Switching Energy vs. $R_{G(ext)}$




Figure 27. Switching Times vs. $R_{G(ext)}$




Figure 26. Clamped Inductive Switching Energy vs. Temperature




Figure 28. Switching Times Definition

Test Circuit Schematic





Figure 29. Clamped Inductive Switching Waveform Test Circuit

Package Dimensions



SYMBOL	MIN (mm)	MAX (mm)		
A	4.83	5.21		
A1	2.22	2.6		
A2	1.91	2.16		
b	1.10	1.30		
b1	0.65	0.79		
b3	1.34	1.44		
С	0.55	0.68		
D	20.76	21.14		
D1	16.25	17.65		
D2	0.92	1.42		
Е	15.75	16.13		
E1	13.1	14.15		
E2	3.68	5.10		
E3	1.00	1.90		
E4	12.38	13.43		
e1	5.08 BSC			
e2	2.79 BSC			
e3	2.54	BSC		
L	19.72	20.32		
L1	3.87	4.47		
ØΡ	3.51	3.65		
Q	5.49	6.00		
S	6.04 6.30			
T	17.5° REF.			
W	3.5 ° REF.			
X	4° REF.			


1	DRAIN
2	SOURCE
3	SOURCE
4	GATE
5	DRAIN

NOTE:

- 1. ALL METAL SURFACES ARE TIN PLATED (MATTE), EXCEPT AREA OF CUT.
- DIMENSIONING & TOLERANCING CONFORM TO ASME Y14.5M-1994.
- 3. ALL DIMENSIONS ARE LISTED IN MILLIMETERS. ANGLES ARE IN DEGREES.
- 4. BURR OR MOLD FLASH SIZE (0.5 mm) IS NOT INCLUDED IN THE DIMENSIONS

Recommended Solder Pad Layout

All dimensions in mm



Revision history

Document Version	Date of release	Descriptiion of changes
1.0	November-2023	Initial datasheet
2.0	January-2024	Corrected typo on Temperature range

Notes & Disclaimer

This document and the information contained herein are subject to change without notice. Any such change shall be evidenced by the publication of an updated version of this document by Wolfspeed. No communication from any employee or agent of Wolfspeed or any third party shall effect an amendment or modification of this document. No responsibility is assumed by Wolfspeed for any infringement of patents or other rights of third parties which may result from use of the information contained herein. No license is granted by implication or otherwise under any patent or patent rights of Wolfspeed.

Notwithstanding any application-specific information, guidance, assistance, or support that Wolfspeed may provide, the buyer of this product is solely responsible for determining the suitability of this product for the buyer's purposes, including without limitation for use in the applications identified in the next bullet point, and for the compliance of the buyers' products, including those that incorporate this product, with all applicable legal, regulatory, and safety-related requirements.

This product has not been designed or tested for use in, and is not intended for use in, applications in which failure of the product would reasonably be expected to cause death, personal injury, or property damage, including but not limited to equipment implanted into the human body, life-support machines, cardiac defibrillators, and similar emergency medical equipment, aircraft navigation, communication, and control systems, aircraft power and propulsion systems, air traffic control systems, and equipment used in the planning, construction, maintenance, or operation of nuclear facilities.

RoHS Compliance

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS2), as implemented January 2, 2013. RoHS Declarations for this product can be obtained from your Wolfspeed representative or from the Product Documentation sections of www.wolfspeed. com.

REACh Compliance

REACh substances of high concern (SVHCs) information is available for this product. Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact your Wolfspeed representative to ensure you get the most up-to-date REACh SVHC Declaration. REACh banned substance information (REACh Article 67) is also available upon request.

Contact info:

4600 Silicon Drive Durham, NC 27703 USA Tel: +1.919.313.5300 www.wolfspeed.com/power

© 2024 Wolfspeed, Inc. All rights reserved. Wolfspeed® and the Wolfstreak logo are registered trademarks and the Wolfspeed logo is a trademark of Wolfspeed, Inc. PATENT: https://www.wolfspeed.com/legal/patents

 ${\it The information in this document is subject to change without notice}.$