

E4M0013120K

Silicon Carbide Power MOSFET
E-Series Automotive
N-Channel Enhancement Mode

Features

- E4M generation SiC MOSFET technology
- Optimized package with separate driver source pin
- 8mm of creepage distance between drain and source
- High blocking voltage with low on-resistance
- High-speed switching with low capacitances
- Fast intrinsic diode with low reverse recovery (Q_{rr})
- Halogen free, RoHS compliant
- Automotive Qualified (AEC-Q101) and PPAP Capable


Benefits

- Reduce switching losses and minimize gate ringing
- Higher system efficiency
- Reduce cooling requirements
- Increase power density
- Increase system switching frequency

Applications

- Motor Control
- EV Battery Chargers
- High Voltage DC/DC Converters

Package



Part Number	Package	Marking
E4M0013120K	TO-247-4L	E4M0013120K

Maximum Ratings ($T_c = 25^\circ\text{C}$ unless otherwise specified)

Symbol	Parameter	Value	Unit	Note
V_{DSmax}	Drain - Source Voltage	1200	V	
V_{GSmax}	Gate - Source Voltage	-8/+19	V	Note: 1
I_D	Continuous Drain Current, $V_{GS} = 15\text{ V}$	$T_c = 25^\circ\text{C}$	153	A Fig. 19 Note: 2
		$T_c = 100^\circ\text{C}$	107	
$I_{D(pulse)}$	Pulsed Drain Current, Pulse width t_p limited by T_{jmax}	337	A	Fig. 22
P_D	Power Dissipation, $T_c=25^\circ\text{C}$, $T_j = 175^\circ\text{C}$	517	W	Fig. 20 Note: 2
T_j, T_{stg}	Operating Junction and Storage Temperature	-55 to +175	$^\circ\text{C}$	
T_L	Solder Temperature, 1.6mm (0.063") from case for 10s	260	$^\circ\text{C}$	
M_d	Mounting Torque , M3 or 6-32 screw	1	Nm	
		8.8	lbf-in	

Note (1): Recommended turn off / turn on gate voltage $V_{GS} = -4V...0V / +15V$

Note (2): Verified by design


Electrical Characteristics ($T_c = 25^\circ\text{C}$ unless otherwise specified)

Symbol	Parameter	Min.	Typ.	Max.	Unit	Test Conditions	Note
$V_{(BR)DSS}$	Drain-Source Breakdown Voltage	1200			V	$V_{GS} = 0\text{ V}, I_D = 100\text{ }\mu\text{A}$	
$V_{GS(th)}$	Gate Threshold Voltage	1.8	2.5	3.8	V	$V_{DS} = V_{GS}, I_D = 23.18\text{ mA}$	Fig. 11
			2.0		V	$V_{DS} = V_{GS}, I_D = 23.18\text{ mA}, T_J = 175^\circ\text{C}$	
I_{DSS}	Zero Gate Voltage Drain Current		1	50	μA	$V_{DS} = 1200\text{ V}, V_{GS} = 0\text{ V}$	
I_{GSS}	Gate-Source Leakage Current		10	250	nA	$V_{GS} = 15\text{ V}, V_{DS} = 0\text{ V}$	
$R_{DS(on)}$	Drain-Source On-State Resistance		13	17	m Ω	$V_{GS} = 15\text{ V}, I_D = 84.29\text{ A}$	Fig. 4, 5, 6
			23			$V_{GS} = 15\text{ V}, I_D = 84.29\text{ A}, T_J = 175^\circ\text{C}$	
g_{fs}	Transconductance		62		S	$V_{DS} = 20\text{ V}, I_{DS} = 84.29\text{ A}$	Fig. 7
			58			$V_{DS} = 20\text{ V}, I_{DS} = 84.29\text{ A}, T_J = 175^\circ\text{C}$	
C_{iss}	Input Capacitance		7407		pF	$V_{GS} = 0\text{ V}, V_{DS} = 0\text{ V to }1000\text{ V}$ $F = 100\text{ kHz}$ $V_{AC} = 25\text{ mV}$	Fig. 17, 18
C_{oss}	Output Capacitance		202				
C_{rss}	Reverse Transfer Capacitance		21				
E_{oss}	C_{oss} Stored Energy		130		μJ		Fig. 16
$C_{o(er)}$	Effective Output Capacitance (Energy Related)		288		pF	$V_{GS} = 0\text{ V}, V_{DS} = 0\text{... }800\text{ V}$	Note: 3
$C_{o(tr)}$	Effective Output Capacitance (Time Related)		458		pF		
E_{ON}	Turn-On Switching Energy (External Diode)		1724		μJ	$V_{DS} = 800\text{ V}, V_{GS} = -4\text{ V}/15\text{ V}, I_D = 84.29\text{ A},$ $R_{G(ext)} = 2.5\text{ }\Omega, L = 99\text{ }\mu\text{H}, T_J = 175^\circ\text{C}$ FWD = External SiC DIODE	Fig. 26, 28
E_{OFF}	Turn Off Switching Energy (External Diode)		2687				
E_{ON}	Turn-On Switching Energy (Body Diode FWD)		2937		μJ	$V_{DS} = 800\text{ V}, V_{GS} = -4\text{ V}/15\text{ V}, I_D = 84.29\text{ A},$ $R_{G(ext)} = 2.5\text{ }\Omega, L = 99\text{ }\mu\text{H}, T_J = 175^\circ\text{C}$ FWD = Internal Body Diode	Fig. 26, 28
E_{OFF}	Turn-Off Switching Energy (Body Diode FWD)		2637				
$t_{d(on)}$	Turn-On Delay Time		12		ns	$V_{DD} = 800\text{ V}, V_{GS} = -4\text{ V}/15\text{ V}$ $I_D = 84.29\text{ A}, R_{G(ext)} = 2.5\text{ }\Omega,$ Timing relative to V_{DS} Inductive load	Fig. 27, 28
t_r	Rise Time		67				
$t_{d(off)}$	Turn-Off Delay Time		166				
t_f	Fall Time		37				
$R_{G(int)}$	Internal Gate Resistance		7.8		Ω	$f = 1\text{ MHz}, V_{AC} = 25\text{ mV}$	
Q_{gs}	Gate to Source Charge		76		nC	$V_{DS} = 800\text{ V}, V_{GS} = -4\text{ V}/15\text{ V}$ $I_D = 84.29\text{ A}$ Per IEC60747-8-4 pg 21	Fig. 12
Q_{gd}	Gate to Drain Charge		102				
Q_g	Total Gate Charge		293				

Note (3): $C_{o(er)}$, a lumped capacitance that gives same stored energy as C_{oss} while V_{ds} is rising from 0 to 800V

$C_{o(tr)}$, a lumped capacitance that gives same charging time as C_{oss} while V_{ds} is rising from 0 to 800V


Reverse Diode Characteristics ($T_c = 25^\circ\text{C}$ unless otherwise specified)

Symbol	Parameter	Typ.	Max.	Unit	Test Conditions	Note
V_{SD}	Diode Forward Voltage	5.1		V	$V_{GS} = -4\text{ V}, I_{SD} = 42.15\text{ A}, T_J = 25^\circ\text{C}$	Fig. 8, 9, 10
		4.7		V	$V_{GS} = -4\text{ V}, I_{SD} = 42.15\text{ A}, T_J = 175^\circ\text{C}$	
I_S	Continuous Diode Forward Current		89	A	$V_{GS} = -4\text{ V}, T_c = 25^\circ\text{C}$	
$I_{S, \text{pulse}}$	Diode pulse Current		337	A	$V_{GS} = -4\text{ V}$, pulse width t_p limited by $T_{J\text{max}}$	
t_{rr}	Reverse Recover time	67		ns	$V_{GS} = -4\text{ V}, I_{SD} = 84.29\text{ A}, V_R = 800\text{ V}$ $dif/dt = 2270\text{ A}/\mu\text{s}, T_J = 175^\circ\text{C}$	
Q_{rr}	Reverse Recovery Charge	1594		nC		
I_{rrm}	Peak Reverse Recovery Current	41		A		
t_{rr}	Reverse Recover time	122		ns	$V_{GS} = -4\text{ V}, I_{SD} = 84.29\text{ A}, V_R = 800\text{ V}$ $dif/dt = 1270\text{ A}/\mu\text{s}, T_J = 175^\circ\text{C}$	
Q_{rr}	Reverse Recovery Charge	1496		nC		
I_{rrm}	Peak Reverse Recovery Current	30		A		

Thermal Characteristics

Symbol	Parameter	Typ.	Max.	Unit	Test Conditions	Note
$R_{\theta JC}$	Thermal Resistance from Junction to Case	0.22	0.29	$^\circ\text{C}/\text{W}$		Fig. 21



Typical Performance




Figure 1. Output Characteristics $T_J = -55\text{ }^{\circ}\text{C}$




Figure 2. Output Characteristics $T_J = 25\text{ }^{\circ}\text{C}$




Figure 3. Output Characteristics $T_J = 175\text{ }^{\circ}\text{C}$




Figure 4. Normalized On-Resistance vs. Temperature




Figure 5. On-Resistance vs. Drain Current
For Various Temperatures




Figure 6. On-Resistance vs. Temperature
For Various Gate Voltage

Typical Performance




Figure 7. Transfer Characteristic for Various Junction Temperatures




Figure 8. Body Diode Characteristic at -55 °C




Figure 9. Body Diode Characteristic at 25 °C




Figure 10. Body Diode Characteristic at 175 °C




Figure 11. Threshold Voltage vs. Temperature




Figure 12. Gate Charge Characteristics

Typical Performance





Figure 13. 3rd Quadrant Characteristic at -55°C Figure 14. 3rd Quadrant Characteristic at 25°C Figure 15. 3rd Quadrant Characteristic at 175°C 

Figure 16. Output Capacitor Stored Energy




Figure 17. Capacitances vs. Drain-Source Voltage (0 - 200V)




Figure 18. Capacitances vs. Drain-Source Voltage (0 - 1200V)

Typical Performance




Figure 19. Continuous Drain Current Derating vs. Case Temperature




Figure 20. Maximum Power Dissipation Derating vs. Case Temperature




Figure 21. Transient Thermal Impedance (Junction - Case)




Figure 22. Safe Operating Area




Figure 23. Clamped Inductive Switching Energy vs. Low Drain Current ($V_{DD} = 800V$)




Figure 24. Clamped Inductive Switching Energy vs. High Drain Current ($V_{DD} = 800V$)

Typical Performance



Figure 25. Clamped Inductive Switching Energy vs. $R_{G(\text{ext})}$ 

Figure 26. Clamped Inductive Switching Energy vs. Temperature



Figure 27. Switching Times vs. $R_{G(\text{ext})}$ 

Figure 28. Switching Times Definition

Test Circuit Schematic






Figure 29. Clamped Inductive Switching Waveform Test Circuit

Package Dimensions



Recommended Solder Pad Layout





Revision history

Document Version	Date of release	Descriptiion of changes
1.0	January-2024	Initial datasheet
2	January - 2025	Legal Disclaimer Updated



Notes & Disclaimer

WOLFSPPEED PROVIDES TECHNICAL AND RELIABILITY DATA, DESIGN RESOURCES, APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, AND OTHER RESOURCES “AS IS” AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, WITH RESPECT THERETO, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, SUITABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD-PARTY INTELLECTUAL PROPERTY RIGHTS.

This document and the information contained herein are subject to change without notice. Any such change shall be evidenced by the publication of an updated version of this document by Wolfsppeed. No communication from any employee or agent of Wolfsppeed or any third party shall effect an amendment or modification of this document. No responsibility is assumed by Wolfsppeed for any infringement of patents or other rights of third parties which may result from use of the information contained herein. No license is granted by implication or otherwise under any patent or patent rights of Wolfsppeed.

The information contained in this document (excluding examples, as well as figures or values that are labeled as “typical”) constitutes Wolfsppeed’s sole published specifications for the subject product. “Typical” parameters are the average values expected by Wolfsppeed in large quantities and are provided for informational purposes only. Any examples provided herein have not been produced under conditions intended to replicate any specific end use. Product performance can and does vary due to a number of factors.

This product has not been designed or tested for use in, and is not intended for use in, any application in which failure of the product would reasonably be expected to cause death, personal injury, or property damage. For purposes of (but without limiting) the foregoing, this product is not designed, intended, or authorized for use as a critical component in equipment implanted into the human body, life-support machines, cardiac defibrillators, and similar emergency medical equipment; air traffic control systems; or equipment used in the planning, construction, maintenance, or operation of nuclear facilities. Notwithstanding any application-specific information, guidance, assistance, or support that Wolfsppeed may provide, the buyer of this product is solely responsible for determining the suitability of this product for the buyer’s purposes, including without limitation (1) selecting the appropriate Wolfsppeed products for the buyer’s application, (2) designing, validating, and testing the buyer’s application, and (3) ensuring the buyer’s application meets applicable standards and any other legal, regulatory, and safety-related requirements.

RoHS Compliance

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS2), as implemented January 2, 2013. RoHS Declarations for this product can be obtained from your Wolfsppeed representative or from the Product Documentation sections of www.wolfsppeed.com.

REACH Compliance

REACH substances of high concern (SVHCs) information is available for this product. Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact your Wolfsppeed representative to ensure you get the most up-to-date REACH SVHC Declaration. REACH banned substance information (REACH Article 67) is also available upon request.

Contact info:

4600 Silicon Drive
Durham, NC 27703 USA
Tel: +1.919.313.5300
www.wolfsppeed.com/power

© 2025 Wolfsppeed, Inc. All rights reserved. Wolfsppeed® and the Wolfstreak logo are registered trademarks and the Wolfsppeed logo is a trademark of Wolfsppeed, Inc.
PATENT: <https://www.wolfsppeed.com/legal/patents>

The information in this document is subject to change without notice.