


# CBB017M12FM4, CBB017M12FM4T

1200 V, 17 mΩ, Silicon Carbide, Full-Bridge Module

## Technical Features

- Ultra-Low Loss
- High Frequency Operation
- Zero Turn-Off Tail Current from MOSFET
- Normally-Off, Fail-Safe Device Operation
- Optional Pre-Applied Thermal Interface Material
- Features Gen4 Technology with Soft Body Diode



$V_{DS}$	1200 V
$R_{DS(on)}$	17 mΩ

## Typical Applications

- EV Chargers
- High-Efficiency Converters / Inverters
- Renewable Energy
- Smart-Grid / Grid-Tied Distributed Generation

## System Benefits

- Enables Compact, Lightweight Systems
- Increased System Efficiency, due to Low Switching & Conduction Losses of SiC
- Reduced Thermal Requirements and System Cost

## Key Parameters

Parameter	Symbol	Min.	Typ.	Max.	Unit	Test Conditions	Note
Drain-Source Voltage	$V_{DS}$			1200	V	$T_{HS} = 25\text{ }^{\circ}\text{C}$	
Maximum Gate-Source Voltage	$V_{GS(max)}$	-8		+19		Transient	Fig. 33
Operational Gate-Source Voltage	$V_{GS(op)}$		-4/15			Static	Note 1
DC Continuous Drain Current ( $T_{VJ} \leq 150\text{ }^{\circ}\text{C}$ )	$I_D$			50	A	$V_{GS} = 15\text{ V}, T_{HS} = 50\text{ }^{\circ}\text{C}, T_{VJ} \leq 150\text{ }^{\circ}\text{C}$	Notes 2,3 Fig. 20
DC Continuous Drain Current ( $T_{VJ} \leq 175\text{ }^{\circ}\text{C}$ )				50		$V_{GS} = 15\text{ V}, T_{HS} = 50\text{ }^{\circ}\text{C}, T_{VJ} \leq 175\text{ }^{\circ}\text{C}$	
Pulsed Drain Current	$I_{DM}$			100		$t_{pmax}$ limited by $T_{VJmax}$ $V_{GS} = 15\text{ V}, T_{HS} = 50\text{ }^{\circ}\text{C}$	
Power Dissipation	$P_D$		168		W	$T_{HS} = 50\text{ }^{\circ}\text{C}, T_{VJ} \leq 175\text{ }^{\circ}\text{C}$	Note 4 Fig. 20
Virtual Junction Temperature	$T_{VJ(op)}$	-40		150	$^{\circ}\text{C}$	Operation	
		-40		175	$^{\circ}\text{C}$	Intermittent with Reduced Life	

Note (1): Recommended turn-on gate voltage is 15 V with  $\pm 5\%$  regulation tolerance

Note (2): Current limit at  $T_{HS} = 50\text{ }^{\circ}\text{C}$  imposed by package

Note (3): Verified by design

Note (4):  $P_D = (T_{VJ} - T_{HS}) / R_{TH(JH,typ)}$

**MOSFET Characteristics (Per Position) ( $T_{vj} = 25\text{ }^{\circ}\text{C}$  unless otherwise specified)**

Parameter	Symbol	Min.	Typ.	Max.	Unit	Test Conditions	Note
Drain-Source Breakdown Voltage	$V_{(BR)DSS}$	1200			V	$V_{GS} = 0\text{ V}, T_{vj} = -40\text{ }^{\circ}\text{C}$	
Gate Threshold Voltage	$V_{GS(th)}$	1.8	2.5	4.0		$V_{DS} = V_{GS}, I_D = 19\text{ mA}$	
			2.0			$V_{DS} = V_{GS}, I_D = 19\text{ mA}, T_{vj} = 175\text{ }^{\circ}\text{C}$	
Zero Gate Voltage Drain Current	$I_{DSS}$		2	200	$\mu\text{A}$	$V_{GS} = 0\text{ V}, V_{DS} = 1200\text{ V}$	
Gate-Source Leakage Current	$I_{GSS}$		40	800	nA	$V_{GS} = 19\text{ V}, V_{DS} = 0\text{ V}$	
Drain-Source On-State Resistance (Devices Only)	$R_{DS(on)}$		16.5	22.3	m $\Omega$	$V_{GS} = 15\text{ V}, I_D = 60\text{ A}, T_{vj} = 25\text{ }^{\circ}\text{C}$	Fig. 2 Fig. 3
			26.4			$V_{GS} = 15\text{ V}, I_D = 60\text{ A}, T_{vj} = 150\text{ }^{\circ}\text{C}$	
			29.7			$V_{GS} = 15\text{ V}, I_D = 60\text{ A}, T_{vj} = 175\text{ }^{\circ}\text{C}$	
Transconductance	$g_{fs}$		54		S	$V_{DS} = 20\text{ V}, I_D = 60\text{ A}, T_{vj} = 25\text{ }^{\circ}\text{C}$	Fig. 4
			58			$V_{DS} = 20\text{ V}, I_D = 60\text{ A}, T_{vj} = 175\text{ }^{\circ}\text{C}$	
Turn-On Switching Energy, $T_{vj} = 25\text{ }^{\circ}\text{C}$ $T_{vj} = 125\text{ }^{\circ}\text{C}$ $T_{vj} = 175\text{ }^{\circ}\text{C}$	$E_{On}$		0.66 0.51 0.58		mJ	$V_{DD} = 600\text{ V},$ $I_D = 50\text{ A},$ $V_{GS} = -4\text{ V}/15\text{ V},$ $R_{G(Off)} = 0\text{ }\Omega, R_{G(On)} = 0\text{ }\Omega,$ $L_G = 23\text{ nH}$	Fig. 11 Fig. 13
Turn-Off Switching Energy, $T_{vj} = 25\text{ }^{\circ}\text{C}$ $T_{vj} = 125\text{ }^{\circ}\text{C}$ $T_{vj} = 175\text{ }^{\circ}\text{C}$	$E_{Off}$		0.036 0.033 0.032				
Internal Gate Resistance	$R_{G(int)}$		2.1		$\Omega$	$f = 100\text{ kHz}$	
Input Capacitance	$C_{iss}$		6.8		nF	$V_{GS} = 0\text{ V}, V_{DS} = 800\text{ V},$ $V_{AC} = 25\text{ mV}, f = 100\text{ kHz}$	Fig. 9
Output Capacitance	$C_{oss}$		0.25				
Reverse Transfer Capacitance	$C_{rss}$		22		pF		
Gate to Source Charge	$Q_{GS}$		120		nC	$V_{DS} = 800\text{ V}, V_{GS} = -4\text{ V}/15\text{ V},$ $I_D = 60\text{ A},$ Per IEC60747-8-4 page 21	
Gate to Drain Charge	$Q_{GD}$		64				
Total Gate Charge	$Q_G$		270				
FET Thermal Resistance, Junction to Heatsink	$R_{th JH}$		0.748		$^{\circ}\text{C}/\text{W}$	Measured with Pre-Applied TIM	Fig. 17

**Diode Characteristics (Per Position) ( $T_{vj} = 25\text{ }^{\circ}\text{C}$  unless otherwise specified)**

Parameter	Symbol	Min.	Typ.	Max.	Unit	Test Conditions	Notes
Body Diode Forward Voltage	$V_{SD}$		5.6		V	$V_{GS} = -4\text{ V}, I_{SD} = 60\text{ A}$	Fig. 7
			5.2			$V_{GS} = -4\text{ V}, I_{SD} = 60\text{ A}, T_{vj} = 175\text{ }^{\circ}\text{C}$	
DC Source-Drain Current (Body Diode)	$I_{SD BD}$		37		A	$V_{GS} = -4\text{ V}, T_{HS} = 50\text{ }^{\circ}\text{C}, T_{vj} \leq 175\text{ }^{\circ}\text{C}$	Note 3 Fig. 20
Reverse Recovery Time	$t_{RR}$		15.6		ns	$V_{GS} = -4\text{ V}, I_{SD} = 50\text{ A}, V_R = 600\text{ V}$ $di/dt = 15.6\text{ A/ns}, T_{vj} = 175\text{ }^{\circ}\text{C}$	Fig. 32
Reverse Recovery Charge	$Q_{RR}$		1.3		$\mu\text{C}$		
Peak Reverse Recovery Current	$I_{RRM}$		145		A		
Reverse Recovery Energy, $T_{vj} = 25\text{ }^{\circ}\text{C}$ $T_{vj} = 125\text{ }^{\circ}\text{C}$ $T_{vj} = 175\text{ }^{\circ}\text{C}$	$E_{RR}$		0.34 0.41 0.50		mJ	$V_{DD} = 600\text{ V}, I_D = 50\text{ A},$ $V_{GS} = -4\text{ V}/15\text{ V}, R_{G(On)} = 0\text{ }\Omega,$ $L_G = 23\text{ nH}$	Fig. 14



Module Physical Characteristics

Parameter	Symbol	Min.	Typ.	Max.	Unit	Test Conditions
Package Resistance, M1 (High-Side)	$R_{HS}$		4.4		mΩ	$T_{HS} = 125^{\circ}\text{C}$ , Note 5
Package Resistance, M2 (Low-Side)	$R_{LS}$		6.0			
Stray Inductance	$L_{Stray}$		16.4		nH	Between DC- and DC+, $f = 10\text{ MHz}$
Case Temperature	$T_c$	-40		125	$^{\circ}\text{C}$	
Mounting Torque	$M_s$		2.0	2.3	N-m	M4 bolts
Weight	W		21		g	
Case Isolation Voltage	$V_{isol}$	3			kV	AC, 50 Hz, 1 minute
Comparative Tracking Index	CTI	200				
Clearance Distance			5.0		mm	Terminal to Terminal
			10.0			Terminal to Heatsink
Creepage Distance			6.3			Terminal to Terminal
			11.5			Terminal to Heatsink


Note (5): Total Effective Resistance (Per Switch Position) = MOSFET  $R_{DS(on)}$  + Switch Position Package Resistance

Temperature Sensor (NTC) Characteristics


Parameter	Symbol	Min.	Typ.	Max.	Unit	Test Conditions
Rated Resistance	$R_{NTC}$		5.0		kΩ	$T_{NTC} = 25^{\circ}\text{C}$
Resistance Tolerance at 25 °C	$\Delta R/R$	-5		5	%	
Beta Value ( $T_2 = 50\text{ }^{\circ}\text{C}$ )	$\beta_{25/50}$		3380		K	
Beta Value ( $T_2 = 80\text{ }^{\circ}\text{C}$ )	$\beta_{25/80}$		3468		K	
Beta Value ( $T_2 = 100\text{ }^{\circ}\text{C}$ )	$\beta_{25/100}$		3523		K	
Power Dissipation	$P_{Max}$			10	mW	$T_{NTC} = 25^{\circ}\text{C}$




## Typical Performance




**Figure 1.** Output Characteristics for Various Junction Temperatures




**Figure 2.** Normalized On-State Resistance vs. Drain Current for Various Junction Temperatures




**Figure 3.** Normalized On-State Resistance vs. Junction Temperature



**Figure 4.** Transfer Characteristic for Various Junction Temperatures




**Figure 5.** 3<sup>rd</sup> Quadrant Characteristic vs. Junction Temperatures at  $V_{GS} = 15$  V




**Figure 6.** 3<sup>rd</sup> Quadrant Characteristic vs. Junction Temperatures at  $V_{GS} = 0$  V (Body Diode)




## Typical Performance




**Figure 7.** 3<sup>rd</sup> Quadrant Characteristic vs. Junction Temperatures at  $V_{GS} = -4$  V (Body Diode)




**Figure 8.** Typical Capacitances vs. Drain to Source Voltage (0 - 200V)




**Figure 9.** Typical Capacitances vs. Drain to Source Voltage (0 - 1200V)



**Figure 10.** Threshold Voltage vs. Junction Temperature




**Figure 11.** Switching Energy vs. Drain Current ( $V_{DD} = 600$  V)




**Figure 12.** Switching Energy vs. Drain Current ( $V_{DD} = 800$  V)




## Typical Performance




**Figure 13.** MOSFET Switching Energy vs. Junction Temperature




**Figure 14.** Reverse Recovery Energy vs. Junction Temperature




**Figure 15.** MOSFET Switching Energy vs. External Gate Resistance



**Figure 16.** Reverse Recovery Energy vs. External Gate Resistance




**Figure 17.** MOSFET Junction to Heatsink Transient Thermal Impedance,  $Z_{th JHS}$  (°C/W)




**Figure 18.** Forward Bias Safe Operating Area (FBSOA)


## Typical Performance




**Figure 19.** Switching Safe Operating Area




**Figure 20.** Continuous Drain Current Derating vs. Heatsink Temperature



**Figure 21.** Maximum Power Dissipation Derating vs. Heatsink Temperature




**Figure 22.** Typical Output Current Capability vs. Switching Frequency (Inverter Application)




**Figure 23.** Nominal NTC Resistance vs. NTC Temperature




## Timing Characteristics




**Figure 24.** Timing vs. Source Current




**Figure 25.** dv/dt and di/dt vs. Source Current




**Figure 25.** Timing vs. Junction Temperature



**Figure 26.** dv/dt and di/dt vs. Junction Temperature




**Figure 27.** Timing vs. External Gate Resistance




**Figure 28.** dv/dt and di/dt vs. External Gate Resistance




## Definitions




**Figure 29.** Turn-off Transient Definitions



**Figure 30.** Turn-on Transient Definitions





**Figure 31.** Reverse Recovery Definitions




**Figure 32.**  $V_{GS}$  Transient Definitions



Pinout



Package Dimension (mm)



DIMENSION TABLE		
SYMBOL	DIMENSION	TOLERANCE
A1	33.8	±0.30
A2	62.8	±0.50
A3	28.1	±0.20
A4	53	±0.10
A5	19.45	±0.20
A6	48	±0.30
A7	42.5	±0.20
A8	16.4	±0.20
A9	4.5	+0.10 -0
A10	36.8	±0.20
A11	∅2.3 √8.5	∅: +0 -0.10 √: ±0.30
B1	16.4	±0.50
B2	12.0	±0.35
B4	1.35	±0.20
ALL PIN LOCATIONS		±0.40



Product Ordering Code

Part Number	Description
CBB017M12FM4	Without Pre-Applied Phase Change Thermal Interface Material
CBB017M12FM4T	With Pre-Applied Phase Change Thermal Interface Material

Supporting Links & Tools

Evaluation Tools & Support

- [All LTSpice Models](#)
- [All PLECS Models](#)
- [SpeedFit 2.0 Design Simulator™](#)
- [Technical Support Forum](#)

Dual-Channel Gate Driver Board

- [EVAL-ADUM4146WHB1Z: Analog Devices® Gate Driver Board](#)
- [Si823H-AxWA-KIT: Skyworks® Gate Driver Board](#)
- [ACPL-355JC: Broadcom® Gate Driver Board](#)
- [CGD1700HB2M-UNA: Wolfspeed Gate Driver Board](#)
- [CGD12HB00D: Differential Transceiver Daughter Board Companion Tool for Differential Gate Drivers](#)

Application Notes

- [CPWR-AN41: Mounting Instructions and PCB Requirements](#)
- [CPWR-AN42: Thermal Interface Material Application Note](#)
- [CPWR-AN45: Dynamic Performance Application Note](#)



## Notes & Disclaimers

---

WOLFSPPEED PROVIDES TECHNICAL AND RELIABILITY DATA, DESIGN RESOURCES, APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, AND OTHER RESOURCES “AS IS” AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, WITH RESPECT THERETO, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, SUITABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD-PARTY INTELLECTUAL PROPERTY RIGHTS.

This document and the information contained herein are subject to change without notice. Any such change shall be evidenced by the publication of an updated version of this document by Wolfsppeed. No communication from any employee or agent of Wolfsppeed or any third party shall effect an amendment or modification of this document. No responsibility is assumed by Wolfsppeed for any infringement of patents or other rights of third parties which may result from use of the information contained herein. No license is granted by implication or otherwise under any patent or patent rights of Wolfsppeed.

The information contained in this document (excluding examples, as well as figures or values that are labeled as “typical”) constitutes Wolfsppeed’s sole published specifications for the subject product. “Typical” parameters are the average values expected by Wolfsppeed in large quantities and are provided for informational purposes only. Any examples provided herein have not been produced under conditions intended to replicate any specific end use. Product performance can and does vary due to a number of factors.

This product has not been designed or tested for use in, and is not intended for use in, any application in which failure of the product would reasonably be expected to cause death, personal injury, or property damage. For purposes of (but without limiting) the foregoing, this product is not designed, intended, or authorized for use as a critical component in equipment implanted into the human body, life-support machines, cardiac defibrillators, and similar emergency medical equipment; air traffic control systems; or equipment used in the planning, construction, maintenance, or operation of nuclear facilities. Notwithstanding any application-specific information, guidance, assistance, or support that Wolfsppeed may provide, the buyer of this product is solely responsible for determining the suitability of this product for the buyer’s purposes, including without limitation (1) selecting the appropriate Wolfsppeed products for the buyer’s application, (2) designing, validating, and testing the buyer’s application, and (3) ensuring the buyer’s application meets applicable standards and any other legal, regulatory, and safety-related requirements.

### RoHS Compliance

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS2), as implemented January 2, 2013. RoHS Declarations for this product can be obtained from your Wolfsppeed representative or from the Product Documentation sections of [www.wolfsppeed.com](http://www.wolfsppeed.com).

### REACH Compliance

REACH substances of high concern (SVHCs) information is available for this product. Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact your Wolfsppeed representative to ensure you get the most up-to-date REACH SVHC Declaration. REACH banned substance information (REACH Article 67) is also available upon request.

### Contact info:

4600 Silicon Drive  
Durham, NC 27703 USA  
Tel: +1.919.313.5300  
[www.wolfsppeed.com/power](http://www.wolfsppeed.com/power)