


CLB800M12HM3P, CLB800M12HM3PT

1200 V, 800 A, Silicon Carbide, Common-Source Module

V_{DS}	1200 V
I_{DS}	800 A

Technical Features

- Low Inductance, Low Profile 62 mm Footprint
- High Junction Temperature (175 °C) Operation
- Implements Gen 3+ SiC MOSFET Technology with Improved Conduction Loss
- Light Weight AlSiC Baseplate
- High Reliability Silicon Nitride Insulator



Typical Applications

- Solid State Circuit Breakers
- EV Battery Disconnect
- T-type Inverters
- Four-Quadrant Power Converters
- UPS and SMPS

System Benefits

- Lightweight, Compact Form Factor with 62 mm Compatible Baseplate Enables System Retrofit
- Increased System Efficiency, due to Low Switching & Conduction Losses of SiC
- High Reliability Material Selection

Maximum Parameters (Verified by Design)

Parameter	Symbol	Min.	Typ.	Max.	Unit	Conditions	Note
Drain-Source Voltage	V_{DS}			1200	V		
Gate-Source Voltage, Maximum Value	$V_{GS(max)}$	-8		+19		Transient	Note 1
Gate-Source Voltage, Recommended	$V_{GS(op)}$		-4/+15			Static	Fig. 19
DC Continuous Drain Current	I_D		1051		A	$V_{GS} = 15 \text{ V}, T_C = 25 \text{ }^\circ\text{C}, T_{VJ} \leq 175 \text{ }^\circ\text{C}$	Notes 2, 3 Fig. 13
			791			$V_{GS} = 15 \text{ V}, T_C = 90 \text{ }^\circ\text{C}, T_{VJ} \leq 175 \text{ }^\circ\text{C}$	
DC Source-Drain Current (Body Diode)	$I_{SD(BD)}$		512			$V_{GS} = -4 \text{ V}, T_C = 25 \text{ }^\circ\text{C}, T_{VJ} \leq 175 \text{ }^\circ\text{C}$	
Pulsed Drain-Source Current	I_{DM}		3164			t_{pmax} limited by T_{VJmax} $V_{GS} = 15 \text{ V}, T_C = 25 \text{ }^\circ\text{C}$	
Power Dissipation	P_D		2540		W	$T_C = 25 \text{ }^\circ\text{C}, T_{VJ} \leq 175 \text{ }^\circ\text{C}$	Note 4 Fig. 14
Virtual Junction Temperature	$T_{VJ(op)}$	-40		175	$^\circ\text{C}$		

Note (1): Recommended turn-on gate voltage is 15 V with $\pm 5 \%$ regulation tolerance

Note (2): Current limit calculated by $I_{D(max)} = \sqrt{(P_D/R_{DS(typ)}(T_{VJ(max)}, I_{D(max)}))}$

Note (3): Verified by design

Note (4): $P_D = (T_{VJ} - T_C)/R_{TH(JC, typ)}$

MOSFET Characteristics (Per Position) ($T_{vj} = 25\text{ }^{\circ}\text{C}$ Unless Otherwise Specified)

Parameter	Symbol	Min.	Typ.	Max.	Unit	Conditions	Note
Drain-Source Breakdown Voltage	$V_{(BR)DSS}$	1200			V	$V_{GS} = 0\text{ V}$, $T_{vj} = -40\text{ }^{\circ}\text{C}$	
Gate Threshold Voltage	$V_{GS(th)}$	1.3	2.5	3.9		$V_{DS} = V_{GS}$, $I_D = 255\text{ mA}$	
			2.0			$V_{DS} = V_{GS}$, $I_D = 255\text{ mA}$, $T_{vj} = 175\text{ }^{\circ}\text{C}$	
Zero Gate Voltage Drain Current	I_{DSS}		12	384	μA	$V_{GS} = 0\text{ V}$, $V_{DS} = 1200\text{ V}$	
Gate-Source Leakage Current	I_{GSS}		0.12	1.2		$V_{GS} = 15\text{ V}$, $V_{DS} = 0\text{ V}$	
Drain-Source On-State Resistance (Devices Only)	$R_{DS(on)}$		1.3	1.7	$\text{m}\Omega$	$V_{GS} = 15\text{ V}$, $I_D = 800\text{ A}$	Fig. 2 Fig. 3
			2.3			$V_{GS} = 15\text{ V}$, $I_D = 800\text{ A}$, $T_{vj} = 175\text{ }^{\circ}\text{C}$	
Transconductance	g_{fs}		619		S	$V_{DS} = 20\text{ V}$, $I_{DS} = 800\text{ A}$	Fig. 4
			573			$V_{DS} = 20\text{ V}$, $I_{DS} = 800\text{ A}$, $T_{vj} = 175\text{ }^{\circ}\text{C}$	
Internal Gate Resistance	$R_{G(int)}$		0.48		Ω	$f = 100\text{ kHz}$	
Input Capacitance	C_{iss}		94.9		nF	$V_{GS} = 0\text{ V}$, $V_{DS} = 800\text{ V}$, $V_{AC} = 25\text{ mV}$, $f = 100\text{ kHz}$	Fig. 9
Output Capacitance	C_{oss}		3.1				
Reverse Transfer Capacitance	C_{rss}		180		pF		
Gate to Source Charge	Q_{GS}		888		nC	$V_{DS} = 800\text{ V}$, $V_{GS} = -4\text{ V}/15\text{ V}$ $I_D = 800\text{ A}$ Per IEC60747-8-4 pg 21	
Gate to Drain Charge	Q_{GD}		804				
Total Gate Charge	Q_G		2784				
Short Circuit Energy	E_{SC}		11.7		J	$V_{BUS} = 800\text{ V}$, $V_{GS} = -4/15\text{ V}$, $R_{G(EXT)} = 5\text{ }\Omega$, $T_{vj} = 175\text{ }^{\circ}\text{C}$, $t_{SC} < 1.54\text{ }\mu\text{s}$, $L_{stray,SC} = 8.4\text{ nH}$	Notes 5, 6
FET Thermal Resistance, Junction to Case	$R_{th\text{ JC}}$		0.059		$^{\circ}\text{C}/\text{W}$		Fig. 11

Diode Characteristics (Per Position) ($T_{vj} = 25\text{ }^{\circ}\text{C}$ Unless Otherwise Specified)

Parameter	Symbol	Min.	Typ.	Max.	Unit	Conditions	Note
Body Diode Forward Voltage	V_{SD}		5.7		V	$V_{GS} = -4\text{ V}$, $I_{SD} = 800\text{ A}$	Fig. 7
			5.2			$V_{GS} = -4\text{ V}$, $I_{SD} = 800\text{ A}$, $T_{vj} = 175\text{ }^{\circ}\text{C}$	

Note (5): Refer to PRD-08296

Note (6): V_{DSmax} depends on effective short circuit stray inductance ($L_{stray,SC}$), $V_{DSmax} = V_{BUS} + L_{stray,SC} \cdot di/dt$



Module Physical Characteristics

Parameter	Symbol	Min.	Typ.	Max.	Unit	Conditions
Package Resistance, M1	R ₁₋₂		106.5		μΩ	T _C = 125 °C, Note 5
Package Resistance, M2	R ₂₋₃		126.3			T _C = 125 °C, Note 5
Stray Inductance	L _{Stray}		4.9		nH	Between Terminals 1 and 3
Case Temperature	T _C	-40		125	°C	
Weight	W		179		g	
Mounting Torque	M _S	4.5		6.0	N-m	Baseplate, M6 Bolts
		0.9	1.1	1.3		Power Terminals, M4 × 0.7 mm Bolts
Case Isolation Voltage	V _{isol}	4			kV	AC, 50 Hz, 1 min
Comparative Tracking Index	CTI	600				
Clearance Distance		9.43			mm	Terminal to Terminal
		12.70				Terminal to Baseplate
Creepage Distance		13.05				Terminal to Terminal
		15.30				Terminal to Baseplate

Note (5): Total Effective Resistance (Per Switch Position) = MOSFET R_{DS(on)} + Switch Position Package Resistance

Temperature Sensor (NTC) Characteristics

Parameter	Symbol	Min.	Typ.	Max.	Unit	Conditions
Resistance at 25 °C	R ₂₅		4700		Ω	T _{NTC} = 25 °C
Tolerance of R ₂₅			±1		%	
Beta Value for 25 °C to 85 °C	B _{25/85}		3435		K	
Beta Value for 0 °C to 100 °C	B _{0/100}		3399		K	
Tolerance of B _{25/85}			±1		%	
Maximum Power Dissipation	P ₂₅		50		mW	

Steinhart & Hart Coefficients for NTC Resistance & NTC Temperature Computation (T in K)

$\ln\left(\frac{R}{R_{25}}\right) = A + \frac{B}{T} + \frac{C}{T^2} + \frac{D}{T^3}$				$\frac{1}{T} = A_1 + B_1 \ln\left(\frac{R}{R_{25}}\right) + C_1 \ln^2\left(\frac{R}{R_{25}}\right) + D_1 \ln^3\left(\frac{R}{R_{25}}\right)$			
A	B	C	D	A ₁	B ₁	C ₁	D ₁
-1.289E+01	4.245E+03	-8.749E+04	-9.588E+06	3.354E-03	3.001E-04	5.085E-06	2.188E-07

Typical Performance




Figure 1. Output Characteristics for Various Junction Temperatures




Figure 2. Normalized On-State Resistance vs. Drain Current for Various Junction Temperatures




Figure 3. Normalized On-State Resistance vs. Junction Temperature




Figure 4. Transfer Characteristic for Various Junction Temperatures




Figure 5. 3rd Quadrant Characteristic vs. Junction Temperatures at $V_{GS} = 15$ V




Figure 6. 3rd Quadrant Characteristic vs. Junction Temperatures at $V_{GS} = 0$ V (Body Diode)

Typical Performance




Figure 7. 3rd Quadrant Characteristic vs. Junction Temperatures at $V_{GS} = -4$ V (Body Diode)




Figure 8. Typical Capacitances vs. Drain to Source Voltage (0 - 200 V)




Figure 9. Typical Capacitances vs. Drain to Source Voltage (0 - 1200V)




Figure 10. Threshold Voltage vs. Junction Temperature




Figure 11. MOSFET Junction to Case Transient Thermal Impedance, Z_{thJC} (°C/W)




Figure 12. Pulsed Current SOA



Typical Performance




Figure 13. Continuous Drain Current Derating vs. Case Temperature




Figure 14. Maximum Power Dissipation Derating vs. Case Temperature




Figure 15. Typical NTC Resistance vs. Temperature

Definitions




Figure 16. Turn-Off Transient Definitions




Figure 17. Turn-On Transient Definitions




Figure 18. Reverse Recovery Definitions






Figure 19. V_{GS} Transient Definitions




Schematic and Pin Out



PIN OUT SCHEME	
PIN	LABEL
①	D1
②	Mid
③	D2
④	G1, Top row pins (2)
⑤	K1, Bottom row pins (2)
⑥	G2, Top row pins (2)
⑦	K2, Bottom row pins (2)
⑧	NTC1
⑨	NTC2




Package Dimensions (mm)



NOTE:
ALL MARKINGS SHALL
CONFORM TO PRC-00786.

DIMENSION TABLE		
SYMBOL	DIMENSION	TOLERANCE
A1	110	±0.60
A2	109.25	±0.60
A3	65	±0.60
A4	64.25	±0.60
A5	3.25	±0.40
A6	11.45	±0.60
B1	93	±0.30
B2	48	±0.30
C1	11.29	±0.40
C2	13.83	±0.40
C3	24	±0.40
C4	34.17	±0.40
C5	36.71	±0.40
C6	1.71	±0.40
C7	17.84	±0.75
C8	2.54	±0.30
C9	0.64	±0.30
C10	10.17	±0.40
D1	23.75	±0.50
D2	23.13	±0.50
D3	24.13	±0.50
D4	12.65	±0.50
D5	71	±0.30
D6	10.75	±0.50



Note (7): To improve product traceability, Wolfstreak products include Data Matrix Content barcodes in the form of ZZZZZZZZZZ-DDDDDD-XXXX-NNNNNNNNNN, where -Z, -D, -X/-N represent product number, date code, and module serial number, respectively. For instance, CLB800M12HM3P-FA2036-0042-6706546042 is a CLB800M12HM3P produced in 2020 week 36 with a unique serial number.

Note (8): CLB800M12HM3P has been certified by UL as an “Electrically Isolated Semiconductor Devices – Component” in accordance with UL 1557. Only power modules that bear the UL marking shown in the Package Dimension figure above should be considered as being covered under the UL Component Recognition Program.



Product Ordering Code

Part Number	Description
CLB800M12HM3P	Without Pre-Applied Phase Change Thermal Interface Material
CLB800M12HM3PT	With Pre-Applied Phase Change Thermal Interface Material

Supporting Links & Tools

Evaluation Tools & Support

- [SpeedFit 2.0 Design Simulator™](#)
- [Technical Support Forum](#)
- [LTspice and PLECS Models](#)

Dual-Channel Gate Driver Board

- [CGD12HB00D: Differential Transceiver Daughter Board Companion Tool for Differential Gate Drivers](#)
- [CGD1700HB2M-UNA: Wolfspeed Gate Driver Board](#)
- [EVAL-ADUM4146WHB1Z: Analog Devices® Gate Driver Board](#)
- [UCC21710QDWEVM-054: Texas Instruments® Gate Driver Board](#)

Application Notes

- [PRD-04814: Design Options for Wolfspeed® Silicon Carbide MOSFET Gate Bias Power Supplies](#)
- [PRD-06379: Environmental Considerations for Power Electronics Systems](#)
- [PRD-08333: Wolfspeed Module CIL Evaluation Kits User Guide](#)
- [PRD-07933: Wolfspeed Power Module Thermal Interface Material Application User Guide](#)
- [PRD-08376: Thermal Characterization Methods and Applications](#)
- [PRD-07845: Power Module Baseplate Capacitance and Electromagnetic Compatibility](#)
- [PRD-08710: Measuring Stray Inductance in Power Electronics Systems](#)
- [PRD-08911: Considerations for Current Balancing in Paralleled SiC Power Modules](#)
- [PRD-09035: Power Module RC Thermal Models User Guide](#)
- [PRD-08296: SiC MOSFET Short Circuit Application Note](#)



Notes & Disclaimers

WOLFSPEED PROVIDES TECHNICAL AND RELIABILITY DATA, DESIGN RESOURCES, APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, AND OTHER RESOURCES “AS IS” AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, WITH RESPECT THERETO, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, SUITABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD-PARTY INTELLECTUAL PROPERTY RIGHTS.

This document and the information contained herein are subject to change without notice. Any such change shall be evidenced by the publication of an updated version of this document by Wolfspeed. No communication from any employee or agent of Wolfspeed or any third party shall effect an amendment or modification of this document. No responsibility is assumed by Wolfspeed for any infringement of patents or other rights of third parties which may result from use of the information contained herein. No license is granted by implication or otherwise under any patent or patent rights of Wolfspeed.

The information contained in this document (excluding examples, as well as figures or values that are labeled as “typical”) constitutes Wolfspeed’s sole published specifications for the subject product. “Typical” parameters are the average values expected by Wolfspeed in large quantities and are provided for informational purposes only. Any examples provided herein have not been produced under conditions intended to replicate any specific end use. Product performance can and does vary due to a number of factors.

This product has not been designed or tested for use in, and is not intended for use in, any application in which failure of the product would reasonably be expected to cause death, personal injury, or property damage. For purposes of (but without limiting) the foregoing, this product is not designed, intended, or authorized for use as a critical component in equipment implanted into the human body, life-support machines, cardiac defibrillators, and similar emergency medical equipment; air traffic control systems; or equipment used in the planning, construction, maintenance, or operation of nuclear facilities. Notwithstanding any application-specific information, guidance, assistance, or support that Wolfspeed may provide, the buyer of this product is solely responsible for determining the suitability of this product for the buyer’s purposes, including without limitation (1) selecting the appropriate Wolfspeed products for the buyer’s application, (2) designing, validating, and testing the buyer’s application, and (3) ensuring the buyer’s application meets applicable standards and any other legal, regulatory, and safety-related requirements.

RoHS Compliance

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS2), as implemented January 2, 2013. RoHS Declarations for this product can be obtained from your Wolfspeed representative or from the Product Documentation sections of www.wolfspeed.com.

REACH Compliance

REACH substances of high concern (SVHCs) information is available for this product. Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact your Wolfspeed representative to ensure you get the most up-to-date REACH SVHC Declaration. REACH banned substance information (REACH Article 67) is also available upon request.

Contact info:

4600 Silicon Drive
Durham, NC 27703 USA
Tel: +1.919.313.5300
www.wolfspeed.com/power