


CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	3-1 @20°C	0.68 ohms max.
D.C. RESISTANCE	6-4 @20°C	1.25 ohms max.
INDUCTANCE	3-1 10kHz, 100mV, Ls	390µH min.
LEAKAGE INDUCTANCE	3-1 tie(4+6),100kHz, 100mV, Ls	3µH max.
DIELECTRIC	1-6 1500VDC, 1 second	1500VDC, 1 minute
URNS RATIO	(6-4):(3-1)	1.41:1

GENERAL SPECIFICATIONS:
OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.
VOLTAGE-SECOND : 23VµS

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability. Marking method, font and color may vary on preproduction samples.

DFM		Packaging Specifications		Tolerances unless otherwise specified: Angles: ±1° Decimals: ±.005 [.13] Fractions: ±1/64 Footprint: ±.005 [.13] This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	DRAWING TITLE TRANSFORMER	PART NO.
DATE		Method: Tape & Reel				750345425
ENG	TLI	PKG-0637				
REV.	01					
DATE	2023/9/8	www.we-online.com/midcom				SPECIFICATION SHEET 1 OF 1