

C4MS047120QT

Switching Optimized 1200V 47mΩ Silicon Carbide Power MOSFET

Features

- Industry compatible drive voltage 15V...18V/-4V...0V
- Soft body diode with low Vds overshoot and ringing
- Low Rds(on) at high operating temperatures
- Improved device capacitance ratio (Ciss/Crss)
- High transient voltage robustness with improved lifetime
- Halogen free, RoHS compliant

Benefits

- Higher efficiency with lower switching losses and EMI
- Faster switching operation enabling high power density
- Enables system level price performance optimization
- Reduction in system level cooling requirements

Typical Applications

- Data Center Power Supplies
- EV Chargers
- Solar/ESS
- Motor Control
- Industrial Power Supplies
- High Voltage DC/DC Converters

Key Parameters

Parameter	Symbol	Min.	Typ.	Max	Unit	Conditions	Note		
Drain - Source Voltage	V_{DS}			1200	V				
Transient Drain - Source Voltage				1300		<100hrs of lifetime	Note 1		
Maximum Gate - Source Voltage (Transient)	$V_{GS(max)}$	-10		+23		Transient	Note 2		
Operational Turn-On Gate - Source Voltage	$V_{GS(op)}$		+15...+18			A	$V_{GS} = 18V, T_C = 25^\circ C, T_J \leq 175^\circ C$	Refer to AN PRD-04814	
Operational Turn-Off Gate - Source Voltage			-4...0		Note 3				
DC Continuous Drain Current	I_D		61						W
Pulsed Drain Current		I_{DM}		142	t_{Pmax} limited by T_{Jmax} $V_{GS} = 18V, T_C = 25^\circ C$				
Power Dissipation	P_D		330						
Operating Junction and Storage Temperature	T_J	-40		+175	°C		Note 4		
Solder Temperature	T_L			260		According to JEDEC J-STD-020			


Note (1): 100 hours of total accumulated lifetime of the product.

Note (2): When applying IPC-9592B derating it is permissible to use Maximum Vgs of +25V

Note (3): Current limit calculated by $I_{D(max)} = \sqrt{(P_D / R_{DS(typ)} / (T_{J(max)} - T_{D(max)}))}$

Note(4): $P_D = (T_J - T_C) / R_{th(JC,typ)}$

Package



Orderable Part number	Package type	Marking
C4MS047120QT-TR	TSC(QT)	C4MS047120QT



Electrical Characteristics ($T_c = 25^\circ\text{C}$ unless otherwise specified)

Symbol	Parameter	Min.	Typ.	Max.	Unit	Test Conditions	Note
$V_{(BR)DSS}$	Drain-Source Breakdown Voltage	1200			V	$V_{GS} = 0\text{ V}, I_D = 100\ \mu\text{A}$	
$V_{GS(th)}$	Gate Threshold Voltage	2.1	2.6	3.9	V	$V_{DS} = V_{GS}, I_D = 5.6\ \text{mA}$	Fig. 11
			2.3		V	$V_{DS} = V_{GS}, I_D = 5.6\ \text{mA}, T_J = 175^\circ\text{C}$	
I_{DSS}	Zero Gate Voltage Drain Current		1	50	μA	$V_{DS} = 1200\ \text{V}, V_{GS} = 0\ \text{V}$	
I_{GSS}	Gate-Source Leakage Current		10	250	nA	$V_{GS} = 18\ \text{V}, V_{DS} = 0\ \text{V}$	
$R_{DS(on)}$	Drain-Source On-State Resistance		47	63	m Ω	$V_{GS} = 18\ \text{V}, I_D = 20.4\ \text{A}$	Fig. 4, 5, 6
			89			$V_{GS} = 18\ \text{V}, I_D = 20.4\ \text{A}, T_J = 175^\circ\text{C}$	
			59			$V_{GS} = 15\ \text{V}, I_D = 20.4\ \text{A}$	
g_{fs}	Transconductance		16		S	$V_{DS} = 20\ \text{V}, I_D = 20.4\ \text{A}, T_J = 175^\circ\text{C}$	Fig. 7
			16			$V_{DS} = 20\ \text{V}, I_D = 20.4\ \text{A}, T_J = 25^\circ\text{C}$	
$R_{DS(on)Tempco}$	On resistance temperature coefficient		1.88			$V_{GS} = 18\ \text{V}, I_D = 20.4\ \text{A}$	Note 4
C_{iss}	Input Capacitance		1859		pF	$V_{GS} = 0\ \text{V}, V_{DS} = 1000\ \text{V}$ $f = 100\ \text{kHz}$ $V_{AC} = 25\ \text{mV}$	Fig. 17, 18
C_{oss}	Output Capacitance		63				
C_{rss}	Reverse Transfer Capacitance		2.9				
C_{iss}/C_{rss}	Capacitance Ratio		630				Note 5
E_{oss}	C_{oss} Stored Energy		33				μJ
$R_{G(int)}$	Internal Gate Resistance		2.3		Ω	$f = 1\ \text{MHz}$	
Q_{gs}	Gate to Source Charge		19		nC	$V_{DS} = 800\ \text{V}, V_{GS} = -4\ \text{V}/18\ \text{V}$ $I_D = 20.4\ \text{A}$ Per IEC60747-8-4 pg 21	Fig. 12
Q_{gd}	Gate to Drain Charge		16				
Q_g	Total Gate Charge		66				

Note (4): $R_{DS(on)Tempco}$ refers to $R_{DS(on)}$ at $25\ \text{C}$ / $R_{DS(on)}$ at $175\ \text{C}$

Note (5): Capacitance ratio is a FOM for Partial turn-on immunity PRD-06933, this is a family wide value*

Reverse Diode Characteristics ($T_c = 25^\circ\text{C}$ unless otherwise specified)

Symbol	Parameter	Typ.	Max.	Unit	Test Conditions	Note
V_{SD}	Diode Forward Voltage	5.1		V	$V_{GS} = -4\ \text{V}, I_{SD} = 10.2\ \text{A}, T_J = 25^\circ\text{C}$	Fig. 8, 9, 10
		4.5		V	$V_{GS} = -4\ \text{V}, I_{SD} = 10.2\ \text{A}, T_J = 175^\circ\text{C}$	
I_S	Continuous Diode Forward Current	38		A	$V_{GS} = -4\ \text{V}, T_c = 25^\circ\text{C}$	
I_{SM}	Diode Pulse Current		142	A	$V_{GS} = -4\ \text{V}$, pulse width t_p limited by T_{jmax}	

Thermal Characteristics

Symbol	Parameter	Typ.	Unit	Test Conditions	Note
$R_{\theta JC}$	Thermal Resistance from Junction to Case	0.45	$^\circ\text{C}/\text{W}$		



Typical Performance




Figure 1. Output Characteristics $T_j = -55^\circ\text{C}$




Figure 2. Output Characteristics $T_j = 25^\circ\text{C}$




Figure 3. Output Characteristics $T_j = 175^\circ\text{C}$




Figure 4. Normalized On-Resistance vs. Temperature




Figure 5. On-Resistance vs. Drain Current For Various Temperatures




Figure 6. On-Resistance vs. Temperature For Various Gate Voltage



Typical Performance




Figure 7. Transfer Characteristic for Various Junction Temperatures




Figure 8. Body Diode Characteristic at -55 °C




Figure 9. Body Diode Characteristic at 25 °C




Figure 10. Body Diode Characteristic at 175 °C




Figure 11. Threshold Voltage vs. Temperature




Figure 12. Gate Charge Characteristics



Typical Performance




Figure 13. 3rd Quadrant Characteristic at -55°C




Figure 14. 3rd Quadrant Characteristic at 25°C




Figure 15. 3rd Quadrant Characteristic at 175°C




Figure 16. Output Capacitor Stored Energy




Figure 17. Capacitances vs. Drain-Source Voltage (0 - 200 V)





Figure 18. Capacitances vs. Drain-Source Voltage (0 - 1200 V)



Package Dimensions



SYMBOL	MIN	MAX	SYMBOL	MIN	MAX
A	2.25	2.35	E9		0.75
A1	0.00	0.15	e		1.14
A2		0.90	e1		11.4
A3		0.50	F	7.40	7.60
b	0.50	0.70	F1	1.47	1.67
b1	-	0.15	F2	7.40	7.60
c	0.46	0.58	F3	3.65	3.85
D	14.90	15.10	F4	5.07	5.27
D1		12.00	F5	10.24	10.44
D2		13.20	L		1.30
D3	14.50	14.70	M		0.60
E	20.81	21.11	N		22
E1	15.30	15.50	O	0°	8°
E2		9.83	P		0.90
E3		0.625	P1	0.70	0.90
E4		0.45	P2	0.90	1.10
E5		0.95	Q		1.60
E6		2.53	R		1.70
E7		2.40	S		0.631
E8		0.90			



Revision history

Document Version	Date of release	Description of changes
P1	June 2026	Initial release



Notes & Disclaimer

WOLFSPEED PROVIDES TECHNICAL AND RELIABILITY DATA, DESIGN RESOURCES, APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, AND OTHER RESOURCES “AS IS” AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, WITH RESPECT THERETO, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, SUITABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRDPARTY INTELLECTUAL PROPERTY RIGHTS.

This document and the information contained herein are subject to change without notice. Any such change shall be evidenced by the publication of an updated version of this document by Wolfspeed. No communication from any employee or agent of Wolfspeed or any third party shall effect an amendment or modification of this document. No responsibility is assumed by Wolfspeed for any infringement of patents or other rights of third parties which may result from use of the information contained herein. No license is granted by implication or otherwise under any patent or patent rights of Wolfspeed.

The information contained in this document (excluding examples, as well as figures or values that are labeled as “typical”) constitutes Wolfspeed’s sole published specifications for the subject product. “Typical” parameters are the average values expected by Wolfspeed in large quantities and are provided for informational purposes only. Any examples provided herein have not been produced under conditions intended to replicate any specific end use. Product performance can and does vary due to a number of factors.

This product has not been designed or tested for use in, and is not intended for use in, any application in which failure of the product would reasonably be expected to cause death, personal injury, or property damage. For purposes of (but without limiting) the foregoing, this product is not designed, intended, or authorized for use as a critical component in equipment implanted into the human body, life-support machines, cardiac defibrillators, and similar emergency medical equipment; air traffic control systems; or equipment used in the planning, construction, maintenance, or operation of nuclear facilities. Notwithstanding any application-specific information, guidance, assistance, or support that Wolfspeed may provide, the buyer of this product is solely responsible for determining the suitability of this product for the buyer’s purposes, including without limitation (1) selecting the appropriate Wolfspeed products for the buyer’s application, (2) designing, validating, and testing the buyer’s application, and (3) ensuring the buyer’s application meets applicable standards and any other legal, regulatory, and safety-related requirements.

RoHS Compliance

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EU (RoHS2), as implemented February 2, 2013. RoHS Declarations for this product can be obtained from your Wolfspeed representative or from the Product Documentation sections of www.wolfspeed.com.

REACH Compliance

REACH substances of high concern (SVHCs) information is available for this product. Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact your Wolfspeed representative to ensure you get the most up-to-date REACH SVHC Declaration. REACH banned substance information (REACH Article 67) is also available upon request.

Contact info:

4600 Silicon Drive
Durham, NC 27703 USA
Tel: +1.919.313.5300
www.wolfspeed.com/power

© 2025 Wolfspeed, Inc. All rights reserved. Wolfspeed® and the Wolfstreak logo are registered trademarks and the Wolfspeed logo is a trademark of Wolfspeed, Inc.
PATENT: <https://www.wolfspeed.com/legal/patents>

The information in this document is subject to change without notice.