

E4MS018120QT

Automotive Silicon Carbide Power MOSFET



Features

- Industry compatible drive voltage 15 V ...18 V/-4 V ...0 V
- Low $R_{DS(on)}$ at high operating temperatures
- Improved device capacitance ratio (C_{iss}/C_{rss})
- Halogen free, RoHS compliant
- Automotive Qualified (AEC-Q101) and PPAP Capable



Benefits

- Higher efficiency with lower switching losses and EMI
- Faster switching operation enabling high power density
- Enables system level price performance optimization
- Reduction in system level cooling requirements

Typical Applications

- Onboard charger
- High voltage DC/DC converters
- HVAC compressors
- Battery management systems

Package



Orderable Part Number	Package Type	Marking
E4MS018120QT-TR	Q-TSC	E4MS018120QT

Absolute Maximum Ratings

Stress beyond those listed under absolute maximum ratings may damage the device.

Symbol	Parameter	Min.	Max.	Unit	Conditions	Note
$V_{DS(max)}$	Drain-Source Voltage		1200	V		
$V_{GS(max)}$	Maximum Gate - Source Voltage (Transient)	-10	+23		Note 1	
I_D	DC Continuous Drain Current		119	A	$V_{GS} = 18\text{ V}, T_c = 25\text{ }^\circ\text{C}, T_J \leq 175\text{ }^\circ\text{C}$	Note 2
			85		$V_{GS} = 18\text{ V}, T_c = 100\text{ }^\circ\text{C}, T_J \leq 175\text{ }^\circ\text{C}$	
I_{DM}	Pulsed Drain Current		369		$V_{GS} = 18\text{ V}, T_c = 25\text{ }^\circ\text{C}, t_{pmax}$ limited by T_{Jmax}	
P_b	Power Dissipation		483	W	$T_c = 25\text{ }^\circ\text{C}, T_J = 175\text{ }^\circ\text{C}$	Note 3
T_J, T_{stg}	Operating Junction and Storage Temperature	-55	+175	°C		
T_L	Solder Temperature		260		According to JEDEC J-STD-020	

Note (1): Refer to AN PRD-09634

Note (2): Current limit calculated by $I_{D(max)} = \sqrt{(P_D / R_{DS(typ)}(T_{J(max)}, I_{D(max)}))}$

Note (3): $P_D = (T_J - T_C) / R_{th(JC, Max)}$



Electrical Characteristics ($T_C = 25\text{ }^\circ\text{C}$ unless otherwise specified)

Symbol	Parameter	Min.	Typ.	Max.	Unit	Test Conditions	Note
$V_{(BR)DSS}$	Drain – Source Breakdown Voltage	1200			V	$V_{GS} = 0\text{ V}$, $I_b = 100\text{ }\mu\text{A}$	
$V_{GS(th)}$	Gate Threshold Voltage	2.0	2.6	3.9	V	$V_{DS} = V_{GS}$, $I_b = 14.5\text{ mA}$	Fig. 11, Note 1
			2.0		V	$V_{DS} = V_{GS}$, $I_b = 14.5\text{ mA}$, $T_J = 175\text{ }^\circ\text{C}$	
I_{bSS}	Zero Gate Voltage Drain Current		1	50	μA	$V_{DS} = 1200\text{ V}$, $V_{GS} = 0\text{ V}$	
I_{cSS}	Gate-Source Leakage Current		10	250	nA	$V_{GS} = 18\text{ V}$, $V_{DS} = 0\text{ V}$	
$V_{GS(op)}$	Recommended Turn on Gate-Source Voltage		+15...+18		V		Note 4
	Recommended Turn off Gate-Source Voltage		-4...0				
$R_{DS(on)}$	Drain-Source On-State Resistance		18	23.4	m Ω	$V_{GS} = 18\text{ V}$, $I_b = 52.7\text{ A}$	Fig. 4, 5, 6
			33.8			$V_{GS} = 18\text{ V}$, $I_b = 52.7\text{ A}$, $T_J = 175\text{ }^\circ\text{C}$	
			21			$V_{GS} = 15\text{ V}$, $I_b = 52.7\text{ A}$	
g_s	Transconductance		39		S	$V_{DS} = 20\text{ V}$, $I_b = 52.7\text{ A}$	Fig. 7
			38			$V_{DS} = 20\text{ V}$, $I_b = 52.7\text{ A}$, $T_J = 175\text{ }^\circ\text{C}$	
$R_{DS(on)Tempco}$	On Resistance Temperature Coefficient		1.88			$V_{GS} = 18\text{ V}$, $I_b = 52.7\text{ A}$	Note 5
C_{iss}	Input Capacitance		4105		pF	$V_{GS} = 0\text{ V}$, $V_{DS} = 1000\text{ V}$ $f = 100\text{ kHz}$ $V_{AC} = 25\text{ mV}$	Fig. 17, 18
C_{oss}	Output Capacitance		148				
C_{rss}	Reverse Transfer Capacitance		6.5				
C_{iss}/C_{rss}	Capacitance Ratio		630				Note 6
E_{oss}	C_{oss} Stored Energy		96		μJ		Fig. 16
$C_{o(er)}$	Effective Output Capacitance (Energy Related)		215		pF	$V_{GS} = 0\text{ V}$, $V_{DS} = 0\text{ V} \dots 800\text{ V}$	Note 7
$C_{o(tr)}$	Effective Output Capacitance (Time Related)		350				
E_{on}	Turn-On Switching Energy (Body Diode FWD) $T_J = 25\text{ }^\circ\text{C}$ $T_J = 175\text{ }^\circ\text{C}$		347		μJ	$V_{DS} = 800\text{ V}$, $V_{GS} = -4\text{ V} / 18\text{ V}$, $I_b = 52.7\text{ A}$, $R_{G(ext)} = 2\text{ }\Omega$, $L_o = 14\text{ nH}$	Fig. 25, 27, 29
			343				
E_{off}	Turn-Off Switching Energy (Body Diode FWD) $T_J = 25\text{ }^\circ\text{C}$ $T_J = 175\text{ }^\circ\text{C}$		133		μJ	$V_{DS} = 800\text{ V}$, $V_{GS} = -4\text{ V} / 18\text{ V}$, $I_b = 52.7\text{ A}$, $R_{G(ext)} = 2\text{ }\Omega$, $L_o = 14\text{ nH}$	Fig. 25, 28, 29
			130				
$t_{d(on)}$	Turn-On Delay Time		14		ns	$V_{DS} = 800\text{ V}$, $V_{GS} = -4\text{ V} / 18\text{ V}$, $I_b = 52.7\text{ A}$, $R_{G(ext)} = 2\text{ }\Omega$, $L_o = 14\text{ nH}$ Timing relative to I_{DS} Inductive load	Fig. 26, 27, 29
t_r	Rise Time		5				
$t_{d(off)}$	Turn-Off Delay Time		34				Fig. 26, 28, 29
t_f	Fall Time		12				
$R_{G(int)}$	Internal Gate Resistance		1.2		Ω	$f = 1\text{ MHz}$	
Q_{gs}	Gate to Source Charge		47		nC	$V_{DS} = 800\text{ V}$, $V_{GS} = -4\text{ V} / 18\text{ V}$ $I_b = 52.7\text{ A}$	Fig. 12
Q_{gd}	Gate to Drain Charge		50				
Q_g	Total Gate Charge		172				

Note (4): Refer to AN PRD-08999.

Note (5): $R_{DS(on)Tempco}$ refers to $R_{DS(on)}$ at $175\text{ }^\circ\text{C}$ / $R_{DS(on)}$ at $25\text{ }^\circ\text{C}$. This is a E4MS 1200 V product family value.

Note (6): Capacitance ratio is a FOM for partial turn-on immunity AN PRD-06933. This is a E4MS 1200 V product family value.

Note (7): $C_{o(er)}$, a lumped capacitance that gives the same stored energy as C_{oss} while V_{DS} is rising from 0 V to 800 V.

$C_{o(tr)}$, a lumped capacitance that gives the same charging time as C_{oss} while V_{DS} is rising from 0 V to 800 V.



Reverse Diode Characteristics ($T_C = 25\text{ }^\circ\text{C}$ unless otherwise specified)

Symbol	Parameter	Typ.	Max.	Unit	Test Conditions	Note
V_{SD}	Diode Forward Voltage	5.1		V	$V_{GS} = -4\text{ V}, I_{SD} = 26.4\text{ A}, T_J = 25\text{ }^\circ\text{C}$	Fig. 8, 9, 10
		4.5			$V_{GS} = -4\text{ V}, I_{SD} = 26.4\text{ A}, T_J = 175\text{ }^\circ\text{C}$	
I_S	Continuous Diode Forward Current		74	A	$V_{GS} = -4\text{ V}, T_C = 25\text{ }^\circ\text{C}$	
I_{SM}	Diode Pulse Current		369		$V_{GS} = -4\text{ V},$ pulse width t_p limited by T_{Jmax}	
t_{rr}	Reverse Recovery Time	17		ns	$V_{GS} = -4\text{ V}, I_{SD} = 52.7\text{ A}, V_R = 800\text{ V},$ $T_J = 175\text{ }^\circ\text{C}, di/dt = 16694\text{ A}/\mu\text{s}$	Fig. 30
Q_{rr}	Reverse Recovery Charge	1099		nC		
I_{RRM}	Peak Reverse Recovery Current	104		A		
E_{RR}	Reverse Recovery Energy $T_J = 25\text{ }^\circ\text{C}$ $T_J = 175\text{ }^\circ\text{C}$	439 720		μJ		

Thermal Characteristics

Symbol	Parameter	Typ.	Max.	Unit	Test Conditions	Note
$R_{\theta JC}$	Thermal Resistance from Junction to Case	0.24	0.31	$^\circ\text{C}/\text{W}$		



Typical Performance




Figure 1. Output Characteristics $T_{vj} = -55\text{ }^\circ\text{C}$




Figure 2. Output Characteristics $T_{vj} = 25\text{ }^\circ\text{C}$




Figure 3. Output Characteristics $T_{vj} = 175\text{ }^\circ\text{C}$




Figure 4. Normalized On-Resistance vs. Temperature




Figure 5. On-Resistance vs. Drain Current for Various Temperatures




Figure 6. On-Resistance vs. Temperature for Various Gate Voltages



Typical Performance




Figure 7. Transfer Characteristic for Various Junction Temperatures




Figure 8. Body Diode Characteristic at $T_{WJ} = -55\text{ }^{\circ}\text{C}$




Figure 9. Body Diode Characteristic at $T_{WJ} = 25\text{ }^{\circ}\text{C}$




Figure 10. Body Diode Characteristic at $T_{WJ} = 175\text{ }^{\circ}\text{C}$




Figure 11. Threshold Voltage vs. Temperature




Figure 12. Gate Charge Characteristics



Typical Performance




Figure 13. 3rd Quadrant Characteristic at $T_{vj} = -55\text{ }^{\circ}\text{C}$




Figure 14. 3rd Quadrant Characteristic at $T_{vj} = 25\text{ }^{\circ}\text{C}$




Figure 15. 3rd Quadrant Characteristic at $T_{vj} = 175\text{ }^{\circ}\text{C}$




Figure 16. Output Capacitor Stored Energy




Figure 17. Capacitances vs. Drain-Source Voltage (0-200 V)




Figure 18. Capacitances vs. Drain-Source Voltage (0-1200 V)

Typical Performance




Figure 19. Continuous Drain Current Derating vs. Case Temperature




Figure 20. Maximum Power Dissipation Derating vs. Case Temperature




Figure 21. Transient Thermal Impedance (Junction - Case) °C/W




Figure 22. Safe Operating Area




Figure 23. Clamped Inductive Switching Energy vs. Drain Current ($V_{DD} = 800\text{ V}$)




Figure 24. Clamped Inductive Switching Energy vs. $R_{G(ext)}$



Typical Performance




Figure 25. Clamped Inductive Switching Energy vs. Temperature




Figure 26. Switching Times vs. $R_{G(ext)}$




Figure 27. Turn On Switching Time Definition




Figure 28. Turn Off Switching Time Definition




Figure 29. Clamped Inductive MOSFET Switching Waveform Test Circuit





Figure 30. Clamped Inductive Body Diode Switching Waveform Test Circuit

Package Dimensions



DETAIL A
SCALE 8 : 1


SYMBOL	MIN	MAX	SYMBOL	MIN	MAX	PIN	DESCRIPTION
A	2.2	2.35	E6	2.53		1	GATE
A1	0	0.15	E7	2.4		2	KELVIN
A2	0.9		E8	0.9		3-11	SOURCE
A3	0.5		E9	0.75		12-23	DRAIN
b	0.5	0.7	e	1.14			
b1	-	0.15	e1	11.4			
c	0.46	0.58	L	1.3			
D	14.9	15.1	M	0.6			
D1	12		N	22			
D2	13.2		O	0°	8°		
D3	14.5	14.7	P	0.9			
E	20.81	21.11	P1	0.7	0.9		
E1	15.3	15.5	P2	0.9	1.1		
E2	9.83		Q	1.6			
E3	0.625		R	1.7			
E4	0.45		S	0.631			
E5	0.95						

NOTE:

1. ALL METAL SURFACES ARE TIN PLATED (MATTE), EXCEPT AREA OF CUT
2. ALL DIMENSIONS ARE LISTED IN MILLIMETERS. ANGLES IN DEGREES
3. DIMENSIONING & TOLERANCING CONFORM TO ASME Y14.5M-1994.
4. DIMENSIONS DO NOT INCLUDE MOLD FLASH (0.15mm MAX PER SIDE) OR GATE BURR (0.3mm MAX)
5. THE LEAD SIDE IS COMPREHENSIVE OF THE THICKNESS OF THE LEAD FINISH MATERIAL

Recommended Solder Pad Layout

All dimensions in mm





Revision History

Documents Version	Date of Change	Description of Changes
1	6/10/2026	Initial Release

Appendix

Appendix Number	Description
A1	<p>The following are recommendations for turning off the MOSFET with 0 V:</p> <ul style="list-style-type: none">• Measure the V_{GS} spike accurately using high-CMRR probes and low common mode noise measurements.• For the safe operation of the device, the voltage spike shall remain < 5 V for a time duration of < 40 ns.



Notes & Disclaimers

WOLFSPEED PROVIDES TECHNICAL AND RELIABILITY DATA, DESIGN RESOURCES, APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, AND OTHER RESOURCES “AS IS” AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, WITH RESPECT THERETO, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, SUITABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD-PARTY INTELLECTUAL PROPERTY RIGHTS.

This document and the information contained herein are subject to change without notice. Any such change shall be evidenced by the publication of an updated version of this document by Wolfspeed. No communication from any employee or agent of Wolfspeed or any third party shall effect an amendment or modification of this document. No responsibility is assumed by Wolfspeed for any infringement of patents or other rights of third parties which may result from use of the information contained herein. No license is granted by implication or otherwise under any patent or patent rights of Wolfspeed.

The information contained in this document (excluding examples, as well as figures or values that are labeled as “typical”) constitutes Wolfspeed’s sole published specifications for the subject product. “Typical” parameters are the average values expected by Wolfspeed in large quantities and are provided for informational purposes only. Any examples provided herein have not been produced under conditions intended to replicate any specific end use. Product performance can and does vary due to a number of factors.

This product has not been designed or tested for use in, and is not intended for use in, any application in which failure of the product would reasonably be expected to cause death, personal injury, or property damage. For purposes of (but without limiting) the foregoing, this product is not designed, intended, or authorized for use as a critical component in equipment implanted into the human body, life-support machines, cardiac defibrillators, and similar emergency medical equipment; air traffic control systems; or equipment used in the planning, construction, maintenance, or operation of nuclear facilities. Notwithstanding any application-specific information, guidance, assistance, or support that Wolfspeed may provide, the buyer of this product is solely responsible for determining the suitability of this product for the buyer’s purposes, including without limitation (1) selecting the appropriate Wolfspeed products for the buyer’s application, (2) designing, validating, and testing the buyer’s application, and (3) ensuring the buyer’s application meets applicable standards and any other legal, regulatory, and safety-related requirements.

RoHS Compliance

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS2), as implemented January 2, 2013. RoHS Declarations for this product can be obtained from your Wolfspeed representative or from the Product Documentation sections of www.wolfspeed.com.

REACH Compliance

REACH substances of high concern (SVHCs) information is available for this product. Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact your Wolfspeed representative to ensure you get the most up-to-date REACH SVHC Declaration. REACH banned substance information (REACH Article 67) is also available upon request.

Contact info:

4600 Silicon Drive
Durham, NC 27703 USA
Tel: +1.919.313.5300
www.wolfspeed.com/power